

LINEAR SYSTEMS

Linear Integrated Systems

2N/PN/SST4391 SERIES

SINGLE N-CHANNEL JFET SWITCH

FEATURES

Replacement for Siliconix 2N/PN/SST4391, 4292, & 4393

LOW ON RESISTANCE $r_{DS(on)} \leq 30\Omega$

FAST SWITCHING $t_{ON} \leq 15ns$

ABSOLUTE MAXIMUM RATINGS¹

@ 25 °C (unless otherwise stated)

Maximum Temperatures

Storage Temperature (2N) -65 to 200°C

Storage Temperature (PN/SST) -55 to 150°C

Junction Operating Temperature (2N) -55 to 200°C

Junction Operating Temperature (PN/SST) -55 to 150°C

Maximum Power Dissipation

Continuous Power Dissipation (2N) 1800mW

Continuous Power Dissipation (PN/SST) 350mW

Maximum Currents

Gate Current 50mA


Maximum Voltages

Gate to Drain or Source (2N/PN) -40V

Gate to Drain or Source (SST) -35V


2N SERIES

TO-18
BOTTOM VIEW




PN SERIES

TO-92
BOTTOM VIEW



SST SERIES

SOT-23
TOP VIEW



STATIC ELECTRICAL CHARACTERISTICS @25 °C (unless otherwise stated)

SYM.	CHARACTERISTIC		TYP	4391		4392		4393		UNIT	CONDITIONS
				MIN	MAX	MIN	MAX	MIN	MAX		
BV _{GSS}	Gate to Source Breakdown Voltage	2N/PN		-40		-40		-40		V	I _G = -1μA, V _{DS} = 0V
		SST		-35		-35		-35			
V _{GS(off)}	Gate to Source Cutoff Voltage	2N/PN		-4	-10	-2	-5	-0.5	-3		V _{DS} = 20V, I _D = 1nA
		SST		-4	-10	-2	-5	-0.5	-3		V _{DS} = 15V, I _D = 10nA
V _{GS(F)}	Gate to Source Forward Voltage		0.7		1		1		1		I _G = 1mA, V _{DS} = 0V
V _{DS(on)}	Drain to Source On Voltage		0.25						0.4		V _{GS} = 0V, I _D = 3mA
			0.3				0.4				V _{GS} = 0V, I _D = 6mA
			0.35		0.4						V _{GS} = 0V, I _D = 12mA
I _{DSS}	Drain to Source Saturation Current ²	2N		50	150	25	75	5	30	mA	V _{DS} = 20V, V _{GS} = 0V
		PN		50	100	25	100	5	60		
		SST		50		25		5			
I _{GSS}	Gate Leakage Current	2N/SST	-5		-100		-100		-100	pA	V _{GS} = -20V, V _{DS} = 0V
		PN	-5		-1000		-1000		-1000		
I _G	Gate Operating Current		-5								V _{DG} = 15V, I _D = 10mA

Linear Integrated Systems

• 4042 Clipper Court • Fremont, CA 94538 • Tel: 510 490-9160 • Fax: 510 353-0261

STATIC ELECTRICAL CHARACTERISTICS CONT. @25 °C (unless otherwise stated)

SYM.	CHARACTERISTIC		TYP	4391		4392		4393		UNIT	CONDITIONS
				MIN	MAX	MIN	MAX	MIN	MAX		
I _{D(off)}	Drain Cutoff Current	2N	5						100	pA	V _{DS} = 20V, V _{GS} = -5V
			5				100				V _{DS} = 20V, V _{GS} = -7V
			5		100						V _{DS} = 20V, V _{GS} = -12V
		PN	5						1000		V _{DS} = 20V, V _{GS} = -5V
			5				1000				V _{DS} = 20V, V _{GS} = -7V
			5		1000						V _{DS} = 20V, V _{GS} = -12V
		SST	5		100		100		100		V _{DS} = 10V, V _{GS} = -10V
r _{DS(on)}	Drain to Source On Resistance				30		60		100	Ω	V _{GS} = 0V, I _D = 1mA

DYNAMIC ELECTRICAL CHARACTERISTICS @25 °C (unless otherwise stated)

SYM.	CHARACTERISTIC		TYP	4391		4392		4393		UNIT	CONDITIONS
				MIN	MAX	MIN	MAX	MIN	MAX		
g_{fs}	Forward Transconductance		6							mS	$V_{DS} = 20V, I_D = 1mA$
g_{os}	Output Conductance		25							μS	$f = 1kHz$
$r_{ds(on)}$	Drain to Source On Resistance				30		60		100	Ω	$V_{GS} = 0V, I_D = 0A$ $f = 1kHz$
C_{iss}	Input Capacitance	2N	12		14		14		14	pF	$V_{DS} = 20V, V_{GS} = 0V$ $f = 1MHz$
		PN	12		16		16		16		
		SST	13								
C_{rss}	Reverse Transfer Capacitance	2N	3.3						3.5		$V_{DS} = 0V, V_{GS} = -5V$ $f = 1MHz$
		PN	3.5						5		
		SST	3.6								
		2N	3.2				3.5				$V_{DS} = 0V, V_{GS} = -7V$ $f = 1MHz$
		PN	3.4				5				
		SST	3.5								
		2N	2.8		3.5						$V_{DS} = 0V, V_{GS} = -12V$ $f = 1MHz$
		PN	3.0		5						
		SST	3.1								
e_n	Equivalent Input Noise Voltage		3							nV/ $\sqrt{Hz}$	$V_{DS} = 10V, I_D = 10mA$ $f = 1kHz$


SWITCHING ELECTRICAL CHARACTERISTICS @25 °C (unless otherwise stated)

SYM.	CHARACTERISTIC		TYP	4391		4392		4393		UNIT	CONDITIONS
				MIN	MAX	MIN	MAX	MIN	MAX		
t _{d(on)}	Turn On Time	2N/PN	2		15		15		15	ns	V _{DD} = 10V, V _{GS(H)} = 0V
		SST	2								
t _r		2N/PN	2		5		5		5		
		SST	2								
t _{d(off)}	Turn Off Time	2N/PN	6		20		35		50		
		SST	6								
t _f		2N/PN	13		15		20		30		
		SST	13								


SWITCHING CIRCUIT CHARACTERISTICS

SYM.	4391	4392	4393
$V_{GS(L)}$	-12V	-7V	-5V
R_L	800 Ω	1600 Ω	3200 Ω
$I_{D(on)}$	12mA	6mA	3mA


SWITCHING TEST CIRCUIT




TO-18 Three Lead



TO-92



SOT-23



NOTES

1. Absolute maximum ratings are limiting values above which serviceability may be impaired.
2. Pulse test: $PW \leq 300\mu s$, Duty Cycle $\leq 3\%$

Information furnished by Linear Integrated Systems is believed to be accurate and reliable. However, no responsibility is assumed for its use; nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Linear Integrated Systems.