

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION


2012

© COPYRIGHT 2012

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
A1	-		A6	NOTE 1 UPDATED	15NOV2017	SV PKS



- 1 SLOT ACCEPTS SINGLE OR DOUBLE COPPER MAGNET WIRE SAME DIAMETERS NOT FOR USE WITH ALUMINUM MAGNET WIRE
- 2 IDENTIFICATION NUMBER FOR MAGNET WIRE RANGE
- 3 CONTACT CAVITY AND APPLICATION ACC. SPECIFICATION 114-94229
- 4 PCB LAYOUT, HOLES ACC. SPECIFICATION. 108-90801
- 5 CUTTING LINE: AREA WILL BE CUTTED OFF BY TERMINATION
- 6 CAVITY CENTER TO HOLE CENTER
- 7 DELIVERY STATE: STRIP ON CORRUGATED REEL WITH PAPER INTERLAYER
- 8 TO BE APPROVED, ON DEMAND BY TE ENGINEERING
- 9 MAX. 2 SPLICES PER REEL; SPLICES BE NOT BONDED TOGETHER

		24	-	19.5 - 17.5; 17	-	Ø 0.85mm to Ø 1.12mm	2120747-2
		12	-	22.5 - 20; 19.5	-	Ø 0.63mm to Ø 0.85mm	2120746-2
	2825388-1	10	26 - 23	26 - 22.5	Ø 0.4mm to Ø 0.56mm	Ø 0.4mm to Ø 0.63mm	2120745-2
		6	29.5 - 26.5; 26	29.5 - 26.5; 26	Ø 0.265mm to Ø 0.4mm	Ø 0.265mm to Ø 0.4mm	2120744-2
		4	33 - 30; 29.5	33 - 30; 29.5	Ø 0.18mm to Ø 0.265mm	Ø 0.18mm to Ø 0.265mm	2120743-2
	LOOSE PEICE PART NUMBER	IDENTI FICATION NO	DOUBLE WIRE	SINGLE WIRE	DOUBLE WIRE	SINGLE WIRE	PART NO
			1 AWG BARE WIRE RANGE	1 BARE WIRE RANGE			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
	0 PLC	±0.2	
	1 PLC	±0.2	
	2 PLC	±0.2	
	3 PLC	±0.2	
	4 PLC	±0.2	
ANGLES		±1°	
MATERIAL		FINISH	
CuNiSi		TINNED	

DWN H. Ballmert 28NOV2012	TE Connectivity		
CHK B. Schnaubelt 30NOV2012			
APVD T. Klenner 30NOV2012			
PRODUCT SPEC 108-94366			
APPLICATION SPEC -	NAME MAG-MATE Slim Line Contact with Multispring		
WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2120743
Customer Drawing		SCALE 5:1	SHEET 1 OF 1
		REV A6	RESTRICTED TO -