




DO NOT SCALE

DIMENSIONS IN mm




METRIC

THIRD ANGLE


PROJECTION



SECTION A-A



SECTION B-B



SECTION C-C

NOTES:

- 1 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED)
- 2 REELED WITH PAPER.
- 3 CONFIGURATION OF CARRIER-STRIP OPTIONAL.
- 4 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED) AMP-O-MATOR APPLICATION.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5 OBSOLETE	PRE-TIN PLATED	PH.BRONZE	4	6-160831-8
	PRE-TIN PLATED	BRASS	4	6-160831-7
	TIN PLATED	PH.BRONZE	4	1-160831-2
	UNPLATED	BRASS	4	1-160831-1
5 OBSOLETE	TIN PLATED	BRASS	4	1-160831-0
	UNPLATED	NICKEL-SILVER		0-160831-9
	SILVERPLATED	PH.BRONZE		0-160831-8
	SILVERPLATED	BRASS		0-160831-7
5 OBSOLETE	UNPLATED	BRASS	2	0-160831-6
	UNPLATED	PH.BRONZE	2	0-160831-5
	TIN PLATED	PH.BRONZE		0-160831-4
	TIN PLATED	BRASS		0-160831-3
	UNPLATED	PH.BRONZE		0-160831-2
	UNPLATED	BRASS		0-160831-1
	FINISH	MATERIAL		PART NUMBER

WIRE RANGE :
1.0-2.5 mm?
INSULATION RANGE :
3.0-4.3mm DIA.

						CUSTOMER DRAWING		FOR REFERENCE ONLY WILL NOT BE UPDATED	
						THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION _____ .12 _____			
						 TE Connectivity			
						NAME			
M2		ECO-11-005294		RK		HMR		19APR11	
LTR.		REVISION RECORD		DR.		CHK.		DATE	
DR.: J.v.LIEMPT		CHK.: M.vDRIEL		APP.: M.v.DRIEL		DWG.No.		REV.LTR.	
DATE: 07 FEB 97		DATE: 18 FEB 02		DATE: 18 FEB 02		C - 160831		M2	
								SHEET 1 OF 1	