

MOS FET Relays


G3VM-201G1

Ultrasensitive MOS FET Relay in 200 V Load series for power savings, SOP Package.

- Trigger LED forward current of 1 mA (maximum) facilitates power saving designs and prolonged battery life.
- Continuous load current of 200 mA.
- RoHS Compliant

■ Application Examples

- Broadband systems and Measurement devices
- Security systems
- Industrial equipment
- Battery powered equipment and Amusement machines


NEW

Note: The actual product is marked differently from the image shown here.

■ List of Models


Contact form	Terminals	Load voltage (peak value) (See the note.)	Model	Number per stick	Number per tape
SPST-NO	Surface-mounting terminals	200 V	G3VM-201G1	100	---
			G3VM-201G1(TR)	---	2,500

Note: The AC peak and DC value are given for the load voltage.


■ Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-201G1





Note: The actual product is marked differently from the image shown here.



■ Terminal Arrangement/Internal Connections (Top View)


G3VM-201G1



Note: The actual product is marked differently from the image shown here.

■ Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-201G1



■ Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)


Item	Symbol	Rating	Unit	Measurement Conditions
Input	LED forward current	I_F	50	mA
	Repetitive peak LED forward current	I_{FP}	1	A
	LED forward current reduction rate	$\Delta I_F/^\circ\text{C}$	-0.5	mA/ $^\circ\text{C}$
	LED reverse voltage	V_R	5	V
	Connection temperature	T_J	125	$^\circ\text{C}$
Output	Load voltage (AC peak/DC)	V_{OFF}	200	V
	Continuous load current (AC peak/DC)	I_O	200	mA
	ON current reduction rate	$\Delta I_O/^\circ\text{C}$	-2.0	mA/ $^\circ\text{C}$
	Connection temperature	T_J	125	$^\circ\text{C}$
Dielectric strength between input and output (See note 1.)		V_{I-O}	1,500	V_{rms}
Operating temperature		T_a	-40 to +85	$^\circ\text{C}$
Storage temperature		T_{stg}	-55 to +100	$^\circ\text{C}$
Soldering temperature (10 s)		---	260	$^\circ\text{C}$

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■ Electrical Characteristics ($T_a = 25^\circ\text{C}$)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions
Input	LED forward voltage	V_F	1.0	1.15	1.3	V
	Reverse current	I_R	---	---	10	μA
	Capacity between terminals	C_T	---	30	---	pF
	Trigger LED forward current	I_{FT}	---	0.4	1	mA
Output	Maximum resistance with output ON	R_{ON}	---	5	8	Ω
	Current leakage when the relay is open	I_{LEAK}	---	1	1000	nA
	Capacity between terminals	C_{OFF}	---	90	---	pF
Capacity between I/O terminals		C_{I-O}	---	0.8	---	pF
Insulation resistance		R_{I-O}	1,000	---	---	$M\Omega$
Turn-ON time		t_{ON}	---	3	8	ms
Turn-OFF time		t_{OFF}	---	0.6	3	ms

Note: 2. Turn-ON and Turn-OFF Times




■ Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}	---	---	160	V
Operating LED forward current	I_F	---	2	25	mA
Continuous load current (AC peak/DC)	I_O	---	---	160	mA
Operating temperature	T_a	-20	---	65	$^\circ\text{C}$

■ Engineering Data


LED forward current vs.
Ambient temperature




Continuous load current vs.
Ambient temperature




LED forward current vs.
LED forward voltage




Continuous load current vs.
On-state voltage




On-state resistance vs.
Ambient temperature




Trigger LED forward current vs.
Ambient temperature




Turn ON, Turn OFF time vs.
LED forward current



Turn ON, Turn OFF time vs.
Ambient temperature



Current leakage vs.
Ambient temperature



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X302-E-1

12/10

Specifications subject to change without notice

Printed in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

G3VM-201G1