

Sonos

The latest sound in fire alarm technology

Fitted with the **TimeSaver Base®**, the Sonos is a unique multi-purpose alarm sounder optimised for fire applications.

Installer Benefits

Unique

Wire-to-base system uses the TimeSaver® design.

Quick & Safe

Simple 'First Fix' installation (no 'Second Fix' wiring).
Smooth flow cabling for faster termination.

Twist & Click

Quick connect / disconnect.
No locking screw required.

Easy Handling

Tone and volume setting can be preset or adjusted 'off-base'.

Performance Benefits

Alarm Tones

32 distinct tones.

Efficiency

Current consumption from
6 to 35 mA.

Audibility

Up to 110 dB at peak.

Synchronisation


Automatic synchronisation.

Compliance

EN54 3:2001.

Integrated beacon

Improved all-round visibility due to large lens.



Unique TimeSaver®
Wire-to-base



Traditional Terminal Block
Wire-to-terminal



Sounder Beacon

Sonos

A new standard in fire alarm sounders designed to fulfil requirements in a variety of applications.

Built in TimeSaver Base®

- Sounder locks into base. No wiring required to sounder head.
- Faster installation reduces commissioning time and overall costs.
- E-Z™ fit slots (for shallow base fixing).
- Timesaver system also on deep base option.

Weatherproof protection to IP65*


- Sonos can be used in all locations, both indoors and outdoors.

Combined sounder/beacon


- The full sounder head becomes a lens, thus providing greater spread of light.

*Applies to deep base option

TimeSaver Base® is a registered trademark of Apollo Fire Detectors.
E-Z™ Fit is a trademark of Apollo Fire Detectors



TimeSaver® Shallow Base



Deep Base

Colours:	Available in red and white
Audibility:	110dBA @ 1 metre (tone dependent)
Tones:	32
Voltage:	8-35V DC, 110-230V AC
Current:	6-35 mA (tone dependent)
IP Rating:	IP65*
Compliance:	EN54 3.2001 and BS5839 pt 1

Operation:	Continuous and synchronised
Frequency:	400-2850HZ
Operating Temp:	-25°C to 70°C
Construction:	Flame retardant polycarbonate
Cable entries:	2 glanded in deep base
Weight:	Sonos deep base 250g, Sonos shallow base 215g
Dimensions:	Sonos deep base: width 97.5mm, height 104.1mm Sonos shallow base: width 100mm, height 81.3mm

Sounder			Beacon			Sounder beacon		
8-35V dc	Red shallow base	18-980450	0.7J/24V:	Red/red shallow base	18-980473	24V dc:	Red/red shallow base	18-980452
	White shallow base	18-980475		Red/amber shallow base	18-980479		Red/amber shallow base	18-980477
	Red deep base	18-980451		Red/red deep base	18-980472		Red/red deep base	18-980453
	White deep base	18-980476		Red/Amber deep base	18-980471		Red/amber deep base	18-980478
	Red shallow base	18-980485		Red/red shallow base	18-980487			
110/230VAC:	White shallow base	18-980486	110/230VAC	Red/amber shallow base	18-980488			
	Red deep base	18-980480		Red/red deep base	18-980482			
	White deep base	18-980481		Red/amber deep base	18-980483			

While we make every effort to ensure the accuracy of the information printed, we disclaim any warranty or representation expressed or implied about its accuracy, completeness or appropriateness for a particular purpose. You assume full responsibility for using the information and you understand that neither Klaxon nor any of its employees or agents are responsible or liable for any claim, loss or damage resulting from its use.

Klaxon
The first name in signals

Klaxon Signals Ltd.
Wrigley Street, Oldham, Lancashire, OL4 1HW, UK.
Tel: +44 (0)161 287 5555 Fax: +44 (0)161 287 5511
E-mail: sales@klaxonsignals.com Web: www.klaxonsignals.com

**A
HALMA GROUP
COMPANY**