


|            |           |
|------------|-----------|
| O.P. (MM)  | P.T. (MM) |
| 15.5 ± 0.8 | 4.1 MAX.  |




O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



CIRCUIT: SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. RATING: 15A @125/250VAC UL, CUL, VDE APPROVED
4. OPERATING FORCE: 45± 20 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER
12. 2002/95/EC (ROHS) COMPLIANT



|     |        |                                |          |     |
|-----|--------|--------------------------------|----------|-----|
| G   | 20754  | 36.00 WAS 36.60                | 9/14/12  | EBP |
| F   | 15694  | EDIT LEVER DIMENSION           | 1/19/06  | PH  |
| E   | 15603  | CHANGES NOTED                  | 12/13/05 | PH  |
| D   | 15058  | CORRECTED DIMENSION AND NOTE 4 | 6/1/05   | JB  |
| C   | 14969  | CHANGED NOTE #4                | 6/1/05   | JB  |
| REV | PCR NO | DESCRIPTION                    | DATE     | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

**E-SWITCH®**

TITLE LS0851502F045S1A

SCALE 1.5:1

|      |           |
|------|-----------|
| DATE | 2/25/2005 |
|------|-----------|

|    |    |
|----|----|
| DR | AR |
|----|----|

DWG Q950005

REV  
G