




Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriété de ©BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.

BERG
ELECTRONICS

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of ©BERG ELECTRONICS Copyright BERG ELECTRONICS INC.

PRODUCT NUMBER
SEE TABLE



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecn no	dr	date		.XX $\pm .01$ / X $\pm .3$		projection		title	
U	REDRAWN	MSC	4/4/88	linear	.XXX $\pm .005$ / XX $\pm .13$				BERGSTIK® I HEADER	
V	V50357	WDF	6/13/95		.XXXX $\pm .0020$ / XXX $\pm .051$				.125/3.18cc SR STRAIGHT	
W	S60163	SLOW	15JUL96	angles	0° $\pm 2^\circ$				product family	BERGSTIK
X	S60211	A H	10/15/96	dr	BK CHUA	15JUL96	INCH/MM		size	dwg no
Y	T00045	JSR	2/25/2K	engr	JOYCE PEH	15JUL96	scale		A	65540
				chr	JOYCE PEH	15JUL96	4:1			
				appd	MK KAN	15JUL96				
sheet index	revision sheet	Y	W	W						
		1	2	3						

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriété de ©BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.

BERG
ELECTRONICS

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of ©BERG ELECTRONICS Copyright BERG ELECTRONICS INC.

PRODUCT NUMBER
SEE TABLE

	OVERPLATING	UNDERPLATING	PLASTIC COLOR
-1YY	30u"/0.76u GOLD	50u"/1.27u NICKEL	BLACK
-2YY	15u"/0.38u GOLD	50u"/1.27u NICKEL	CREAM
-3YY	50u"/1.27u GOLD	50u"/1.27u NICKEL	BROWN
-4YY	150u"/3.81u 93/7 TIN LEAD	-----	BLACK
-5YY	15u"/.38u GXT	50u"/1.27u NICKEL	DK BLUE
-6YY	30u"/.76u GXT	50u"/1.27u NICKEL	LT BLUE


OBSOLETE

OBSOLETE

PART NUMBER INFORMATION

PRODUCT BASE NO. XXXXX-YYY
 NUMBER OF POSITIONS NOTE 5
 TERMINAL PLATING

EXAMPLE: 65547-408 DENOTES AN 8 POSITION PART WITH 150u"/3.81u TIN PLATED TERMINALS. THE OVERALL PLASTIC LENGTH MAY BE 1.050/26.67 MAX. (NOTE 6). THE PLASTIC COLOR IS BLACK.



RECOMMENDED HOLE PATTERN

NOTES:

- MOLDING MATERIAL: 20% MIN GLASS FILLED NYLON, RATED PER UL-94V-0.
PIN MATERIAL: 3/4 HARD PHOS BRONZE.
- MEASURED AT DATUM -D- WITH PART IN RESTRAINED CONDITION.
- 5 LBS/ 2.3 KGS MINIMUM TERMINAL PUSH-OUT FORCE IN EITHER DIRECTION.
- BERG LOGO MAY APPEAR ON THIS SURFACE.
- MIN NO. OF POSITIONS = 1.
MAX NO. OF POSITIONS = 36.
- .060/1.52 MAX AS MOLDED (MOLDED AS 36 POS. ONLY).
.085/2.16 MAX WHEN BROKEN TO SPECIFIED LENGTHS.
- .020/0.51 MAX FLASH AROUND PIN IN THIS AREA.
- TWO SIDES OF LEAD-IN ON PINS NOT PLATED.
TYPICAL BOTH SIDES.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecn no	dr	date	linear	.XX ± .01 / X ± .3	projection	title		
v					.XXX ± .005 / XX ± .13		BERGSTIK® 1 HEADER		
w				angles	.XXX ± .0020 / XXX ± .051		.125/3.18cc SR STRAIGHT		
				dr	BK CHUA 15JUL.96	INCH/MM	product family	BERGSTIK	code
				enrg	JOYCE PEH 15JUL.96	scale	size	dwg no	sheet
				chr	JOYCE PEH 15JUL.96	1:1	A	65540	2 of
				appd	MK KAN 15JUL.96				
sheet index	revision	sheet	1						

All rights strictly reserved. Reproduction or issue to third parties in any form and/or by any means, electronic or mechanical, including photocopying, recording, or by any information storage and retrieval system, is prohibited without written authority from the proprietor.

Property of © BERG ELECTRONICS Copyright BERG ELECTRONICS INC.

		1		2												3	
PRODUCT	TOTAL PIN LENGTH		TAIL LENGTH		MATING LENGTH		AVAILABLE PLATING										
NUMBER	DIM A	DIM A	DIM B	DIM B	DIM C	DIM C	-1YY	-2YY	-3YY	-4YY	-5YY	-6YY					
65540-XXY	0.525	13.34	0.195	4.95	0.230	5.84	YES	YES	YES	YES	NO	NO					
65541-XXY	0.825	20.96	0.495	12.57	0.230	5.84	YES	YES	YES	YES	NO	NO					
65542-XXY	0.425	10.80	0.095	2.41	0.230	5.84	YES	YES	YES	YES	NO	NO					
65543-XXY	0.615	15.62	0.285	7.24	0.230	5.84	YES	YES	YES	YES	NO	NO					
65544-XXY	0.730	18.54	0.400	10.16	0.230	5.84	YES	YES	YES	YES	NO	NO					
65545-XXY	0.965	24.51	0.635	16.13	0.230	5.84	YES	YES	YES	YES	NO	NO					
65546-XXY	1.025	26.04	0.695	17.65	0.230	5.84	YES	YES	YES	YES	NO	NO					
65547-XXY	0.450	11.43	0.120	3.05	0.230	5.84	YES	YES	YES	YES	NO	NO					
65548-XXY	0.480	12.19	0.150	3.81	0.230	5.84	YES	YES	YES	YES	YES	NO					
65549-XXY	0.580	14.73	0.250	6.35	0.230	5.84	YES	YES	YES	YES	NO	NO					
65550-XXY	0.655	16.64	0.325	8.26	0.230	5.84	YES	YES	YES	YES	NO	NO					
65551-XXY							NOT AVAILABLE										
65552-XXY							NOT AVAILABLE										
65553-XXY	1.155	29.34	0.825	20.96	0.230	5.84	YES	YES	YES	YES	NO	NO					
65623-XXY	0.855	21.72	0.455	11.56	0.300	7.62	YES	YES	YES	YES	NO	NO					
65634-XXY	0.615	15.62	0.215	5.46	0.300	7.62	YES	YES	YES	YES	NO	NO					
65635-XXY	0.525	13.34	0.107	2.72	0.318	8.08	YES	YES	YES	YES	NO	NO					
65636-XXY	0.673	17.09	0.120	3.05	0.453	11.51	YES	YES	YES	YES	NO	NO					
65957-XXY	0.650	16.51	0.232	5.89	0.318	8.08	YES	YES	YES	YES	NO	NO					
65963-XXY	0.945	24.00	0.615	15.62	0.230	5.84	YES	YES	YES	YES	NO	NO					
66487-XXY							NOT AVAILABLE										
67899-XXY							NOT AVAILABLE										
68698-XXY							NOT AVAILABLE										
68699-XXY	0.861	21.87	0.461	11.71	0.300	7.62	YES	YES	YES	YES	NO	NO					
68700-XXY							NOT AVAILABLE										
68701-XXY							NOT AVAILABLE										

OBsolete

OBsolete

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS			
ltr	ecn no	dr	date	linear	XX ±.01/X ±.3		projection 	title BERGSTIK® 1 HEADER 1.25/3.18cc SR STRAIGHT			
v					.XXX ±.005/XX ±.13						
w					.XXX ±.0020/XXX ±.051						
				angles	0° ±2°		INCH/MM 	product family		code	
				dr	BK CHUA	15JUL96		size		dwg no	
				engr	JOYCE PEH	15JUL96		A		65540	
				chr	JOYCE PEH	15JUL96		scale		1:1	
				appd	MK KAN	15JUL96					
sheet index		revision sheet								cage code 22526	4