



PRODUCT NUMBER
65039-YXX(E)LF

DESIGN CODE
0 = STANDARD
2 = OPTIONAL RIB
SEE SHEET 2

PIN STYLE
SEE SHEET 2

INDICATES THE PRODUCT IS RoHS
COMPLIANT, SEE NOTE 6

65039-YXXLF OR 65039-YXXELF ARE
EXACTLY THE SAME PRODUCTS.
EXTENSION "E" JUST FOR OLD EUROPEAN
DESIGN AND MANUFACTURING SITE




NOTES:

1. MOLDING MATERIAL : MODIFIED POLYPHELYNENE
COLOR BLACK, UL 94 V0
2. LATCH MUST WITHSTAND 18N MIN PULL OUT FORCE
3. STANDARD PACKAGING IN POLYBAGS
4. TERMINALS MUST BE CRIMPED PROPERLY FOR
SATISFACTORY LATCHING :
 - FOR CRIMPING INSTRUCTIONS, SEE TA-75 AND TA-295
 - FOR TERMINAL APPLICATION SEE TA-531.PRODUCT SPECIFICATION: BUS-12-067.

5. THIS HOUSING IS INTENDED FOR USE WITH
MINI PV TERMINAL WITH 22-36 GAUGE WIRE

6. RoHS COMPLIANT PRODUCT SPECIFICATIONS :

- MEETS PACKAGING SPECS AS PER GS-14-920
- PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family BERCONN		
ltr	ecn no	dr	date	tolerances unless otherwise specified		 mm scale 5:1	title MINI LATCH SR		
BE	V07-0483	HTB	07.07.24	angles	.x ±0.3		POLARIZED HSG 2.54mm		
BF	F12-0064	LMU	12.06.08	linear	.xx ±0.13		dwg no		
BG	B-14321	LMU	13.03.21		.xxx ±0.05		sheet 1 of 2		
				dr	L.MULIN 12.06.08		size		
				engr	L.MULIN 12.06.08		65039		
				chr		type	CUSTOMER		
				appd	JCO 12.06.08		Drawing		
sheet index	revision sheet	BG	BF						
		1	2						

