



NOTES:

- 1. CONFORMS TO EIA--310-D SPECIFICATIONS FOR RACKS AND CABINETS.
- 2. THE BONDING CAGE NUT AND BONDING SCREW MUST BE USED TOGETHER TO ACHIEVE BONDING BETWEEN EQUIPMENT MOUNTING FLANGES AND CAGE NUT RAILS. DO NOT SUBSTITUTE THE BONDING CAGE NUT OR BONDING SCREW WITH ANY OTHERS.



COMPONENT DESCRIPTION	PART NUMBERS	
	CNB4K	CNBK
	QUANTITY	
BONDING CAGE NUT CAGE NUT RAIL THICKNESS TOLERANCE: 0.064 TO 0.105 in. [1.63mm TO .27 mm] GREEN	4	50
GREEN BONDING SCREW, 1/2 in. [12.7 mm] LONG COMBO HEAD UTILIZES, #2 PHILLIPS OR SLOTTED SCREWDRIVER OR 5/16 in. OR 8mm SOCKET DRIVE	4	50

03	11/11	JHNU	RGB	REVISED PANEL THICKNESS: 0.105 WAS 0.0105	N10966BD-C41747	RGB	RGB	PANDUIT CORP. TINLEY PARK, ILLINOIS BONDING CAGE NUT KIT (CNB4K, CNBK) CUSTOMER DRAWING			
02	9/11	JHNU	RGB	ADDED NOTE 2 REVISED COMPONENT DESCRIPTION	N10966BD-C41747	RGB	RGB				
01	7/08	JHNU	JMAR	REVISED SCREW VIEW AND DESCRIPTION							
00	4/08	JHNU	JMAR	RELEASED							
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	SCALE	N/A	DRAWING NO / CAD FILE	C41747_03