



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1


PANDUIT PART NO.	FLANGE THICKNESS	WEIGHT 10pcs lbs (g)
JP75HBC25RB - ---	0.125 - 0.25 (3.18 - 6.35)	1.43 (648)
JP75HBC50RB - ---	0.3125 - 0.50 (7.94 - 12.7)	
JP75HBC75RB - ---	0.5625 - 0.75 (14.29 - 19.05)	



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
2. HOOK MATERIAL: NYLON 6/6
ANGLE BRACKET MATERIAL: PRE-GALVANIZED STEEL
RIVET MATERIAL: ALUMINUM
CLAMP MATERIAL: SPRING STEEL
3. PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 3/4" (19.05) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 15 lbs.
4. PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
5. PRODUCT MARKINGS:
 cULus logo and statement:
 "SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."
 ULC logo and statement:
 "IN ACCORDANCE WITH CAN/ULC S-102.2-10 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=35."

OO	11/13/2012	DBLA	GGC	KLN	INITIAL RELEASE	GAECN00227
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE				
J-PRO J-HOOK WITH 360° HAMMER-ON BEAM CLAMP (JP75HBC__R-__)				
CUSTOMER DRAWING				
ITEM REVISION NAME				
12I031AI/00				
DATASET FILE NAME				
12I031AI_DC_C11008/00A				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		MATERIAL: SEE NOTE 2		
		THIRD ANGLE PROJECTION		
DRAWING NUMBER:		C11008		
DRAWN BY		DATE		SIZE
DBLA		11/13/2012		A
CHK	SCALE	SHT 1 OF 1		
KLN	NONE			

2

1