



Product number
SEE TABLE, SHEET 4




rev	ecn no	dr	date
A	S07-0058	CH	2007-02-22
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface -  ASME Y14.5		tolerance std ASME Y14.5 -		projection 		MM 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	C. H. TAN	2005-12-19	ANGULAR	LINEAR	0.X		±		size A4	Scale 3:1		
Eng	C. H. TAN	2005-12-19			0.XX		±					
Chr	C. H. TAN	2007-02-22			0.XXX		±					
Appr	JOEY NG	2007-02-22	0°	±°					ECN ***			
			Product family AirMax VS					Spec ref				
			title AirMax VS VERT RECPT ASSY PRESS-FIT, 120 POSITION, 24mm					dwg no 10064493			Rev A	
			catalog no -					CUSTOMER			sheet 1 of 4	



Copyright FCI.



ADJACENT HEADER WIDTHS	DIM A	DIM B
24MM/24MM	3.00	24.00
26MM/26MM	5.00	26.00
24MM/26MM	4.00	25.00



title AirMax VS VERT RECPT ASSY
PRESS-FIT, 120 POSITION, 24mm
catalog no -

dwg no 10064493

Rev. A

CUSTOMER sheet 2 of 4

REV F - 2006-04-17

PDM: Rev:A

STATUS: Released

4 Printed: Dec 01, 2010



Copyright FCI.

A

B

C


D

A

B

C

D



ADJACENT HEADER WIDTHS	DIM C	DIM D
24MM/24MM	3.00	24.00
26MM/26MM	5.00	26.00
24MM/26MM	4.00	25.00



title AirMax VS VERT RECPT ASSY
PRESS-FIT, 120 POSITION, 24mm
catalog no -

dwg no 10064493

Rev. A

CUSTOMER sheet 3 of 4

PART NUMBER	PRESS-FIT TAIL PLATING TYPE
10064493-101	TIN/LEAD OVER NICKEL
10064493-101LF	TIN OVER NICKEL (LEAD FREE)

NOTES:

1. CONNECTOR MATERIALS:
HOUSING & RETAINER: HIGH TEMP THERMOPLASTIC, NATURAL, UL94V-0
IMLA PLASTIC: HIGH TEMP THERMOPLASTIC, BLACK, UL94V-0
CONTACT: COPPER ALLOY

2. CONTACT PLATING:
SEPARABLE INTERFACE: PERFORMANCE-BASED PLATING, QUALIFIED TO MEET
THE REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-239, INCLUDING
TELCORDIA GR-1217-CORE (November 1995) CENTRAL OFFICE

PRESS-FIT TAILS: SEE TABLE

3. PRODUCT SPECIFICATION: GS-12-239

4. APPLICATION SPECIFICATION: GS-20-035

5. PRODUCT MARKING, (PART NUMBER & LOT CODE), ON THIS SURFACE


6. REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING
PCB LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES

7. POSITIONS F & L OF ODD NUMBERED COLUMNS AND POSITIONS G & M
OF EVEN NUMBERED COLUMNS CORRESPOND TO EARLY MATE HEADER PINS

8. THERE IS NO GROUND BUSSING WITHIN THE CONNECTOR SYSTEM

9. REFER TO CUSTOMER DRAWING 10045979 FOR INFORMATION ON PCB HOLE
DIAMETERS AND PLATING OPTIONS.

10. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.



11. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C
PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION,
INFRA-RED OR VAPOR PHASE REFLOW OVEN.

12. PACKAGING MEETS GS-14-920 LEAD FREE LABELING
SPECIFICATION.

FCI

Copyright FCI.

	title		AirMax VS VERT RECPT ASSY		dwg no	10064493		Rev A
			PRESS-FIT, 120 POSITION, 24mm					
	catalog no		-		CUSTOMER		sheet 4 of 4	