



REV.	DATE	ECR NO.	DESCRIPTION
NC	11/19/10	XXXXXX	INITIAL RELEASE



RECOMMENDED PCB HOLE PATTERN

1. DURABILITY: 100 CYCLES MIN.
2. TEMPERATURE RANGE: -40°C TO +80°C
3. FREQUENCY RANGE: DC - 6.0 GHz

5	COVER PLATE	BRASS	NEXCOTE	1
4	INSULATOR-REAR	PTFE	NATURAL	1
3	BODY	BRASS	GOLD	1
2	CONTACT PIN	BERYLLIUM COPPER	GOLD	1
1	INSULATOR	PTFE	NATURAL	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN M.ZHANG	11/19/10
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	C:/CONNEX/134100.DWG

Amphenol Connex

PART DESCRIPTION

QMA JACK, RIGHT ANGLE, PCB MOUNT

PART NO.

134100

DWG. NO. 134100.DWG

REV. NC

SIZE A

SCALE NA