









RECOMMENDED P.C.B. PATTERN LAYOUT
GENERAL TOLERANCE: ±0.05

NOTES:

1. MATERIAL:

HOUSING: LCP, GRAY, UL94V-0;
TERMINAL: COPPER ALLOY, THICKNESS: 0.15mm;
SHELL: STAINLESS STEEL, THICKNESS: 0.30mm.

2. PLATING:


TERMINAL: CONTACT AREA: GOLD FLASH (0.11 MICRON MIN.) OVER
MINIMUM 0.75 MICRON Pd/Ni.
SOLDER TAIL AREA: GOLD FLASH (0.05 MICRON MINIMUM).
UNDER PLATING: NICKEL 2.0 MICROMN MINIMUM.
SHELL: MATTE TIN 1.27 MICRON MINIMUM.
UNDER PLATING: NICKEL 1.27 MICRON MINIMUM.

3. TAIL COPLANARITY 0.08mm MAXIMUM.







4. PRODUCT SPECIFICATION: PS-47589-001.

5. PACKAGING SEPCIFICATION: PK-47589-001.

6. COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV 2000/53/EC.



REVISED	EC NO: SH2014-0260	2013/12/23	DRWN:XOZHANG	2013/12/23	CHKD:XOZHANG	2014/02/11	APPR:AYIN	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		TITLE		
													MM ONLY		1:1	METRIC					



RECOMMENDED P.C.B. PATTERN LAYOUT
GENERAL TOLERANCE: ±0.05

NOTES:

1. MATERIAL:

HOUSING: LCP, GRAY, UL94V-0;
TERMINAL: COPPER ALLOY, THICKNESS: 0.15mm;
SHELL: STAINLESS STEEL, THICKNESS: 0.30mm.

2. PLATING:


TERMINAL: CONTACT AREA: GOLD FLASH (0.11 MICRON MIN.) OVER
MINIMUM 0.75 MICRON Pd/Ni.
SOLDER TAIL AREA: GOLD FLASH (0.05 MICRON MINIMUM).
UNDER PLATING: NICKEL 2.0 MICROMN MINIMUM.
SHELL: MATTE TIN 1.27 MICRON MINIMUM.
UNDER PLATING: NICKEL 1.27 MICRON MINIMUM.

3. TAIL COPLANARITY 0.08mm MAXIMUM.

4. PRODUCT SPECIFICATION: PS-47589-001.

5. PACKAGING SEPCIFICATION: PK-47589-001.

6. COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV 2000/53/EC.



REVISED	EC NO: SH2014-0260	2013/12/23	DRWN:XOZHANG	2013/12/23	CHKD:XOZHANG	2014/02/11	APPR:AYIN	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		TITLE		
												MM ONLY		1:1	METRIC					