



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

.25 [6.3] DIA
THRU



NOTES:

1. BRACKETS [] DENOTES DIMENSIONS IN MILLIMETERS
2. CUSTOM PERMANENT MARKING AVAILABLE. CONSULT FACTORY

							TITLE						
							METAL TAGS – 1 HOLE						
05A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01031	CUSTOMER DRAWING						
04	5/05	JAMB	EJD	JJB	ADDED PART NO. MT350W38–C316	12679	ITEM REVISION NAME		N41063BS/05				
03	10/03	BRH	DPN	JJB	REMOVED PART NO. MT350W38 FROM TABLE	11168	DATASET FILE NAME		N41063BS_DC/05A				
02	5/02	JAMB	DPN	JJB	MATERIAL FOR PART NO. MT172W38–C WAS 302 SS STAP WAS "P302"	10040	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  –  THIRD ANGLE PROJECTION					MATERIAL:	
01	1/01	KMD	JAC	JAC	REMOVED MT 172W–38–C316 & MT350W38–C FROM TABLE . CAD FILE SPEC WAS NPC_S41063_00	09063						STAINLESS STEEL	
00	11/91	SM	JAC	LA	RELEASED	00679						DRAWING NUMBER:	
												N41063BS_DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		
							SAM	11-11-91	JAC	1:1	A		