








IC TO BE SEATED





FOOTPRINT

FOOTPRINT AS VIEWED LOOKING DOWN FROM TOP OF SOCKET



DATE	ECO NO	DESCRIPTION	BY
May 12 1993	CDN 93022		A.K
Oct 4 1993	DCN 93025	Revise	A.K
Sep 5 1994		Revise	A.K



RECOMMENDED IC REF)

Performance.

1. Insulation Resistance : 1000 MΩ min. at 500V.D.C
2. Dielectric Withstanding Voltage : 600 V.A.C (RMS)
3. Contact Resistance : 30 mΩ max. at 20 mV max.
4. Temperature Range : -40°C ~ +150°C

④	CONTACT- (2)	Be Cu	4	PLATING : Au
③	CONTACT- (1)	Be Cu	4	PLATING : Au
②	BASE-8P	PEI	1	COLOR : BLACK
①	COVER-8P	PEI	1	COLOR : BLACK
P.NO	PART DESCRIPTION	MATERIAL	QTY	NOTE
GENERAL TOLERANCES ±0.3 (±.012)				
UNIT mm (in.)	SCALE	ANGLE 3rd.	TITLE	
DRAWN	/	/	SOP 8P SOCKET	
CHECKED	/	/		
APPROVED	/	/		
DWG NO.				652B0082211



WELLS JAPAN LIMITED
ウエルズ・ジャパン株式会社