










RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)

- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE
- 3 CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- 4 PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- 5 DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.

ROW	E	J	J	T	T	J	N
	D	J	J	T	T	J	N
	C	J	J	T	T	J	N
	B	J	J	T	T	J	N
	A	J	J	T	T	J	N
1 2 3 4 5 6							
SIGNAL							
POSITION							

CODE LETTER	MATING POST LENGTH ±0.1	LEAD LENGTH (REF)
J	6.5	4.25
N	7.25	4.25
T	8	4.25



DETAIL Z
SCALE 20:1

10	5	11.88	30	5223022-1
C	B	A	NO OF SIGNAL POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG B.MCMMASTER	22NOV04	tyco Electronics	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm		CHK R.WERTZ	22NOV04		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		ASSEMBLY, PIN, SIGNAL, VERTICAL, 5 ROW, Z-PACK 2mm FB, PRESS FIT LEADS, RANDOM SEQUENCED		
MATERIAL		APPLICATION SPEC		RESTRICTED TO		
FINISH		WEIGHT		SCALE 4:1		
1 2 3		CUSTOMER DRAWING		SHEET 1 of 1 REV 0		