

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-R55511-A4

CATALOG LISTING
BZ-R55511-A4
PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE

5

REPLACES

RELEASE NO. PR-10454

CHECK

CHECK

REVISIONS

A C067209

J A P

3 MAY 90

B C0

73287-0

20 OCT 93

C C0

77588

K D R


29 MAR 94

D 206008

CSL

16 JUL 02

CHECK



NOTES




MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS

2

SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 7-12 OZ

DIFFERENTIAL FORCE — — 1/2-1 1/4 OZ

DIFFERENTIAL TRAVEL — — .001 MAX

OVERTRAVEL — — — .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L103

15A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VAC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

	DES. UNITS	TOL. mils	DES. UNITS	TOL. mils
NO PLACES	"	1/100	"	0.0100
ONE PLACE	"	0.0010	"	0.0010
TWO PLACES	"	0.0001	"	0.0001
THREE PLACES	"	0.00001	"	0.00001
ANGLES	"		"	

SI METRIC

US CUSTOMARY

DESIGN UNITS

WEIGHT .074 LB

RASTER

FO-52848-A

DRAWN

T M M 6 AUG 81

81 CHECK D12

CHECK

CHECK

RELEASE NO. PR-10454

REPLACES