





SHELL	A $\pm$ 0.38	B $\pm$ 0.12	C $\pm$ 0.10	D $\pm$ 0.25	E $\pm$ 0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.GX000
15	39.14	33.32	25.18	25.12	19.18	D15P24A.GX000
25	53.03	47.04	39.12	38.84	33.12	D25P24A.GX000
37	69.32	63.50	55.68	55.30	49.68	D37P24A.GX000

TIN LEAD PART NUMBER

SHELL	A $\pm$ 0.38	B $\pm$ 0.12	C $\pm$ 0.10	D $\pm$ 0.25	E $\pm$ 0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.GX00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.GX00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.GX00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.GX00LF

LEAD FREE PART NUMBER

Protection: 4 --> flash AU

 $6 \rightarrow 0.76 \mu \text{ AL}$

Protection: 4 --> flash AU


 $6 \rightarrow 0.76 \mu \text{ AU}$

GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C01-8646-0000

rev	ecr no	dr	date
C	—	JOU	1996/09/09
E	LS05-001	MPE	2005/03/11
F	LS05-0056	MPE	2005/06/27
G	LS06-0019	LGO	2006/02/07
H	LS06-0097	LGO	2006/07/29
J	110-0038	NG	2010-02-03
—	—	—	—

www.fciconnect.com				surface ISO 1302		tolerance std ISO 406 ISO 1101	projection 			
				TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	LELEON	1992/09/10	ANGULAR	LINEAR		0.X	±0.1	size	A3	Scale 2
Eng	PESSON	1992/09/10				0.XX	±0.1			
Chr	NIRMAL.G	2010-02-03	0.XX	±2°		0.XXX	±0.1	ECN	110-0038	
Appr	SUDHIR.V	2010-02-03	Product family			D-SUB		Spec ref	-	
MALE CONNECTOR DELTA D ST			title			dwg no			Rev.	
straight,t,solder type for			catalog no			-			CUSTOMER sheet 1 of 1	
										



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)

