


5x20mm
Fast-Acting



IEC 60127-2/SS 2

DIN 41 661

- **FaxBack Document # 202**

- **Glass tube**

Brass caps, nickel-plated

- **Approvals:**

VDE: File No. 45220/87867

SEMCO: File No. 8746155/9522109

cULus Recognized: File No. E 67006

- **Packaging:**

00: Bulk (1000 pcs. per Box)


02: Pack (10 pcs. per Pack)

40: Axial Leads/Bulk

43: Axial Leads/Tape & Reel
(1000 pcs. per Reel)



Series 193



Note: Contact WICKMANN for individual I-t curves

- **Limits for Pre-arcing Time**

Rated Current	150%	210%	275%	400%	1000%
32 ... 100mA	> 1h	< 30min	10 ... 500ms	3 ... 100ms	< 20ms
125mA ... 6.30A	> 1h	< 30min	50ms ... 2s	10 ... 300ms	< 20ms

Permissible continuous operating current is $\leq 100\%$ at ambient temperature of 23°C (73.4°F).

Rated Current / Rated Voltage	Amp Code	Breaking Capacity	Voltage Drop (max) ¹ $100\% \times I_{\text{Rated}}$ (mV)	Power Dissipation (max) ¹ $150\% \times I_{\text{Rated}}$ (W)	Melting Integral (max) $1000\% \times I_{\text{Rated}}$ (A ² s) 	Approvals		
						VDE	SEMCO	cULus
32mA / 250V	0032	L $\cong$ 35A at 250VAC $\cos \phi = 1.0$	10000	1.6	0.002			•
40mA / •	0040		8000	1.6	0.0032			•
50mA / •	0050		7000	1.6	0.005			•
63mA / •	0063		5000	1.6	0.0079			•
80mA / •	0080		4000	1.6	0.0032	•	•	•
100mA / •	0100		3500	1.6	0.007	•	•	•
125mA / •	0125		2000	1.6	0.014	•	•	•
160mA / •	0160		2000	1.6	0.024	•	•	•
200mA / •	0200		1700	1.6	0.018	•	•	•
250mA / •	0250		1400	1.6	0.032	•	•	•
315mA / •	0315		1300	1.6	0.062	•	•	•
400mA / •	0400		1200	1.6	0.13	•	•	•
500mA / •	0500		1000	1.6	0.23	•	•	•
630mA / •	0630		650	1.6	0.44	•	•	•
800mA / •	0800		240	1.6	1	•	•	•
1.00A / •	1100	L $\cong$ 40A ~ L $\cong$ 50A ~ L $\cong$ 63A ~	200	1.6	1.4	•	•	•
1.25A / •	1125		200	1.6	2.7	•	•	•
1.60A / •	1160		190	1.6	4.3	•	•	•
2.00A / •	1200		170	1.6	7.8	•	•	•
2.50A / •	1250		170	1.6	13	•	•	•
3.15A / •	1315		150	2.5	20	•	•	•
4.00A / •	1400		130	2.5	21	•	•	•
5.00A / •	1500		130	2.5	38	•	•	•
6.30A / •	1630		130	2.5	72	•	•	•

¹ values according to IEC 60127; WICKMANN values may be lower

- **Order Information**

Qty.	Order- Number	Series	Amp Code	Packaging
		1 9 3		0