

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.  
DIFFUSION RESTREINTE - AMP  
© COPYRIGHT 20 BY -

RELEASED FOR PUBLICATION  
LIBRE A LA DISPOSITION  
ALL RIGHTS RESERVED.  
Tous droits reserves.

20

PIECE A UTILISER AVEC:  
PORTE-MODULE 50 VOIES MOS ASSY REF:1379077-X  
CLIP MOS REF: 144969-X  
OUTIL DE DEMONTAGE REF TE:1308372-1

FOR USE WITH:  
50 POS. MOS CONNECTOR ASSY REF: 1379077-X  
MOS RECEPTACLE: 144969-X  
DISASSEMBLY TOOL TE REF: 1308372-1

|                                        |               |               |                                              |                     |           |
|----------------------------------------|---------------|---------------|----------------------------------------------|---------------------|-----------|
| MODULE 50 VOIES /<br>50 POS. CONNECTOR | 2             | 1             | PBT 20% FV                                   | BLEU / BLUE<br>X550 | 1379079-1 |
| SHUNT / CLIP                           | 1             | 8             | INOX DORURE SELECTIVE<br>0.1 à 0.3 micron AU |                     |           |
| DESIGNATION /<br>DESCRIPTION           | REP./<br>ITEM | QTE./<br>QTY. | MATIERE / MATERIAL                           | COULEUR /<br>COLOR  |           |

8.4 REF

0.85±0.1

1.9<sup>0</sup><sub>-0.1</sub>

12.7<sup>0</sup><sub>-0.1</sub>

14±0.1

REPERE ALVEOLE /  
CAVITY IDENTIFICATION

REPERE ALVEOLE /  
CAVITY IDENTIFICATION

REPERE ALVEOLE /  
CAVITY IDENTIFICATION

REPERE ALVEOLE /  
CAVITY IDENTIFICATION

DATE CODE DE L'ASSEMBLAGE  
(optionnel) /  
ASS'Y DATE CODE (OPTIONAL)

65.6 REF

62.3

2.54 REF

2.54 REF

3.6<sup>0</sup><sub>-0.3</sub>

17°

63.7

REPERE ALVEOLE /  
CAVITY IDENTIFICATION

CODE DATE DU MOULAGE  
/ DATE CODE

REPERE ALVEOLE /  
CAVITY IDENTIFICATION

25

18

12

6

1

AMP

LOGO P.S.A (OPTIONNEL / OPTIONAL)

UNIQUEMENT POUR LES ALVEOLES  
REP 1 A 25 (OPTIONNEL) /  
ONLY FOR CAVITIES  
ITEM 1 TO 25 (OPTIONAL)

25

18

12

6

1

AMP

COUPE / SECTION A-A  
ECHELLE / SCALE 10:1

6.7<sup>0</sup><sub>-0.1</sub>

(3.6)

18.5±0.3

2.7<sup>+0.1</sup><sub>0</sub>

1.2<sup>0</sup><sub>-0.1</sub>

16

8.5±0.5

RO.5<sup>0</sup><sub>-0.2</sub>

THIS DRAWING IS A CONTROLLED DOCUMENT.  
CE PLAN EST UN DOCUMENT CONTROLE PAR AMP INCORPORATED.  
IL EST SUSCEPTIBLE D'ETRE REVISE, CORRECTE LE SERVICE  
TECHNIQUE D'AMP DE FRANCE POUR ORIENTER LA DERNIERE REVISION.  
DIMENSIONS: - TOLERANCES, UNLESS  
OTHERWISE SPECIFIED  
TOLERANCES NON SPECIFIEES  
(S'ILY A DES DECIMALES): -

mm

MATERIAL/MATIERE - FINISH/FINITION -#5

VOIR TABLEAU

DWY/DESSINE 18AUG2014  
MADHUSUDHAN N  
CHK/VERIFIE 18AUG2014  
E.CHATELUS  
APVD/APPROUVE 18AUG2014  
Y.ROUILLARD  
PRODUCT SPEC  
SPEC. PRODUIT  
108-15188  
APPLICATION SPEC  
SPEC. APPLICATION

SIZE  
FORMA

WEIGHT  
MASSE APPROX. -

CUSTOMER DRAWING

NAME  
TITRE

MODULE 50 VOIES MOS DONT 8 SHUNTS INVERSE  
MOS 50 POS SOCKET HOUSING WITH 8SC REVERSED

SIZE  
FORMA

CAGE CODE  
-

DRAWING NO  
No. PLAN  
1379079

RESTRICTED TO  
RESERVE A

UNIQUEMENT  
POUR REFERENCE

SCALE  
ECHELLE 9:2

SHEET  
FEUILLE 1

OF  
DE 1

REV  
A

TE Connectivity

4805 (3/13)