


# DEE/U 104 Multipole Receptacles



Contact polarity A




Contact polarity Z




Keying codes (View from F)



All dimensions see note 1)



Solder (-x30/-x40)



PCB (-x39/-x49)

CONTACT CONFIGURATION	Contacts	Solder cup Ø	C	PIN Ø
104 A Z 051	2	1.86	-	-
104 A Z 040	3	1.86	-	-
104 A Z 037	4	1.18	-	-
104 A Z 087	4	0.79/2.48	19.4 18.9	0.50/1.60 0.70/1.07
104 A Z 053	5	1.18	-	-





Pin layout / PCB hole pattern for polarity A - View from F (3)

040





037

087

053



Polarity Z - View from F



All dimensions in mm

Rev. Pages

600539

1

1/3

Notes :

- 1) All tolerances resulting from connector assembly are typically  $\pm 0.3\text{mm}$
- 2) If receptacle is screwed directly into threaded hole, oversize thread by  $+0.05\text{mm}$

3) Recommended PCB hole dimensions may be adjusted to application

4) Please contact us


Part number example : DEE 104 A092-130

# DEE/U 104 Multipole Receptacles




Contact polarity A



Contact polarity Z



Keying codes (View from F)



All dimensions see note 1)

CONTACT CONFIGURATION	Contacts	Solder cup Ø	C	PIN Ø
104 A Z 065	6	0.79	19.4 19.1	0.50 0.63
104 A Z 054	7	0.79	-	-
104 A Z 066	8	0.79	19.4 -	0.50 -
104 A Z 055	9	0.79/1.18	-	-
104 A Z 056	11	0.79	19.4 19.1	0.50 0.63

Solder (-x30/-x40)


PCB (-x39/-x49)

Pin layout / PCB hole pattern for polarity A - View from F (3)


054

066


055



(4)






(4)



Polarity Z - View from F

(4)



All dimensions in mm

Rev. Pages

600539

1

2/3

Notes :

- 1) All tolerances resulting from connector assembly are typically  $\pm 0.3\text{mm}$
- 2) If receptacle is screwed directly into threaded hole, oversize thread by  $+0.05\text{mm}$

3) Recommended PCB hole dimensions may be adjusted to application

4) Please contact us

Part number example : DEE 104 A092-130


 [www.fischerconnectors.com](http://www.fischerconnectors.com)

# DEE/U 104 Multipole Receptacles



Contact polarity A





Contact polarity Z



Keying codes (View from F)



All dimensions see note 1)






Solder (-x30/-x40)

PCB (-x39/-x49)




CONTACT CONFIGURATION	Contacts	Solder cup Ø	C	PIN Ø
104 A 086	16	0.79	19.4	0.50
104 A 092	19	0.79	-	-
*104 A 124	27	-	-	-

\*Please contact us for additional information

Pin layout / PCB hole pattern for polarity A - View from F (3)



Polarity Z - View from F



All dimensions in mm

Rev. Pages

600539

1 3/3

Notes :

- 1) All tolerances resulting from connector assembly are typically  $\pm 0.3\text{mm}$
- 2) If receptacle is screwed directly into threaded hole, oversize thread by  $+0.05\text{mm}$

3) Recommended PCB hole dimensions may be adjusted to application

4) Please contact us

Part number example : DEE 104 A092-130