


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE		COLOR	WIRE STRIP LENGTH +1/32 -0 [+0,8 -0]	DIMENSIONS in. [mm]				MAX WIRE INSUL DIA	INSTALLATION TOOLS
	AWG	[mm ²]			L	P	ID-1	OD-1		
FSDX75-8	22-20	[0,50]	WHITE	15/32 [11,91]	0.53 [13,5]	0.32 [8,0]	0.04 [1,1]	0.05 [1,4]	0.12 [3,0]	CT-1002 CT-1003 CT-1123
FSDX76-8	18	[0,75]	GRAY	15/32 [11,91]	0.55 [14,0]	0.32 [8,0]	0.05 [1,3]	0.06 [1,6]	0.14 [3,4]	
FSDX77-8	--	[1,0]	RED	15/32 [11,91]	0.57 [14,5]	0.32 [8,0]	0.06 [1,5]	0.07 [1,8]	0.14 [3,4]	
FSDX78-8	16	[1,5]	BLACK	15/32 [11,91]	0.57 [14,5]	0.32 [8,0]	0.07 [1,8]	0.08 [2,1]	0.15 [3,8]	
FSDX84-12	6	[16,0]	BLUE	7/8 [22,2]	.91 [23,0]	0.47 [12,0]	0.24 [6,0]	0.25 [6,4]	0.37 [9,5]	CT-1004 CT-1104


* INSULATION COLOR CONFORMS TO DIN SPECIFICATION

NOTES:

- USED FOR:
 - STRAINED COPPER WIRE ONLY
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
- MATERIAL:
 - STAMPING: COPPER, TIN PLATED
 - HOUSING: POLYPROPYLENE, COLOR CODED
- SEE www.panduit.com FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



CERTIFIED
LR31212

								TITLE FERRULES WITH SLEEVES SINGLE WIRE DIN END SLEEVES CUSTOMER DRAWING					
								ITEM REVISION NAME N41752BA/03				PANDUIT	
								DATASET FILE NAME N41752BA_DC/03A					
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XX ± .XXX ± ANGLES ± THIRD ANGLE PROJECTION					
03	02.18.13	BDK	BCT	VMB	NOTE 2:B "POLYPROPELENE" WAS "PLASTIC" UPDATED DRAWING TO CURRENT STANDARDS EXPANDED WIRE RANGE ON FSDX75-8 FSDX77-8 REMOVED 18 GAGE ADDED CSA LOGO	A41752	MATERIAL: SEE NOTES DRAWING NUMBER: A41752						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JKD	DATE -	CHK SKB	SCALE N.T.S.	SHEET 1 OF 1		SIZE A