


Detailed Specifications & Technical Data

BELDEN
SENDING ALL THE RIGHT SIGNALS

ENGLISH MEASUREMENT VERSION

B9B811 Fiber - All Dielectric Cable - In/Outdoor Riser



For more
Information
please call

1-800-Belden1



General Description:

FiberExpress Single Jacket-All Dielectric Cable, 12-Fiber, OM1 OFNR, Loose Tube, Indoor & Outdoor Rated with UV Resistant Black Jacket, No grounding required. Suited for aerial lashing and underground conduit.

Physical Characteristics (Overall)

Fiber Type:	62.5 Micron (OM1)
Number of Fibers:	12
Buffer Tube Material:	Thermoplastic

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Strength Member

Strength Member Material:

Aramid Yarn, Fiberglass Epoxy Rod

Overall Cable

Overall Nominal Diameter:

0.510 in.

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +75°C
Installation Temperature Range:	-30°C To + 70°C
Operating Temperature Range:	-40°C To +70°C
Bulk Cable Weight:	108 lbs/1000 ft.
Min. Bend Radius/Minor Axis:	10.200 in.
Min. Bend Radius for Long Term Application:	5.100 in.
Max. Load for Installation:	600 lbs.
Max. Load for Long Term Application:	200 lbs.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/UL Specification:	OFNR
CEC/C/UL Specification:	OFN
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/22/2008
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MI Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Riser
C(UL) Flame Test:	FT4
CSA Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes
Suitability - Burial:	No

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

B9B811 Fiber - All Dielectric Cable - In/Outdoor Riser

Sunlight Resistance:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	No
Optical Characteristics (Overall)	
Maximum Attenuation @ 850nm:	3.5 dB/km
Maximum Attenuation @ 1300nm:	1.2 dB/km
Minimum Bandwidth @ 850nm:	200 MHz ² km
Minimum Bandwidth @ 1300nm:	600 MHz ² km
Maximum Gigabit Ethernet Length @ 850nm:	300 meters
Maximum Gigabit Ethernet Length @ 1300nm:	550 meters

Fiber Coding MLT EMEA:

Fiber/Tube No.	Color
1	Blue
2	Orange
3	Green
4	Brown
5	Slate
6	White
7	Red
8	Black
9	Yellow
10	Violet
11	Rose
12	Aqua

Related Documents:

[Loose Tube Single Jacket All Dielectric.pdf](#) - Loose Tube Single Jacket All Dielectric technical information.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
B9B811	1 FT	0.000	BLACK		SJAD 12F OM1 OFNR LT

Revision Number: 2 Revision Date: 02-06-2013

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) resulting from the use of the information and specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[B9B811](#)