

RESISTIVE LOAD					LAMP	INDUCTIVE
DC VOLTS		AC VOLTS			LOAD	LOAD
28	125	250	125	250	28 VDC 125 VAC	28 VDC 125 VAC

10A-125, 250, 277 VAC  
1/4HP-125VAC; 1/2HP-250, 277VAC
3A-125VAC "L" CODE L192 

- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
- 2 - CIRCUIT DESIGNATION, MICRO SWITCH CATALOG LISTING AND "MS" NUMBER MARKED ON SIDE OF SWITCH
- 3 - FURNISHED UNASSEMBLED
- 4 - FOR TERMINAL COVER SEE MICRO SWITCH CATALOG LISTING 5PA8
- 5 - KEYWAY SHOWN ON LEFT SIDE
- 6 - SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE OF TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS
- 7 - APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
- 8 - THESE SWITCHES ARE QUALIFIED UNDER MIL-S-3950
- 9 - FROM BOTTOM OF KEYWAY TO MAJOR DIA. OF 15/32 THREAD