






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC				
ltr	ecr no	dr	date	tolerances unless otherwise specified				INCH/MM 	title					
A	V12795	RDS	10/24/91	angles	linear	.XX±.01/.3			VERTICAL SHROUD					
B	V20224	MRC	3/2/92			.XXX±.005/.13			4 ROW W/O GUIDE PINS					
C	V23049	SAR	7/24/92	0'±2'		.XXXX±.0020/.05		scale 1:1						
D	V41077	GAH	7/6/94	dr	D.SHEAFFER	8/7/91				dwg no		sheet 1 of 2		size
E	V94441	JWS	12/30/99	enr	S.CLARK	10/24/91				50437		A3		
F	V05-0967	DAI	10/20/05	chr	S.CLARK	10/24/91								
G	M06-0283	MHT	7/27/06	appd	S.CLARK	10/24/91								
sheet	revision	G	G											
index	sheet	1	2											

form: A3


PDM: Rev:G

STATUS: Released


Printed: May 13, 2011

PRODUCT NUMBER

SEE NOTE 1



SECTION U-U



SECTION X-X

NOTES:

1. PRODUCT NUMBERING CODE:

50437-X YYX LF

LEAD FREE (OPTIONAL)

ALWAYS "X"

NO. OF POSITIONS SEE NOTE 2

ALWAYS "X"

BASE NUMBER

- ② THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6, 7, 8, 9,.....79, 80.

- ③ MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC.
FLAME RETARDANT PER UL94 V-0. COLOR: BLACK.

- ④ MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE.

- ⑤ LENGTH FORMULAS

$$\text{DIM A} = .100/2.54 \times \text{NO. OF COLUMNS} + .75/19.1$$

$$\text{DIM B} = .100/2.54 \times \text{NO. OF COLUMNS} + .450/11.43$$

$$\text{DIM C} = .100/2.54 \times \text{NO. OF COLUMNS} - .100/2.54$$

6. THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

7. THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE OVEN.

mat'l. code		surface		tolerance		projection		product family	
SEE NOTE 3		ISO 1302 ✓		ISO 406 ISO 1101		INCH/MM		HPC	
ltr	ec	no	dr	date	tolerances unless otherwise specified		scale 1:1	title	
G					angles	linear		VERTICAL SHROUD	
						.XX±.01/.3		4 ROW W/O GUIDE PINS	
					0'±2'	.XXX±.005/.13 .XXXX±.0020/.051		dwg no	
					dr	D.SHEAFFER	8/7/91	sheet 2 of 2 size	
					enr	S.CLARK	10/24/91	50437	
					chr	S.CLARK	10/24/91	A3	
					appd	S.CLARK	10/24/91	type	
sheet		revision						Product Customer Drawing	
index		sheet							

form: A3