




- △ HOUSING MATERIAL; UL94 V-0 RATED LCP, COLOR: NATURAL.
CONTACT MATERIAL; PHOS BRONZE
- BOARDLOCK MATERIAL; BRASS
- △2 CONTACT PLATING; 0.76 μm MIN GOLD IN MATING AREA
0.13 μm - 0.20 μm GOLD IN SOLDER AREA.
BOTH OVER 1.27 μm MIN NICKEL ON ENTIRE STOCK.
- △3 BOARDLOCK PLATING; 3.8 μm MIN BRIGHT TIN/LEAD ON ENTIRE STOCK
OVER 1.27 μm MIN NICKEL ON ENTIRE STOCK.
- △4 DATUMS ESTABLISHED BY CUSTOMER.
- △5 BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- △6 NO TRACES ON EXTERNAL BOARD LAYER IN THIS AREA.
- △7 BOARDLOCK PLATING; 3.8 μm MIN TIN ON ENTIRE STOCK
OVER 1.27 μm MIN NICKEL ON ENTIRE STOCK.
- △8 ROHS 2002/95/EC COMPLIANT.

8	7	2	4	5-1445339-1
	3	2	4	1445339-1
			NO OF POS.	PART NUMBER

SEE DRAWING NO. 11-2 FOR TYPICAL DOCUMENT FOR TYPICAL ELECTRONIC CONNECTION IT IS THE RESPONSIBILITY OF THE CUSTOMER TO OBTAIN THE LATEST REVISION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN D. FARJAN 28FEB2001 CHK - NAME -		 Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 1. PLC ±.01 2. PLC ±.013 3. PLC ±.013 4. PLC ±.013 4. PLC ±.013 ANGLES ±1		AMPMODU MICRO INTERCONNECT RECEPTACLE ASSEMBLY 4 POSITION	
MATERIAL 		FINISH SEE TABLE		SIZE A1	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C1445339	
				SCALE 12:1	
				SHEET 1 OF 1	
				REV B	