



© 1963 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

SYM	ZONE	DESCRIPTION	DATE	APPROVAL
N		REV PER ECO-09-021304	PY 10-09	DE



PHILIPS HEAD SCREWS FOR -1 AND 5--1 ONLY
SLOTTED FILLISTER HEAD SCREWS FOR -2, -3, -4, 5--3 AND 5--4




SECTION B-B
SCALE: 10-1

ASSY. NO	A	B	FINISH
202287-1 SUPERSEDED BY 5--1	1.001	1.509	ZINC PLATE PER ASTM-B-635 TYPE II CLASS 3 COLORLESS SUPPLEMENTARY CHROMATE
202287-2	1.001	1.509	OLIVE DRAB ZINC PLATE PER ASTM-B-635 CLASS 3 TYPE II
202287-3 SUPERSEDED BY 5--3	1.001	1.509	FINISH SAME AS -1
202287-4 SUPERSEDED BY 5--4	.595	1.103	FINISH SAME AS -1
5-202287-1	1.001	1.509	FINISH: PLATED ELECTROLESS NICKEL PER SAE-AMS-C-2607A .000400-.000800 THK (NO INTENTIONAL ADDITIONS OF LEAD OR CHROMIUM PER DFE STD 230-700)
5-202287-3	1.001	1.509	FINISH: PLATED ELECTROLESS NICKEL PER SAE-AMS-C-2607A .000400-.000800 THK (NO INTENTIONAL ADDITIONS OF LEAD OR CHROMIUM PER DFE STD 230-700)
5-202287-4	.595	1.103	FINISH: PLATED ELECTROLESS NICKEL PER SAE-AMS-C-2607A .000400-.000800 THK (NO INTENTIONAL ADDITIONS OF LEAD OR CHROMIUM PER DFE STD 230-700)

.125-.130
DIA. HOLES

.187 R.
TYP.



AMP INFO		QTY REQ	NOMENCLATURE OR DESCRIPTION	PART OR IDENTIFYING NO		
LOC	PRINT DIST					
DF	M	BO				
LIST OF MATERIALS OR PARTS LIST						
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON			SIGNATURE	DATE	AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
FRACTIONS	DECIMALS	ANGLES	DR	2-25-63	TRADEMARK	
± 1/64	± .015	± #	CHK	4-12-63	NAME	
MATERIAL			DSGN ENGR	3-1-63	RECEPTACLE ASSEMBLY, MODULE SERIES "G"	
HEAT TREAT			APPD	5/13/63	CODE IDENT NO	
FINISH			DSGN APPD		SIZE	NUMBER
SEE TABLE			OTHER APPD		202287	REV
					00779	N
					SCALE 2-1	WT
					CALC	ACTUAL
					SHEET	1 OF 1

CUSTOMER DRAWING