

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOCCE

DIST17

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1. MAXIMUM CASSETTE ASSEMBLY LOSS: 1.25dB.

2

WHITE MARKING ON MPO TO BE FACING TOWARD TOP OF CONNECTOR MODULE. WHITE MARK INDICATES FIBER 1 SIDE.

3

SEE TRACE LABEL DETAIL.

4. A COPY OF CASSETTE ASSEMBLY LOSS TEST DATA WILL BE PLACED INSIDE OR WITH THE UNIT PACKAGE. CASSETTES WILL BE TESTED AT 1300nm WAVELENGTH.

5. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

3

tycoXXXXXXXXXXXXXX

50/125umSTRAIGHT1938057-X

MADE IN USA

FIBER PATH - STRAIGHT

MPO L1 PORT POSITION NO	LC PORT POSITION NO
1	1B
2	1A
3	2B
4	2A
5	3B
6	3A
7	4B
8	4A
9	5B
10	5A
11	6B
12	6A

AQUA SECURE	AQUA SECURE	1-1938057-1
SLATE SECURE	SLATE SECURE	1-1938057-0
ROSE SECURE	ROSE SECURE	1938057-9
VIOLET SECURE	VIOLET SECURE	1938057-8
BROWN SECURE	BROWN SECURE	1938057-7
ORANGE SECURE	ORANGE SECURE	1938057-6
YELLOW SECURE	YELLOW SECURE	1938057-5
BLUE SECURE	BLUE SECURE	1938057-4
GREEN SECURE	GREEN SECURE	1938057-3
RED SECURE	RED SECURE	1938057-2
BLACK STANDARD	BEIGE STANDARD	1938057-1
MPO COUPLING BUSHING COLOR & TYPE	LC ADAPTER COLOR & TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH -

MATERIAL -

DWN D. FENNELL 08NOV06

CHK D. FENNELL 08NOV06

APVD D. FENNELL 08NOV06

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

tyco

Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME CASSETTE, 6 PORT, 50/125um,
MPO TO LC, STRAIGHT FIBER PATH

SIZE A2CAGE CODE 00779DRAWING NO 1938057RESTRICTED TO -

SCALE NTS

SHEET 2 of 2

REV A

1938057

AMP 3307-7 REV 31MAR2000