EVERLIGHT AMERICAS

DATASHEET

SMD ▪ B
EASV3015RGBA0



Features

- Package in 8mm tape on 7″ diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Full color type
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

Description

- The SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Device Selection Guide

Code	Chip Materials	Emitted Color	Resin Color
R6	AlGaInP	Brilliant Red	Water Clear
GH	InGaN	Brilliant Green	
BH	InGaN	Blue	

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Code	Rating	Unit
Reverse Voltage	V_R		5	V
Forward Current	I_F	R6	25	mA
		GH	25	
		BH	20	
Peak Forward Current (Duty 1/10 @1KHz)	I_{FP}	R6	60	mA
		GH	100	
		BH	100	
Power Dissipation	Pd	R6	60	mW
		GH	95	
		BH	75	
Electrostatic Discharge(HBM)	ESD	R6	2000	V
		GH	150	
		BH	150	
Operating Temperature	T_{opr}		-40 ~ +85	℃
Storage Temperature	Tstg		-40 ~ +90	℃
Soldering Temperature	Tsol		Reflow Soldering : 260 ℃ for 10 sec. Hand Soldering : 350 ℃ for 3 sec.	

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Electro-Optical Characteristics (Ta=25℃)

Parameter	Symbol	Code	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	Iv	R6	63	90	-----	mcd	
		GH	125	180			
		BH	32	50			
Viewing Angle	$2\theta_{1/2}$		-----	100	-----	Deg	
Peak Wavelength	λ p	R6	-----	632	------	nm	
		GH		518			
		BH		468			
Dominant Wavelength	λ d	R6	-----	624	-----	nm	I_F=20mA
		GH		525			
		BH		470			
Spectrum Radiation Bandwidth	△λ	R6	-----	20	-----	nm	
		GH		35			
		BH		25			
Forward Voltage	V_F	R6	-----	2.0	2.4	V	
		GH		3.3	3.9		
		BH		3.3	3.9		
Reverse Current	I_R	R6	-----	-----	10	μA	V_R=5V
		GH			50		
		BH			50		

Note:
1. Tolerance of Luminous Intensity: ±11%
2. Tolerance of Forward Voltage: ±0.1V

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Typical Electro-Optical Characteristics Curves
R6

Spectrum Distribution



Forward Current vs. Forward Voltage



Luminous Intensity vs. Ambient Temperature



Luminous Intensity vs Forward Current



Forward Current Derating Curve



Radiation Diagram Ta=25°C



Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Typical Electro-Optical Characteristics Curves
GH













Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Typical Electro-Optical Characteristics Curves
BH













Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Package Outline Dimensions



Top



Polarity



Side



Bottom

Recommend Sodering Pad



Suggested pad dimension is just for reference only.
Please modify the pad dimension based on individual need.

Note: Tolerances unless mentioned ±0.1mm. Unit = mm

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Moisture Resistant Packing Materials

Label Explanation

- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number

Reel Dimensions



Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm

Moisture Resistant Packaging



Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Precautions For Use

1. Over-current-proof
   Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage
   2.1 Do not open moisture proof bag before the products are ready to use.
   2.2 Before opening the package: The LEDs should be kept at 30℃ or less and 90%RH or less.
   2.3 After opening the package: The LED's floor life is 1 year under 30℃ or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
   2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment : 60±5℃ for 24 hours.

3. Soldering Condition
   3.1 Pb-free solder temperature profile



   3.2 Reflow soldering should not be done more than two times.
   3.3 When soldering, do not put stress on the LEDs during heating.
   3.4 After soldering, do not warp the circuit board.

4.Soldering Iron
   Each terminal is to go to the tip of soldering iron temperature less than 350℃ for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing
   Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5

DISCLAIMER

1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

Copyright © 2010, Everlight Americas Inc. All Rights Reserved. Release Date : 3-Jun-2017. Issue No: DSE-0012945 Rev.5