









NOTE
THROUGH-HOLES FOR MOUNTING LATCHES ALSO SHOULD BE PLATED.

TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

NO. OF CONTACTS: 40,60,68,80,100,120
CRITERION PIN



NO. OF CONTACTS: 30,34,50



MATERIAL

INSULATOR: NYLON RESIN GLASS REINFORCED (UL94V-0)

COLOR: BLACK

CONTACT: COPPER ALLOY

MOUNTING LATCH: PHOSPHOR BRONZE

SOLDER PLATED

CONTACT PLATING TABLE

[THICKNESS: μm]

CONTACT AREA	REMAINDER
GOLD 0.25 MIN	SOLDER
OVER NICKEL 3Z	OVER NICKEL

PRINTED CIRCUIT CONNECTOR

CAT. NO.

PHEC_P-S21

DRAWING NO.

JSC 90735

BURNDY
JAPAN, Ltd.

DESIGNED

DRAWN

CHECKED

APPROVED

DATE

M. Oba

4.8/1

J. Koyashiki

Mar. 8, 1990

SCALE

DIM IN

MATERIAL

REFERENCE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV

DATE

DESCRIPTION

CKD

REV





DATE

DESCRIPTION


CKD

REV

DATE




RECOMMENDED PC BOARD
THICKNESS: 1.6 ± 0.2
HOLE PATTERN (COMPONENT SIDE)
NO. OF CONTACTS: 40, 60, 80, 100, 120
N: NO. OF CONTACTS




NOTE
THROUGH-HOLES FOR MOUNTING LATCHES ALSO SHOULD BE PLATED.
CRITERION PIN

NO. OF CONTACTS: 40, 60, 80, 100, 120



NO. OF CONTACTS: 30, 34, 50



MATERIAL

INSULATOR: PBT RESIN GLASS REINFORCED (UL94V-0)

COLOR: BLACK

CONTACT: PHOSPHOR BRONZE

MOUNTING LATCH: PHOSPHOR BRONZE

SOLDER PLATED

CAT. NO.	NO. OF CONTACTS (MATING SIDE)	DIMENSIONS				
		A	B	C	D	E
PHEC30R-S21	15/ROW X 2 ROWS	34.55	31.75	27.26	21.26	17.78
PHEC34R-S21	17/ROW X 2 ROWS	37.09	34.29	29.8	23.8	20.32
PHEC40R-S21	20/ROW X 2 ROWS	40.9	38.1	33.61	27.61	24.13
PHEC50R-S21	25/ROW X 2 ROWS	47.25	44.45	39.96	33.96	30.48
PHEC60R-S21	30/ROW X 2 ROWS	53.6	50.8	46.31	40.31	36.83
PHEC68R-S21	34/ROW X 2 ROWS	58.68	55.88	51.39	45.39	41.91
PHEC80R-S21	40/ROW X 2 ROWS	66.3	63.5	59.01	53.01	49.53
PHEC100R-S21	50/ROW X 2 ROWS	79.0	76.2	71.71	65.71	62.23
PHEC120R-S21	60/ROW X 2 ROWS	91.7	88.9	84.41	78.41	74.93

TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

CONTACT PLATING TABLE

(THICKNESS: μm)

CONTACT AREA	REMAINDER
GOLD 0.25 MIN. OVER NICKEL 3.2	SOLDER OVER NICKEL




PRINTED CIRCUIT CONNECTOR

CAT. NO. PHEC...R-S21
DRAWING NO. JSC 90737
REV 4
BURNDY JAPAN Ltd.


DESIGNED
DRAWN M. Oba
CHECKED H. Oba
APPROVED H. Oba
DATE Mar. 8, 1990

SCALE
DIM. IN mm
MATERIAL


REV	DATE	DESCRIPTION	CKD
1	93-1-29	WRONG CONTACT DIM. CORRECTED.	
2	92-8-11	30,34,50,68 POSITIONS ADDED	No. 5.9
3	90-5-30	EC 7866	No. JK
4	90-4-20	EC 7837	No. JK
REFERENCE			




RECOMMENDED PC BOARD
THICKNESS: 1.6 ±0.2
HOLE PATTERN (COMPONENT SIDE)



NOTE
PROVIDE LAND SO THAT FLANGE PORTION OF THE CONNECTOR
CAN BE PUT.



TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3



PHEC60RT-S212

MATERIAL

INSULATOR: PPS RESIN GLASS REINFORCED (UL94V-0)
COLOR: BLACK

CONTACT: PHOSPHOR BRONZE

SCREW NUT: STAINLESS

NO. OF CONTACTS: 30/ROW X 2 ROWS (MATING SIDE)

CONTACT PLATING TABLE

CONTACT AREA		REMAINDER	
GOLD 0.25 MIN.		SOLDER	
OVER NICKEL 32		OVER NICKEL	




PRINTED CIRCUIT CONNECTOR
SURFACE MOUNT TYPE

REV	DATE	DESCRIPTION	CHKD.
4	8-14 '92	WRONG CONTACT DIM. CORRECTED	
3	1-8 '92	100 POSITIONS OF DELETED.	
2	6-8 '90	DIM. CHANGED.	
1	4-20 '90	EC7866	
		VARIATION ADDED.	


SCALE
DIM. IN
MATERIAL

DESIGNED
DRAWN
CHECKED
APPROVED
DATE

CAT. NO.
PHEC60RT-S21_
DRAWING NO.
JSC 90739
REV
4
BURNDY
JAPAN, Ltd.



NOTE
PROVIDE LAND SO THAT FLANGE PORTION OF THE CONNECTOR
CAN BE PUT.



RECOMMENDED PC BOARD
THICKNESS: 1.6 ±0.2
HOLE PATTERN (COMPONENT SIDE)

TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

MATERIAL

INSULATOR : PPS RESIN GLASS REINFORCED (UL94V-0)
COLOR : BLACK

CONTACT : PHOSPHOR BRONZE

SCREW NUT : STAINLESS

NO. OF CONTACTS : 50/ROW X 2 ROWS (MATING SIDE)

CONTACT PLATING TABLE

[THICKNESS : μm]

CONTACT AREA	REMAINDER
GOLD 0.25 MIN. OVER NICKEL 3Z	SOLDER OVER NICKEL

PRINTED CIRCUIT CONNECTOR
SURFACE MOUNT TYPE

CAT. NO.

PHEC100RT-S21

DRAWING NO.

JSC 91839

0

BURNDY
JAPAN, Ltd.

DESIGNED

DRAWN

CHECKED

APPROVED

DATE Aug. 11, 1992

SCALE

DIM. IN


MATERIAL

REV. DATE DESCRIPTION CKD.


REFERENCE

30AUC-10
4-0-17M

DRAWING NO.
JSC 90752




NO. OF CONTACTS: 30,34,50




NO. OF CONTACTS: 40,60,68,80,100

CRITERION PIN



1905 REF.
1905 REF.
1905 REF.



PHEC...R-S21-H

MOUNTING LATCH

MATERIAL

INSULATOR: PBT RESIN GLASS REINFORCED (UL94V-0)

COLOR: BLACK


CONTACT: PHOSPHOR BRONZE

MOUNTING LATCH: PHOSPHOR BRONZE

SOLDER PLATED

CAT. NO.	NO. OF CONTACTS (MATING SIDE)	DIMENSIONS				
		A	B	C	D	E
PHEC30R-S21-H	15/ROW X 2 ROWS	34.55	31.75	27.26	21.26	17.78
PHEC34R-S21-H	17/ROW X 2 ROWS	37.09	34.29	29.8	23.8	20.32
PHEC40R-S21-H	20/ROW X 2 ROWS	40.9	38.1	33.61	27.61	24.13
PHEC50R-S21-H	25/ROW X 2 ROWS	47.25	44.45	39.96	33.96	30.48
PHEC60R-S21-H	30/ROW X 2 ROWS	53.6	50.8	46.31	40.31	36.83
PHEC68R-S21-H	34/ROW X 2 ROWS	58.68	55.88	51.39	45.39	41.91
PHEC80R-S21-H	40/ROW X 2 ROWS	66.3	63.5	59.01	53.01	49.53
PHEC100R-S21-H	50/ROW X 2 ROWS	79.0	76.2	71.71	65.71	62.23

TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3



NOTE
THROUGH-HOLES FOR MOUNTING LATCHES ALSO SHOULD
BE PLATED.

NO. OF CONTACTS: 30,34,50

RECOMMENDED PC BOARD
THICKNESS: 1.6 ±0.2
HOLE PATTERN (COMPONENT SIDE)
NO. OF CONTACTS: 40,60,68,80,100

CONTACT AREA	REMAINDER
GOLD 0.25 MIN OVER NICKEL 3.2	SOLDER OVER NICKEL

CONTACT PLATING TABLE
(THICKNESS: μm)

REV	DATE	DESCRIPTION	CHKD.
5	'93 6-22	100 POSITIONS ADDED.	M.O.
4	'93 2-1	WRONG CONTACT DIM. CORRECTED.	90
3	'92 8-11	100,120 POSITIONS DELETED. 30,34,50,68 POSITIONS ADDED.	90
2	'90 5-30	DIM. CHANGED (36.61 → 33.61)	90
1	'90 5-14	EC 7866	HE



SCALE
DIM. IN mm
MATERIAL

DESIGNED
DRAWN
CHECKED
APPROVED
DATE
Mar. 24, 1990



PRINTED CIRCUIT CONNECTOR
HIGH STAND OFF TYPE
CAT. NO.
PHEC...R-S21-H
DRAWING NO.
JSC 90752
REV
5
BURNDY
JAPAN, Ltd.

RECOMMENDED PC BOARD
THICKNESS: 1.6 ±0.2
HOLE PATTERN (COMPONENT SIDE)

NO. OF CONTACTS: 40,60,68




NO. OF CONTACTS: 30,34,50




NOTE
THROUGH-HOLES FOR MOUNTING LATCHES ALSO SHOULD BE PLATED.

NO. OF CONTACTS: 40,60,68



NO. OF CONTACTS: 30,34,50



TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

CAT. NO.	NO. OF CONTACTS (MATING SIDE)	DIMENSIONS				
		A	B	C	D	E
PHEC30R-S21-H1	15/ROW X 2 ROWS	34.55	31.75	27.26	21.26	17.78
PHEC34R-S21-H1	17/ROW X 2 ROWS	37.09	34.29	29.8	23.8	20.32
PHEC40R-S21-H1	20/ROW X 2 ROWS	40.9	38.1	33.61	27.61	24.13
PHEC50R-S21-H1	25/ROW X 2 ROWS	47.25	44.45	39.96	33.96	30.48
PHEC60R-S21-H1	30/ROW X 2 ROWS	53.6	50.8	46.31	40.31	36.83
PHEC68R-S21-H1	34/ROW X 2 ROWS	58.68	55.88	51.39	45.39	41.91

MATERIAL

INSULATOR: PBT RESIN GLASS REINFORCED (UL94V-0)

COLOR: BLACK

CONTACT: PHOSPHOR BRONZE

MOUNTING LATCH: PHOSPHOR BRONZE

SOLDER PLATED

CONTACT PLATING TABLE

[THICKNESS: μm]

CONTACT AREA	REMAINDER
GOLD 0.25 MIN. OVER NICKEL 3.2	SOLDER OVER NICKEL

PRINTED CIRCUIT CONNECTOR
HIGH STAND OFF TYPE
CAT. NO.

PHEC_R-S21-H1

DRAWING NO. JSC 91840

REV 1

BURNDY JAPAN, Ltd.

DESIGNED
DRAWN *M. Oba*
CHECKED A.matsuo
APPROVED *S. Ito*
DATE Aug. 17, 1992

SCALE
DIM IN mm
MATERIAL

REV	DATE	DESCRIPTION	CKD
1	93	WRONG CONTACT DIM. CORRECTED.	
2	93		
3	93		

