

9808	9101	5650	8679
9808-0-15-XX-16-XX-04-0 Press-fit in .067 mounting hole	9101-0-15-XX-16-XX-10-0 Press-fit in .067 mounting hole	5650-0-19-XX-16-XX-10-0 Press-fit in .067 mounting hole	8679-0-15-XX-16-XX-10-0 Solder mount in .071 min. mounting hole

8827	6021	1873	
8827-0-15-XX-16-XX-04-0 Press-fit in .061 mounting hole	6021-0-15-XX-16-XX-10-0 Solder mount in .062 min. mounting hole	1873-0-15-XX-16-XX-04-0 Press-fit in .066 mounting hole	

--	--	--	--

SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 15 - XX - 16 - XX - XX - 0 BASIC PART # → SPECIFY SHELL FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL ◇ 15 10μ" GOLD OVER NICKEL ◇ SPECIFY CONTACT FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL ◇ 27 30μ" GOLD OVER NICKEL ◇ CONTACT #16 CONTACT (DATA ON PAGE 221) RoHS 2002/95/EC
--	---