

Fourth Quarter 2010



Focus Product Selector Guide

Featuring:

8-, 16- and 32-bit PIC® Microcontrollers

dsPIC® Digital Signal Controllers

Analog & Interface Products

Serial EEPROMs, Serial SRAMs, SST NOR Flash Memory

Wireless and RF Products



Training



Collateral



Development



Support



Design



Availability

MICROCHIP

*A Partner in **Your** Success*

Microchip: A Partner in Your Success

Microchip is a leading provider of microcontroller and analog semiconductors, providing low-risk product development, lower total system cost and faster time to market for thousands of diverse customer applications worldwide. Offering outstanding technical support along with dependable delivery and quality, Microchip serves over 63,000 customers in more than 65 countries who are designing high-volume embedded control applications in the consumer, automotive, office-automation, communications and industrial-control markets worldwide.

8-bit PIC® Microcontrollers

Based on a powerful RISC core, the PIC microcontroller architecture provides users with an easy migration path from 6 to 100 pins among all families, with little or no code change required. Advanced features include sophisticated timing peripherals, integrated analog-to-digital converters and communications peripherals (Ethernet/I²C™/SPI/USB/CAN ports and LIN USARTs). For more information visit: www.microchip.com/8bit

16-bit PIC® Microcontrollers

The 16-bit PIC24 Family is comprised of two sub-families. The PIC24F offers a cost-effective low power step up in performance, memory and peripherals for many applications that are pushing the envelope of 8-bit microcontroller capabilities. For more demanding applications, the PIC24H offers 40 MIPS performance, more memory and additional peripherals, such as CAN communication modules. For more information visit: www.microchip.com/16bit

32-bit PIC® Microcontrollers

The PIC32 family adds more performance and more memory while maintaining pin, peripheral and software compatibility with Microchip's 16-bit MCU/DSC families. The PIC32 family operates at up to 80 MHz and offers ample code and data space capabilities with up to 512 KB Flash and 128 KB RAM. For more information visit: www.microchip.com/32bit

dsPIC® Digital Signal Controllers

The dsPIC family of Digital Signal Controllers (DSCs) features a fully implemented digital signal processor (DSP) engine, with up to 40 MIPS non-pipelined performance, C compiler friendly design, and a familiar microcontroller architecture and design environment. The dsPIC 16-bit Flash DSCs provide the industry's highest performance, and have features supporting motor control, digital power conversion, speech and audio, intelligent sensing and general purpose embedded control applications. For more information visit: www.microchip.com/dsPIC

Analog and Interface Products

Microchip's integrated analog technology, peripherals and features are engineered to meet today's demanding design requirements. Our broad spectrum of analog products addresses

thermal management, power management, battery management, mixed-signal, linear, interface and safety & security solutions. Our broad portfolio of stand-alone analog and interface devices offers highly integrated solutions that combine various analog functions in space-saving packages and support a variety of bus interfaces. Many of these devices support functionality that enhances the analog features currently available on PIC® microcontrollers. For more information visit: www.microchip.com/analog

RF Front End Products

Microchip's selection of RF Front End devices enhance the performance and operating range of wireless products at 2.4 and 5 GHz. SST Power amplifier products provide high linear output power as required for 802.11 (WiFi®) and 802.15.4 (ZigBee®) standards with industry leading efficiency and reliability. Our selection of integrated Front End Modules (FEM), combines the function of power amplifier with switches, Low Noise Amplifier (LNA) and filters into a single space saving package. The FEM reduces board complexity and sizes. For more information visit:

www.microchip.com/analog

Wireless Products

Microchip offers radio-frequency products for adding wireless connectivity to embedded PIC microcontroller and dsPIC DSC-based designs for the following technologies: IEEE 802.15.4/ZigBee, Sub-GHz RF and IEEE 802.11/Wi-Fi. For more information visit:

www.microchip.com/wireless

Memory Products

Microchip's broad portfolio of memory devices include Serial EEPROM, Serial SRAM, Serial Flash and Parallel Flash Devices. Our innovative, low-power designs and extensive testing have ensured industry leading robustness and endurance along with best-in-class quality at low costs. For more information visit:

www.microchip.com/memory

Real-Time Clocks

Microchip offers a family of highly integrated, low cost Real Time Clock/Calendar devices with battery backup capability, digital trimming along with onboard EEPROM and SRAM memory. For more information visit: www.microchip.com/clock

Table of Contents

8-bit PIC Microcontrollers	3
16-bit PIC Microcontrollers (PIC24F).....	9
16-bit PIC Microcontrollers (PIC24H)	12
32-bit PIC Microcontrollers	13
dsPIC30F DSC Families	14
dsPIC33 DSC General Purpose Family.....	15
dsPIC33 DSC Motor Control and Power Conversion Family.....	16
dsPIC33 DSC SMPS and Digital Power Conversion Family.....	17
Analog and Interface Products	
Thermal Management	18
Power Management	18

Linear	20
Mixed Signal.....	20
Interface	21
Safety & Security	21
Motor Drivers	22
RF Products	22
Serial Memory Products.....	23
Real Time Clock/Calendar (RTCC).....	23
SST NOR Flash Memory	24
Wireless Products	25
Terms and Definitions	25
Packaging.....	26

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	Pins		Core	Memory				Voltage Range	Operating Speed		LCD Segments	mTouch™ Channels	Analog Sensing & Measurement					Digital				Communication					Monitors		Timer 1 Gate	5 ku Pricing†	Packages (Designator)	Special Features			
		Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)		Data EE (B)	Maximum Speed			Internal Oscillator	Charge Time Measurement Unit	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI	Ethernet (MAC/PHY)	FS-USB					ECAN	BOR/PBOR	PLVD
6-Pin	PIC10F200	R	6	4	BL	0.375 KB 0.25 Kw	–	–	16	–	2V-5.5V	4 MHz	4 MHz	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.30	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor
	PIC10F202	R	6	4	BL	0.75 KB 0.50 Kw	–	–	24	–	2V-5.5V	4 MHz	4 MHz	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.33	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor
	PIC10F204	R	6	4	BL	0.375 KB 0.25 Kw	–	–	16	–	2V-5.5V	4 MHz	4 MHz	0	1	–	–	–	1	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.33	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor
	PIC10F206	R	6	4	BL	0.75 KB 0.50 Kw	–	–	24	–	2V-5.5V	4 MHz	4 MHz	0	1	–	–	–	1	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.36	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor
	PIC10F220	R	6	4	BL	0.375 KB 0.25 Kw	–	–	16	–	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	2	–	2	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.36	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor
	PIC10F222	R	6	4	BL	0.75 KB 0.50 Kw	–	–	23	–	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	2	–	2	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.39	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	Smallest form-factor
	PIC10F320	NR	6	4	MR	4375 KB 0.25 Kw	✓	✓	32	–	1.8V-5.5V	16 MHz	16 MHz	0	3	–	3	–	0	–	–	2	1	–	–	–	–	–	–	–	SW0	–	–	\$0.39	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	CLC, CWG, DDS, Temp*
	PIC10F322	NR	6	4	MR	0.875 KB 0.50 Kw	✓	✓	64	–	1.8V-5.5V	16 MHz	16 MHz	0	3	–	3	–	0	–	–	2	1	–	–	–	–	–	–	–	SW0	–	–	\$0.42	PDIP (P), 2x3 DFN (MC), SOT-23 (OT)	CLC, CWG, DDS, Temp*
8-Pin	PIC12F508	R	8	6	BL	0.75 KB 0.50 Kw	–	–	25	–	2V-5.5V	4 MHz	4 MHz	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.41	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	–
	PIC12F509	R	8	6	BL	1.5 KB 1 Kw	–	–	41	–	2V-5.5V	4 MHz	4 MHz	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.45	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	–
	PIC12F510	R	8	6	BL	1.5 KB 1 Kw	–	–	38	–	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	3	–	3	–	1	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.49	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	–
	PIC12F519	R	8	6	BL	1.5 KB 1 Kw	–	–	41	64	2V-5.5V	8 MHz	4 MHz, 8 MHz	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.49	PDIP (P), SOIC (SN), MSOP (MS), 2x3 DFN (MC)	Lowest cost Data EE
	PIC12F609	R	8	6	MR	1.75 KB 1 Kw	–	–	64	–	2V-15V	20 MHz	4 MHz, 8 MHz	0	–	–	–	–	1	–	–	1	1	–	–	–	–	–	–	BOR	–	–	✓	\$0.52	PDIP (P), SOIC (SN), MSOP (MS), 4x4 DFN (MD), 3x3 DFN (MF)	–
	PIC12F615	R	8	6	MR	1.75 KB 1 Kw	–	–	64	–	2V-15V	20 MHz	4 MHz, 8 MHz	0	4	–	4	–	1	–	1	2	1	–	–	–	–	–	–	BOR	SW0	–	✓	\$0.55	PDIP (P), SOIC (SN), MSOP (MS), 4x4 DFN (MD), 3x3 DFN (MF)	–
	PIC12F617	R	8	6	MR	3.5 KB 2 Kw	✓	✓	128	–	2V-5.5V	20 MHz	4 MHz, 8 MHz	0	4	–	4	–	1	–	1	2	1	–	–	–	–	–	–	BOR	SW0	–	✓	\$0.59	PDIP (P), SOIC (SN), MSOP (MS), 3x3 DFN (MF)	–
	PIC12F629	R	8	6	MR	1.75 KB 1 Kw	–	–	64	128	2V-5.5V	20 MHz	4 MHz	0	–	–	–	–	1	–	–	1	1	–	–	–	–	–	–	BOR	–	–	✓	\$0.70	PDIP (P), SOIC (SN), 4x4 DFN (MD), 6x5 DFN (MF)	–
	PIC12F1822	 R	8	6	EMR	3.5 KB 2 Kw	✓	✓	128	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	4	–	4	–	1	–	1	2	1	–	1	1	–	–	–	BOR	SW0	–	✓	\$0.73	PDIP (P), SOIC (SN), 3x3 DFN (MF)	XLP, Temp*
	PIC12F675	R	8	6	MR	1.75 KB 1 Kw	–	–	64	128	2V-5.5V	20 MHz	4 MHz	0	3	–	3	–	1	–	–	1	1	–	–	–	–	–	–	BOR	–	–	✓	\$0.77	PDIP (P), SOIC (SN), 4x4 DFN (MD), 6x5 DFN (MF)	–
	PIC12F635	R	8	6	MR	1.75 KB 1 Kw	–	–	64	128	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	–	–	–	–	1	–	–	1	1	–	–	–	–	–	–	BOR	✓	–	✓	\$0.84	PDIP (P), SOIC (SN), 4x4 DFN (MD)	KeeLoq®
	PIC12F683	R	8	6	MR	3.5 KB 2 Kw	–	–	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	3	–	3	–	1	1	–	2	1	–	–	–	–	–	–	PBOR	–	–	✓	\$0.91	PDIP (P), SOIC (SN), 4x4 DFN (MD)	–
	PIC12F752	NR	8	6	MR	1.75 KB 1 Kw	–	–	64	–	2V-5.5V	20 MHz	4 MHz, 8 MHz	0	4	–	4	–	2	1	–	3	1	–	–	–	–	–	–	BOR	SW0	–	✓	Call for Pricing	PDIP (P), SOIC (SN), 3x3 DFN (MF)	CWG
14-Pin	PIC16F505	R	14	12	BL	1.5 KB 1 Kw	–	–	72	–	2V-5.5V	20 MHz	4 MHz	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.48	PDIP (P), SOIC (SL), TSSOP (ST), 3x3 QFN (MG)	–
	PIC16F506	R	14	12	BL	1.5 KB 1 Kw	–	–	67	–	2V-5.5V	20 MHz	4/8 MHz	0	4	–	4	–	2	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.52	PDIP (P), SOIC (SL), TSSOP (ST), 3x3 QFN (MG)	–
	PIC16F526	R	14	12	BL	1.5 KB 1 Kw	–	–	67	64	2V-5.5V	20 MHz	4/8 MHz	0	4	–	4	–	2	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.55	PDIP (P), SOIC (SL), TSSOP (ST), 3x3 QFN (MG)	Lowest cost Data EE
	PIC16F610	R	14	12	MR	1.75 KB 1 Kw	–	–	64	–	2V-15V	20 MHz	4/8 MHz	0	–	–	–	–	2	–	–	1	1	–	–	–	–	–	–	BOR	–	✓	✓	\$0.59	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	–
	PIC16F616	R	14	12	MR	3.5 KB 2 Kw	–	–	128	–	2V-15V	20 MHz	4/8 MHz	0	8	–	8	–	2	–	1	2	1	–	–	–	–	–	–	BOR	SW0	✓	✓	\$0.69	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	–
	PIC16F1823	 R	14	12	EMR	3.5 KB 2 Kw	✓	✓	128	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	8	–	8	–	2	–	1	2	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$0.78	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	XLP, Temp*
	PIC16F1824	 R	14	12	EMR	7 KB 4 Kw	✓	✓	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	8	–	8	–	2	2	2	4	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$0.84	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	DSM, XLP, Temp*
	PIC16F630	R	14	12	MR	1.75 KB 1 Kw	–	–	64	128	2V-5.5V	20 MHz	4 MHz	0	–	–	–	–	1	–	–	1	1	–	–	–	–	–	–	BOR	–	–	✓	\$0.91	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	–
	PIC16F636	R	14	12	MR	3.5 KB 2 Kw	–	–	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	–	–	–	–	2	–	–	1	1	–	–	–	–	–	–	BOR	–	–	✓	\$0.92	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	KeeLoq®
PIC16F1825	 NR	14	12	EMR	14 KB 8 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	8	–	8	–	2	2	2	4	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$0.92	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	DSM, XLP, Temp*	

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

*Reference Application Note AN1333 for temperature indicator implementation.

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	Pins		Core	Memory				Voltage Range	Operating Speed		LCD Segments	mTouch™ Channels	Analog Sensing & Measurement					Digital				Communication					ECAN	Monitors			Timer 1 Gate	5 ku Pricing†	Packages (Designator)	Special Features			
		Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)		Data EE (B)	Maximum Speed			Internal Oscillator	Charge Time Measurement Unit	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI		Ethernet (MACPHY)	FSUSB	BOR/BPDR					PLVD	SR-Latch	
14-Pin (Cont.)	PIC16F676	R	14	12	MR	1.75 KB 1 Kw	–	–	64	128	2V-5.5V	20 MHz	4 MHz	0	8	–	–	8	–	1	–	–	1	1	–	–	–	–	–	–	BOR	–	–	✓	\$0.98	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	–	14-Pin (Cont.)
	PIC16F684	R	14	12	MR	3.5 KB 2 Kw	–	–	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	8	–	–	8	–	2	–	1	2	1	–	–	–	–	–	–	BOR	–	–	✓	\$0.98	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	–	
	PIC16F688	R	14	12	MR	7 KB 4 Kw	✓	–	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	8	–	–	8	–	2	–	–	1	1	–	1	–	–	–	–	BOR	–	–	✓	\$1.04	PDIP (P), SOIC (SL), TSSOP (ST), 4x4 QFN (ML)	–	
	PIC16F54	R	18	12	BL	0.75 KB 0.50 Kw	–	–	25	–	2V-5.5V	20 MHz	0	0	–	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.39	PDIP (P), SOIC (SO), SSOP (SS)	–	
18-Pin	PIC16F716	R	18	13	MR	3.5 KB 2 Kw	–	–	128	–	2V-5.5V	20 MHz	0	0	–	–	–	4	–	0	–	1	2	1	–	–	–	–	–	–	BOR	–	–	–	\$0.77	PDIP (P), SOIC (SO), SSOP (SS)	–	18-Pin
	PIC16F1826	R	18	16	EMR	3.5 KB 2 Kw	✓	✓	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	12	–	–	12	–	2	–	1	2	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$0.97	PDIP (P), SOIC (SO), SSOP (SS), QFN (ML)	DSM, XLP, Temp*	
	PIC16F1827	R	18	16	EMR	7 KB 4 Kw	✓	✓	384	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	12	–	–	12	–	2	2	2	4	1	–	1	2	2	–	–	BOR	SW0	✓	✓	\$1.04	PDIP (P), SOIC (SO), SSOP (SS), QFN (ML)	DSM, XLP, Temp*	
	PIC16F627A	R	18	16	MR	1.75 KB 1 Kw	–	–	224	128	2V-5.5V	20 MHz	4 MHz, 48 kHz	0	–	–	–	–	2	1	–	2	1	1	–	–	–	–	–	BOR	–	–	–	\$1.30	PDIP (P), SOIC (SO), SSOP (SS), QFN (ML)	–		
	PIC16F628A	R	18	16	MR	3.5 KB 2 Kw	–	–	224	128	2V-5.5V	20 MHz	4 MHz, 48 kHz	0	–	–	–	–	2	1	–	2	1	1	–	–	–	–	–	BOR	–	–	–	\$1.47	PDIP (P), SOIC (SO), SSOP (SS), QFN (ML)	–		
	PIC16F648A	R	18	16	MR	7 KB 4 Kw	–	–	256	256	2V-5.5V	20 MHz	4 MHz, 48 kHz	0	–	–	–	–	2	1	–	2	1	1	–	–	–	–	–	BOR	–	–	–	\$1.67	PDIP (P), SOIC (SO), SSOP (SS), QFN (ML)	–		
20-Pin	PIC16F720	R	20	18	MR	3.5 KB 2 Kw	✓	✓	128	–	1.8V-5.5V	16 MHz	16 MHz, 500 kHz	0	12	–	12	–	–	0	1	–	2	1	1	–	1	1	–	–	BOR	SW0	–	✓	\$0.77	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	XLP, Temp*	20-Pin
	PIC16F721	R	20	18	MR	7 KB 4 Kw	✓	✓	256	–	1.8V-5.5V	16 MHz	16 MHz, 500 kHz	0	12	–	12	–	–	0	1	–	2	1	1	–	1	1	–	–	BOR	SW0	–	✓	\$0.84	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	XLP, Temp*	
	PIC16F631	R	20	18	MR	1.75 KB 1 Kw	✓	–	64	128	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	–	–	–	–	2	–	–	1	1	–	–	–	–	–	–	BOR	SW0	✓	✓	\$0.91	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	–		
	PIC16F677	R	20	18	MR	3.5 KB 2 Kw	✓	–	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	–	–	1	1	–	–	1	1	–	–	BOR	SW0	✓	✓	\$0.99	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	–	
	PIC16F1828	R	20	18	EMR	7 KB 4 Kw	✓	✓	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	12	–	–	12	–	2	2	2	4	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$0.99	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	DSM, XLP, Temp*	
	PIC16F1829	NR	20	18	EMR	14 KB 8 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	0	12	–	–	12	–	2	2	2	4	1	–	1	2	2	–	–	BOR	SW0	✓	✓	\$1.06	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	DSM, XLP, Temp*	
	PIC16F687	R	20	18	MR	3.5 KB 2 Kw	✓	–	128	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	–	–	1	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$1.07	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	–	
	PIC16F785	R	20	18	MR	3.5 KB 2 Kw	–	–	128	256	2V-15V	20 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	1	–	2	1	–	–	–	–	–	–	BOR	SW0	–	✓	\$1.12	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	2-phase PWM, 2x Op Amp	
	PIC16F685	R	20	18	MR	7 KB 4 Kw	✓	–	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	–	1	2	1	–	–	–	–	–	–	BOR	SW0	✓	✓	\$1.13	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	–	
	PIC16F689	R	20	18	MR	7 KB 4 Kw	✓	–	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	–	–	1	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$1.13	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	–	
	PIC16F690	R	20	18	MR	7 KB 4 Kw	✓	–	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	–	1	2	1	–	1	1	1	–	–	BOR	SW0	✓	✓	\$1.20	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	–	
	PIC18F13K22	R	20	18	PIC18	8 KB 4 Kw	✓	✓	256	256	1.8V-5.5V	64 MHz	64 MHz, 31 kHz	0	12	–	–	12	–	2	–	1	1	3	–	1	1	1	–	–	PBOR	SW0	✓	–	\$1.33	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	XLP, Temp*	
28-Pin	PIC18F13K50	R	20	15	PIC18	8 KB 4 Kw	✓	✓	512	256	1.8V-5.5V	48 MHz	32 MHz, 31 kHz	0	9	–	–	9	–	2	–	1	1	3	–	1	1	1	–	1	PBOR	SW0	✓	–	\$1.39	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), XLP, Temp*	28-Pin
	PIC18F14K22	R	20	18	PIC18	16 KB 8 Kw	✓	✓	512	256	1.8V-5.5V	64 MHz	64 MHz, 31 kHz	0	12	–	–	12	–	2	–	1	1	3	–	1	1	1	–	–	PBOR	SW0	✓	–	\$1.47	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	XLP, Temp*	
	PIC18F14K50	R	20	15	PIC18	16 KB 8 Kw	✓	✓	768	256	1.8V-5.5V	48 MHz	32 MHz, 31 kHz	0	9	–	–	9	–	2	–	1	1	3	–	1	1	1	–	1	PBOR	SW0	✓	–	\$1.53	PDIP (P), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), XLP, Temp*	
	PIC16F57	R	28	20	BL	3 KB 2 Kw	–	–	72	–	2V-5.5V	20 MHz	0	0	–	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	\$0.52	SPDIP (SP), SOIC (SO), SSOP (SS)	–	
	PIC16F722A	R	28	25	MR	3.5 KB 2 Kw	✓	–	128	–	1.8V-5.5V	20 MHz	16 MHz	0	11	–	11	–	–	0	2	–	2	1	1	–	1	1	–	–	BOR	SW0	–	✓	\$0.78	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*	
	PIC16LF1902	NR	28	25	EMR	3.5 KB 2 Kw	✓	✓	128	–	1.8V-3.6V	20 MHz	16 MHz	72	11	–	–	11	–	–	–	–	1	1	–	–	–	–	–	–	–	–	–	–	\$0.78	SPDIP (SP), SOIC (SO), SSOP (SS), 4x4 UQFN (MV)	Integrated LCD Driver, XLP, Temp*	
28-Pin	PIC16F723A	R	28	25	MR	7 KB 4 Kw	✓	–	192	–	1.8V-5.5V	20 MHz	16 MHz	0	11	–	11	–	–	0	2	–	2	1	1	–	1	1	–	–	BOR	SW0	–	✓	\$0.85	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*	28-Pin
	PIC16LF1903	NR	28	25	EMR	7 KB 4 Kw	✓	✓	256	–	1.8V-3.6V	20 MHz	16 MHz	72	11	–	–	11	–	–	–	–	1	1	–	–	–	–	–	–	–	–	–	–	\$0.85	SPDIP (SP), SOIC (SO), SSOP (SS), 4x4 UQFN (MV)	Integrated LCD Driver, XLP, Temp*	
	PIC16LF1906	NR	28	25	EMR	14 KB 8 Kw	✓	✓	512	–	1.8V-3.6V	20 MHz	16 MHz	72	11	–	–	11	–	–	–	–	1	1	–	1	–	–	–	–	–	–	–	–	\$0.91	SPDIP (SP), SOIC (SO), SSOP (SS), 4x4 UQFN (MV)	Integrated LCD Driver, XLP, Temp*	

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

*Reference Application Note AN1333 for temperature indicator implementation.

8-bit PIC® Microcontrollers

Product		Released (R) Not Released (NR)	Pins		Core	Memory					Voltage Range	Operating Speed		LCD Segments	mTouch™ Channels	Analog Sensing & Measurement				Digital				Communication						ECAN	Monitors		SR-Latch	Timer 1 Gate	5 ku Pricing†	Packages (Designator)	Special Features	
			Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)		Maximum Speed	Internal Oscillator			Change Time Measurement Unit	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI	Ethernet (MAC/PHY)		FS-USB	BOR/PBOR						PLVD
28-Pin (Cont.)	PIC16F1516	NR	28	25	EMR	14 KB 8 Kw	✓	✓	512	–	1.8V-5.5V	20 MHz	16 MHz	0	17	–	–	17	–	–	2	–	2	1	–	1	1	1	–	–	–	PBOR	SW	–	✓	\$0.95	SPDIP (SP), SSOP (SS), SOIC (SO), 4x4 UQFN (MV)	XLP, Temp*
	PIC16F1518	NR	28	25	EMR	28 KB 16 Kw	✓	✓	1024	–	1.8V-5.5V	20 MHz	16 MHz	0	17	–	–	17	–	–	2	–	2	1	–	1	1	1	–	–	–	PBOR	SW	–	✓	\$1.01	SPDIP (SP), SSOP (SS), SOIC (SO), 4x4 UQFN (MV)	XLP, Temp*
	PIC16F882	R	28	25	MR	3.5 KB 2 Kw	✓	✓	128	128	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	11	–	–	11	–	2	1	1	2	1	–	1	1	1	–	–	–	BOR	SW0	✓	✓	\$1.16	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML)	–
	PIC16F726	R	28	25	MR	14 KB 8 Kw	✓	–	368	–	1.8V-5.5V	20 MHz	16 MHz	0	11	–	11	–	–	0	2	–	2	1	1	–	1	1	–	–	–	BOR	SW0	–	✓	\$1.23	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*
	PIC16F1933	R	28	25	EMR	7 KB 4 Kw	✓	✓	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	60	11	–	–	11	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW0	✓	✓	\$1.23	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*
	PIC18F23K20	R	28	25	PIC18	8 KB 4 Kw	✓	✓	512	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	11	–	–	11	–	2	1	1	1	3	–	1	1	1	–	–	–	BOR	✓	–	–	\$1.23	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP
	PIC16F1936	R	28	25	EMR	14 KB 8 Kw	✓	✓	512	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	60	11	–	–	11	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW0	✓	✓	\$1.30	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*
	PIC18F24K20	R	28	25	PIC18	16 KB 8 Kw	✓	✓	768	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	11	–	–	11	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	\$1.30	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP
	PIC16F883	R	28	25	MR	7 KB 4 Kw	✓	✓	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	11	–	–	11	–	2	1	1	2	1	–	1	1	1	–	–	–	BOR	SW0	✓	✓	\$1.37	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	–
	PIC16F1938	R	28	25	EMR	28 KB 16 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	60	11	–	–	11	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW0	✓	✓	\$1.37	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*
	PIC18F25K20	R	28	25	PIC18	32 KB 16 Kw	✓	✓	1536	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	11	–	–	11	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	\$1.37	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP
	PIC18F23K22	R	28	25	PIC18	8 KB 4 Kw	✓	✓	512	256	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	17	✓	–	17	–	2	1	1	1	3	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$1.41	SPDIP (SP), SOIC (SO), SSOP (SS), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*
	PIC18F24J10	R	28	21	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	32 kHz	0	10	–	–	10	–	2	2	–	1	2	–	1	1	1	–	–	–	BOR	–	–	–	\$1.44	SPDIP (SP), SOIC (SO), QFN (ML)	–
	PIC18F24K22	R	28	25	PIC18	16 KB 8 Kw	✓	✓	768	256	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	17	✓	–	17	–	2	1	1	1	3	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$1.48	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML), 4x4 UQFN (MV)	XLP, Temp*
	PIC16F886	R	28	25	MR	14 KB 8 Kw	✓	✓	368	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	11	–	–	11	–	2	1	1	2	1	–	1	1	1	–	–	–	BOR	SW0	✓	✓	\$1.49	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	–
	PIC18F25J10	R	28	21	PIC18	32 KB 16 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	32 kHz	0	10	–	–	10	–	2	2	–	1	2	–	1	1	1	–	–	–	BOR	–	–	–	\$1.58	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	–
	PIC18F25K22	R	28	25	PIC18	32 KB 16 Kw	✓	✓	1536	256	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	17	✓	–	17	–	2	2	3	3	4	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$1.62	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP, Temp*
	PIC18F24J11	R	28	21	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	10	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW0	–	–	\$1.65	SPDIP (SP), SOIC (SO), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F26K20	R	28	25	PIC18	64 KB 32 Kw	✓	✓	3936	1024	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	11	–	–	11	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	\$1.65	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP, Temp*
	PIC18F25J11	R	28	21	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	10	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW0	–	–	\$1.79	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F24J50	R	28	22	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	10	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW0	–	–	\$1.86	SPDIP (SP), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F26K22	R	28	25	PIC18	64 KB 32 Kw	✓	✓	3896	1024	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	17	✓	–	17	–	2	2	3	3	4	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$1.92	SPDIP (SP), SSOP (SS), SOIC (SO), 6x6 QFN (ML)	XLP, Temp*
	PIC18F25K80	NR	28	24	PIC18	32 KB 16 Kw	✓	✓	3648	1024	1.8V-5.5V	64 MHz	8 MHz, 31 kHz	0	8	✓	–	–	8	2	4	1	2	3	–	2	1	1	–	–	1	PBOR	✓	–	–	\$1.93	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	CAN 2.0, CTMU, Deep Sleep Mode, XLP
	PIC18F25J50	R	28	22	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	10	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW0	–	–	\$2.00	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F26J11	R	28	21	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	10	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW0	–	–	\$2.07	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F26K80	NR	28	24	PIC18	64 KB 32 Kw	✓	✓	3648	1024	1.8V-5.5V	64 MHz	8 MHz, 31 kHz	0	8	✓	–	–	8	2	4	1	2	3	–	2	1	1	–	–	1	PBOR	✓	–	–	\$2.21	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	CAN 2.0, CTMU, Deep Sleep Mode, XLP
	PIC18F2450	R	28	23	PIC18	16 KB 8 Kw	✓	✓	768	–	2V-5.5V	48 MHz	32 kHz	0	–	–	–	10	–	0	1	–	1	2	–	1	–	–	–	1	–	PBOR	SW0	–	–	\$2.23	SPDIP (SP), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed)
	PIC18F26J13	R	28	23	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	–	10	3	7	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.24	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	SPI w/DMA, XLP
PIC18F26J50	R	28	22	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	10	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW0	–	–	\$2.28	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP	
PIC18F26J53	R	28	22	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	–	10	3	7	3	4	4	–	2	2	2	–	1	–	BOR	✓	–	–	\$2.45	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), SPI w/DMA, XLP	

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

*Reference Application Note AN1333 for temperature indicator implementation.

8-bit PIC® Microcontrollers

Product		Released (R) Not Released (NR)	Pins		Core	Memory					Voltage Range	Operating Speed		LCD Segments	mTouch™ Channels	Analog Sensing & Measurement				Digital				Communication					ECAN	Monitors		SR-Latch	Timer 1 Gate	5 ku Pricing¹	Packages (Designator)	Special Features			
			Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)		Maximum Speed	Internal Oscillator			Charge Time Measurement Unit	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	IC™	SPI		Ethernet (MACPHY)	FS-USB							BOR/PBOR	PLVD
28-Pin (Cont.)	PIC18F27J13	R	28	23	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	–	10	3	7	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.48	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	SPI wDMA, XLP	28-Pin (Cont.)
	PIC18F27J53	R	28	22	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	10	✓	–	–	10	3	7	3	4	4	–	2	2	2	–	1	–	BOR	✓	–	–	\$2.69	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	USB 2.0 (Full Speed), SPI wDMA, XLP	
	PIC18F2550	R	28	24	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	10	–	–	10	–	2	2	–	1	3	–	1	1	1	–	1	–	PBOR	SW0	–	–	\$3.44	PDIP (P), SPDIP(SP), SOIC (SO)	USB 2.0 (Full Speed)	
	PIC18F2553	R	28	24	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	–	–	–	10	2	2	–	1	3	–	1	1	1	–	1	–	PBOR	SW0	–	–	\$4.12	SPDIP(SP), SOIC (SO)	USB 2.0 (Full Speed)		
40/44-Pin	PIC16F59	R	40	32	BL	3 KB 2 Kw	–	–	134	–	2V-5.5V	20 MHz	0	0	–	–	–	–	0	–	–	1	–	–	–	–	–	–	–	–	–	–	–	–	–	\$0.85	PDIP (P), TQFP (PT)	–	40/44-Pin
	PIC16LF1906	NR	40	36	EMR	7 KB 4 Kw	✓	✓	256	–	1.8V-3.6V	20 MHz	16 MHz	116	14	–	–	14	–	–	–	–	1	1	–	1	–	–	–	–	–	–	–	–	–	\$1.19	PDIP (P), TQFP (PT), 5x5 UQFN (MV)	Integrated LCD Driver, XLP, Temp*	
	PIC16LF1907	NR	40	36	EMR	14 KB 8 Kw	✓	✓	512	–	1.8V-3.6V	20 MHz	16 MHz	116	14	–	–	14	–	–	–	–	1	1	–	1	–	–	–	–	–	–	–	–	–	\$1.25	PDIP (P), TQFP (PT), 5x5 UQFN (MV)	Integrated LCD Driver, XLP, Temp*	
	PIC16F1517	NR	40	36	EMR	14 KB 8 Kw	✓	✓	512	–	1.8V-5.5V	20 MHz	16 MHz	0	28	–	–	28	–	–	2	–	2	1	–	1	1	1	–	–	–	PBOR	SW	–	✓	\$1.32	PDIP (P), TQFP (PT), 5x5 UQFN (MV)	XLP, Temp*	
	PIC16F1519	NR	40	36	EMR	28 KB 16 Kw	✓	✓	1024	–	1.8V-5.5V	20 MHz	16 MHz	0	28	–	–	28	–	–	2	–	2	1	–	1	1	1	–	–	–	PBOR	SW	–	✓	\$1.37	PDIP (P), TQFP (PT), 5x5 UQFN (MV)	XLP, Temp*	
	PIC16F724	R	40	36	MR	7 KB 4 Kw	✓	–	192	–	1.8V-5.5V	20 MHz	16 MHz	0	16	–	14	–	–	0	2	–	2	1	1	–	1	1	–	–	–	BOR	SW0	–	✓	\$1.40	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC16F1934	R	40	36	EMR	7 KB 4 Kw	✓	✓	256	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	96	16	–	–	14	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW0	✓	✓	\$1.47	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC18F43K20	R	40	36	PIC18	8 KB 4 Kw	✓	✓	512	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	14	–	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	BOR	✓	–	–	\$1.47	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP	
	PIC16F727	R	40	36	MR	14 KB 8 Kw	✓	–	368	–	1.8V-5.5V	20 MHz	16 MHz	0	16	–	14	–	–	0	2	–	2	1	1	–	1	1	–	–	–	BOR	SW0	–	✓	\$1.54	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC16F1937	R	40	36	EMR	14 KB 8 Kw	✓	✓	512	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	96	16	–	–	14	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW0	✓	✓	\$1.54	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC18F44K20	R	40	36	PIC18	16 KB 8 Kw	✓	✓	768	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	14	–	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	\$1.54	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP	
	PIC16F1939	R	40	36	EMR	28 KB 16 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	96	16	–	–	14	–	2	2	3	4	1	–	1	1	1	–	–	–	PBOR	SW0	✓	✓	\$1.61	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC18F45K20	R	40	36	PIC18	32 KB 16 Kw	✓	✓	1536	256	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	14	–	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	\$1.61	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP	
	PIC16F884	R	40	36	MR	7 KB 4 Kw	✓	✓	256	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	14	–	–	14	–	2	1	1	2	1	–	1	1	1	–	–	–	BOR	SW0	✓	✓	\$1.63	PDIP (P), TQFP (PT), 8x8 QFN (ML)	–	
	PIC18F44J10	R	40	32	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	31 kHz	0	13	–	–	13	–	2	1	1	1	2	–	1	2	2	–	–	–	BOR	–	–	–	\$1.67	PDIP (P), TQFP (PT), QFN (ML)	–	
	PIC18F43K22	R	40	36	PIC18	8 KB 4 Kw	✓	✓	512	256	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	28	✓	–	28	–	2	1	1	1	3	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$1.68	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC18F44K22	R	40	36	PIC18	16 KB 8 Kw	✓	✓	768	256	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	28	✓	–	28	–	2	1	1	1	3	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$1.75	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC16F887	R	40	36	MR	14 KB 8 Kw	✓	✓	368	256	2V-5.5V	20 MHz	8 MHz, 31 kHz	0	14	–	–	14	–	2	1	1	2	1	–	1	1	1	–	–	–	BOR	SW0	✓	✓	\$1.78	PDIP (P), TQFP (PT), 8x8 QFN (ML)	–	
	PIC18F45J10	R	40	32	PIC18	32 KB 16 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	31 kHz	0	13	–	–	13	–	2	1	1	1	2	–	1	2	2	–	–	–	BOR	–	–	–	\$1.81	PDIP (P), TQFP (PT), QFN (ML)	–	
	PIC18F46K20	R	40	36	PIC18	64 KB 32 Kw	✓	✓	3936	1024	1.8V-3.6V	64 MHz	16 MHz, 31 kHz	0	14	–	–	14	–	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	✓	–	–	\$1.82	PDIP (P), TQFP (PT), 8x8 QFN (ML)	XLP	
	PIC18F45K22	R	40	36	PIC18	32 KB 16 Kw	✓	✓	1536	256	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	28	✓	–	28	–	2	2	2	3	4	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$1.89	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC18F44J11	R	40	34	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	13	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW0	–	–	\$1.95	TQFP (PT), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP	
	PIC18F45J11	R	40	34	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	13	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW0	–	–	\$2.09	TQFP (PT), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP	
	PIC18F44J50	R	40	34	PIC18	16 KB 8 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	13	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW0	–	–	\$2.16	TQFP (PT), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP	
	PIC18F45K80	NR	40/44	35	PIC18	32 KB 16 Kw	✓	✓	3648	1024	1.8V-5.5V	64 MHz	8 MHz, 31 kHz	0	15	✓	–	–	15	2	4	1	2	3	–	2	1	1	–	–	1	PBOR	✓	✓	✓	\$2.17	PDIP (P), TQFP (PT), QFN (ML)	CAN 2.0, CTMU, Deep Sleep Mode, XLP	
	PIC18F46K22	R	40	36	PIC18	64 KB 32 Kw	✓	✓	3896	1024	1.8V-5.5V	64 MHz	16 MHz, 31 kHz	0	28	✓	–	28	–	2	2	2	3	4	–	2	2	2	–	–	–	PBOR	✓	✓	✓	\$2.17	PDIP (P), TQFP (PT), 8x8 QFN (ML), 5x5 UQFN (MV)	XLP, Temp*	
	PIC18F45J50	R	40	34	PIC18	32 KB 16 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	13	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW0	–	–	\$2.30	TQFP (PT), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP	

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

*Reference Application Note AN1333 for temperature indicator implementation.

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	Pins		Core	Memory				Operating Speed			LCD Segments	mTouch™ Channels	Analog Sensing & Measurement					Digital				Communication					ECAN	Monitors			Timer 1 Gate	5 ku Pricing†	Packages (Designator)	Special Features			
		Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)	Voltage Range	Maximum Speed			Internal Oscillator	Charge Time Measurement Unit	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI		Ethernet (MAC/PHY)	FS-USB	BOR/PBOR					PLVD	SR-Latch	
40/44-Pin (Cont.)	PIC18F46J11	R	40	34	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	13	–	2	–	2	2	3	–	2	2	2	–	–	–	BOR	SW0	–	–	\$2.37	PDIP (P), TQFP (PT), QFN (ML)	Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F4450	R	40	34	PIC18	16 KB 8 Kw	✓	✓	768	–	2V-5.5V	48 MHz	31 kHz	0	13	–	–	13	–	0	1	–	1	2	–	1	–	–	–	1	–	PBOR	SW0	–	–	\$2.39	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed)
	PIC18F46K80	NR	40/44	35	PIC18	64 KB 32 Kw	✓	✓	3648	1024	1.8V-5.5V	64 MHz	8 MHz, 31 kHz	0	15	✓	–	–	15	2	4	1	2	3	–	2	1	1	–	–	1	PBOR	✓	–	–	\$2.45	PDIP (P), TQFP (PT), QFN (ML)	CAN 2.0, CTMU, Deep Sleep Mode, XLP
	PIC18F46J13	R	44	34	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	–	13	3	7	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.52	TQFP (PT), QFN (ML)	SPI w/DMA, XLP
	PIC18F46J50	R	40	34	PIC18	64 KB 32 Kw	✓	✓	3800	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	13	–	2	–	2	2	3	–	2	2	2	–	1	–	BOR	SW0	–	–	\$2.58	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed), Peripheral Pin Select, Deep Sleep Mode, XLP
	PIC18F46J53	R	44	33	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	–	13	3	7	3	4	4	–	2	2	2	–	1	–	BOR	✓	–	–	\$2.73	TQFP (PT), QFN (ML)	Integrated LCD Driver, SPI w/DMA, XLP
	PIC18F47J13	R	44	34	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	–	13	3	7	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.76	TQFP (PT), QFN (ML)	SPI w/DMA, XLP
	PIC18F47J53	R	44	33	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	13	✓	–	–	13	3	7	3	4	4	–	2	2	2	–	1	–	BOR	✓	–	–	\$2.97	TQFP (PT), QFN (ML)	Integrated LCD Driver, SPI w/DMA, XLP
	PIC18F4550	R	40	35	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	13	–	–	13	–	2	1	1	1	3	–	1	1	1	–	1	–	PBOR	SW0	–	–	\$3.65	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed)
	PIC18F4523	R	40	36	PIC18	32 KB 16 Kw	✓	✓	1536	256	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	13	–	–	–	13	2	1	1	1	3	–	1	1	1	–	–	–	PBOR	SW0	–	–	\$3.67	PDIP (P), TQFP (PT), QFN (ML)	–
PIC18F4553	R	40	35	PIC18	32 KB 16 Kw	✓	✓	2048	256	2V-5.5V	48 MHz	8 MHz, 31 kHz	0	13	–	–	–	13	2	1	1	1	3	–	1	1	1	–	1	–	PBOR	SW0	–	–	\$4.33	PDIP (P), TQFP (PT), QFN (ML)	USB 2.0 (Full Speed)	
64-Pin	PIC16F1526	NR	64	54	EMR	14 KB 8 Kw	✓	✓	768	–	1.8V-5.5V	20 MHz	16 MHz	0	30	–	–	30	–	–	10	–	6	3	–	2	2	2	–	–	–	PBOR	SW0	–	✓	\$1.47	TQFP (PT), QFN (MR)	XLP, Temp*
	PIC16F1527	NR	64	54	EMR	28 KB 16 Kw	✓	✓	1536	–	1.8V-5.5V	20 MHz	16 MHz	0	30	–	–	30	–	–	10	–	6	3	–	2	2	2	–	–	–	PBOR	SW0	–	✓	\$1.54	TQFP (PT), QFN (MR)	XLP, Temp*
	PIC16F1946	R	64	53	EMR	14 KB 8 Kw	✓	✓	512	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	184	17	–	–	17	–	3	2	3	4	1	–	2	2	2	–	–	–	BOR	SW0	✓	✓	\$1.75	TQFP (PT), QFN (MR)	XLP, Temp*
	PIC16F1947	R	64	53	EMR	28 KB 16 Kw	✓	✓	1024	256	1.8V-5.5V	32 MHz	32 MHz, 31 kHz	184	17	–	–	17	–	3	2	3	4	1	–	2	2	2	–	–	–	BOR	SW0	✓	✓	\$1.82	TQFP (PT), QFN (MR)	XLP, Temp*
	PIC18F63J11	R	64	54	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	PBOR	SW0	–	–	\$2.20	TQFP (PT)	–
	PIC18F65J10	R	64	50	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	31 kHz	0	11	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.25	TQFP (PT)	–
	PIC18F64J11	R	64	54	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW0	–	–	\$2.27	TQFP (PT)	–
	PIC18F63J90	R	64	51	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	132	12	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.35	TQFP (PT)	Integrated LCD Driver
	PIC18F65J11	R	64	54	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	12	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW0	–	–	\$2.37	TQFP (PT)	–
	PIC18F65K22	R	64	53	PIC18	32 KB 16 Kw	✓	✓	2048	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	0	16	✓	–	–	16	3	5	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.39	QFN (MR), TQFP (PT)	XLP
PIC18F64J90	R	64	51	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	132	12	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.41	TQFP (PT)	Integrated LCD Driver	
PIC18F66J10	R	64	50	PIC18	64 KB 32 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	31 kHz	0	11	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.49	TQFP (PT)	–	
PIC18F65J90	R	64	50	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	132	12	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.52	TQFP (PT)	Integrated LCD Driver	
PIC18F65K90	R	64	53	PIC18	32 KB 16 Kw	✓	✓	2048	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	132	16	✓	–	–	16	3	5	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.53	QFN (MR), TQFP (PT)	Integrated LCD Driver, XLP	
PIC18F65J50	R	64	49	PIC18	32 KB 16 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	8	–	–	8	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	\$2.63	TQFP (PT)	USB 2.0 (Full Speed)	
PIC18F66J11	R	64	50	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	11	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.63	TQFP (PT)	–	
PIC18F66J90/3	R	64	51	PIC18	64 KB 32 Kw	✓	✓	3900	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	132	12	✓	–	12	12	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.70	TQFP (PT)	Integrated LCD Driver, RTCC	
PIC18F65K80	NR	64	54	PIC18	32 KB 16 Kw	✓	✓	3648	1024	1.8V-5.5V	64 MHz	8 MHz, 31 kHz	0	15	✓	–	–	15	2	4	1	2	3	–	2	1	1	–	–	1	PBOR	✓	–	–	\$2.70	TQFP (PT), QFN (MR)	CAN 2.0, CTMU, Deep Sleep Mode, XLP	
PIC18F66K22	R	64	53	PIC18	64 KB 32 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	0	16	✓	–	–	16	3	7	3	6	5	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.70	QFN (MR), TQFP (PT)	XLP	
PIC18F67J10	R	64	50	PIC18	128 KB 64 Kw	✓	✓	3936	–	2V-3.6V	40 MHz	31 kHz	0	11	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.77	TQFP (PT)	–	

Products sorted by pin count followed by pricing.
† - Pricing subject to change; please contact your Microchip representative for most current pricing.
◊ - Software PLVD implemented via ADC.
*Reference Application Note AN1333 for temperature indicator implementation.

8-bit PIC® Microcontrollers

Product		Released (R) Not Released (NR)	Pins		Core	Memory				Operating Speed				LCD Segments	mTouch™ Channels	Analog Sensing & Measurement					Digital				Communication						Monitors				5 ku Pricing†	Packages (Designator)	Special Features		
			Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)	Data EE (B)	Voltage Range	Maximum Speed	Internal Oscillator			Charge Time Measurement Unit	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	PC™	SPI	Ethernet (MAC/PHY)	FS-USB	ECAN	BOR/PBOR	PLVD	SR-Latch				Timer 1 Gate	
64-Pin (Cont.)	PIC18F66K90	R	64	53	PIC18	64 KB 32 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	132	16	✓	–	–	16	3	7	3	6	5	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.84	QFN (MR), TQFP (PT)	Integrated LCD Driver, XLP	
	PIC18F66J50	R	64	49	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	8	–	–	8	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	\$2.90	TQFP (PT)	USB 2.0 (Full Speed)	
	PIC18F67J11	R	64	50	PIC18	128 KB 64 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	11	–	–	11	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.93	TQFP (PT)	–	
	PIC18F67K22	R	64	53	PIC18	128 KB 64 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	0	16	✓	–	–	16	3	7	3	6	5	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.94	QFN (MR), TQFP (PT)	XLP	
	PIC18F66K80	NR	64	54	PIC18	64 KB 32 Kw	✓	✓	3648	1024	1.8V-5.5V	64 MHz	8 MHz, 31 kHz	0	11	✓	–	–	15	2	4	1	2	3	–	2	1	1	–	–	1	PBOR	✓	–	–	\$2.98	TQFP (PT), QFN (MR)	CAN 2.0, CTMU, Deep Sleep Mode, XLP	
	PIC18F67J90/3	R	64	51	PIC18	128 KB 64 Kw	✓	✓	3900	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	132	12	✓	–	–	12	12	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$3.00	TQFP (PT)	Integrated LCD Driver, RTCC
	PIC18F67K90	R	64	53	PIC18	128 KB 64 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	132	16	✓	–	–	16	3	7	3	6	5	–	2	2	2	–	–	–	BOR	✓	–	–	\$3.08	QFN (MR), TQFP (PT)	Integrated LCD Driver, XLP	
	PIC18F67J50	R	64	49	PIC18	128 KB 64 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	8	–	–	8	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	\$3.19	TQFP (PT)	USB 2.0 (Full Speed)	
	PIC18F6493	R	64	50	PIC18	16 KB 8 Kw	✓	–	768	–	2V-5.5V	32 MHz	8 MHz, 31 kHz	132	12	–	–	–	12	2	2	–	1	3	1	1	1	1	–	–	–	PBOR	SW0	–	–	\$3.29	TQFP (PT)	Integrated LCD Driver	
	PIC18F66J60	R	64	39	PIC18	64 KB 32 Kw	✓	✓	3808	–	2V-3.6V	42 MHz	31 kHz	0	11	–	–	11	–	2	2	3	2	3	–	1	1	1	–	–	–	BOR	✓	–	–	\$3.36	TQFP (PT)	Integrated MAC, 10 Base T PHY	
	PIC18F67J60	R	64	39	PIC18	128 KB 64 Kw	✓	✓	3808	–	2V-3.6V	42 MHz	31 kHz	0	11	–	–	11	–	2	2	3	2	3	–	1	1	1	1	–	–	BOR	✓	–	–	\$3.65	TQFP (PT)	Integrated MAC, 10 Base T PHY	
	PIC18F6723	R	64	54	PIC18	128 KB 64 Kw	✓	✓	3936	1024	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	12	–	–	–	12	2	2	3	2	3	–	2	2	2	–	–	–	PBOR	SW0	–	–	\$7.99	TQFP (PT)	–	
80-Pin	PIC18F83J11	R	80	70	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW0	–	–	\$2.46	TQFP (PT)	–	
	PIC18F85J10	R	80	66	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.49	TQFP (PT)	–	
	PIC18F84J11	R	80	70	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW0	–	–	\$2.52	TQFP (PT)	–	
	PIC18F83J90	R	80	66	PIC18	8 KB 4 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	192	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.60	TQFP (PT)	Integrated LCD Driver	
	PIC18F85J11	R	80	70	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	SW0	–	–	\$2.63	TQFP (PT)	–	
	PIC18F85K22	R	80	69	PIC18	32 KB 16 Kw	✓	✓	2048	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	24	✓	–	–	24	3	5	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.66	TQFP (PT)	XLP		
	PIC18F84J90	R	80	66	PIC18	16 KB 8 Kw	✓	✓	1024	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	192	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.67	TQFP (PT)	Integrated LCD Driver	
	PIC18F86J10	R	80	66	PIC18	64 KB 32 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.74	TQFP (PT)	–	
	PIC18F85J90	R	80	66	PIC18	32 KB 16 Kw	✓	✓	2048	–	2V-3.6V	40 MHz	8 MHz, 31 kHz	192	–	–	–	12	–	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.77	TQFP (PT), LQFP (PL)	Integrated LCD Driver	
	PIC18F85K90	R	80	69	PIC18	32 KB 16 Kw	✓	✓	2048	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	192	24	✓	–	–	24	3	5	3	4	4	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.80	TQFP (PT)	Integrated LCD Driver, XLP	
	PIC18F85J50	R	80	65	PIC18	32 KB 16 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	\$2.90	TQFP (PT)	USB 2.0 (Full Speed)	
	PIC18F86J11	R	80	66	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.90	TQFP (PT)	–	
	PIC18F86J90/3	R	80	67	PIC18	64 KB 32 Kw	✓	✓	3900	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	192	12	✓	–	12	12	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$2.97	TQFP (PT)	Integrated LCD Driver, RTCC	
	PIC18F86K22	R	80	69	PIC18	64 KB 32 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	24	✓	–	–	24	3	7	3	6	5	–	2	2	2	–	–	–	BOR	✓	–	–	\$2.97	TQFP (PT)	XLP		
	PIC18F87J10	R	80	66	PIC18	128 KB 64 Kw	✓	✓	3936	–	2V-3.6V	40 MHz	31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$3.02	TQFP (PT), LQFP (PL)	–	
	PIC18F86K90	R	80	69	PIC18	64 KB 32 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	192	24	✓	–	–	24	3	7	3	6	5	–	2	2	2	–	–	–	BOR	✓	–	–	\$3.11	TQFP (PT)	Integrated LCD Driver, XLP	
	PIC18F86J50	R	80	65	PIC18	64 KB 32 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	12	–	2	2	3	2	3	–	2	2	2	–	1	–	BOR	✓	–	–	\$3.15	TQFP (PT)	USB 2.0 (Full Speed)	
	PIC18F87J11	R	80	66	PIC18	128 KB 64 Kw	✓	✓	3904	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	–	–	–	15	–	2	2	3	2	3	–	2	2	2	–	–	–	BOR	✓	–	–	\$3.19	TQFP (PT)	–	
	PIC18F87K22	R	80	69	PIC18	128 KB 64 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	24	✓	–	–	24	3	7	3	6	5	–	2	2	2	–	–	–	BOR	✓	–	–	\$3.21	TQFP (PT)	XLP		
	PIC18F87J90/3	R	80	67	PIC18	128 KB 64 Kw	✓	✓	3900	–	2V-3.6V	48 MHz	8 MHz, 31 kHz	192	12	✓	–	12	12	2	2	–	1	3	1	1	1	1	–	–	–	BOR	✓	–	–	\$3.26	TQFP (PT)	Integrated LCD Driver, RTCC	

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

8-bit PIC® Microcontrollers

Product	Released (R) Not Released (NR)	Pins		Core	Memory				Voltage Range	Operating Speed		LCD Segments	mTouch™ Channels	Analog Sensing & Measurement					Digital				Communication					ECAN	Monitors		Timer 1 Gate	5 ku Pricing†	Packages (Designator)	Special Features				
		Total	I/O		Program	Self-Read	Self-Write	Data RAM (B)		Data EE (B)	Maximum Speed			Internal Oscillator	Charge Time Measurement Unit	8-bit ADC	10-bit ADC	12-bit ADC	Comparators	CCP	ECCP	8-bit Timer	16-bit Timer	AUSART	EUSART	I²C™	SPI		Ethernet (MAC/PHY)	FS-USB					BOR/PBOR	PLVD	SR-Latch	
80-Pin (Cont.)	PIC18F87K90	NR	80	69	PIC18	128 KB 64 Kw	✓	✓	4096	1024	1.8V-5.5V	64 MHz	31 kHz, 500 kHz, 16 MHz	192	24	✓	-	-	24	3	7	3	6	5	-	2	2	2	-	-	-	BOR	✓	-	-	\$3.35	TQFP (PT)	Integrated LCD Driver, XLP
	PIC18F87J50	R	80	65	PIC18	128 KB 64 Kw	✓	✓	3904	-	2V-3.6V	48 MHz	8 MHz, 31 kHz	0	-	-	-	12	-	2	2	3	2	3	-	2	2	2	-	1	-	BOR	✓	-	-	\$3.44	TQFP (PT)	USB 2.0 (Full Speed)
	PIC18F86J60	R	80	55	PIC18	64 KB 32 Kw	✓	✓	3808	-	2V-3.6V	42 MHz	31 kHz	0	-	-	-	15	-	2	2	3	2	3	-	2	1	1	1	-	-	BOR	✓	-	-	\$3.63	TQFP (PT)	Integrated MAC, 10 Base T PHY
	PIC18F8493	R	80	66	PIC18	16 KB 8 Kw	✓	-	768	-	2V-5.5V	32 MHz	8 MHz, 31 kHz	192	-	-	-	-	12	2	2	-	1	3	1	1	1	1	-	-	-	PBOR	SW0	-	-	\$3.78	TQFP (PT)	Integrated LCD Driver
	PIC18F87J60	R	80	55	PIC18	128 KB 64 Kw	✓	✓	3808	-	2V-3.6V	42 MHz	32 kHz, 31 kHz	0	-	-	-	15	-	2	2	3	2	3	-	2	1	1	1	-	-	BOR	✓	-	-	\$3.92	TQFP (PT)	Integrated MAC, 10 Base T PHY
	PIC18F8723	R	80	70	PIC18	128 KB 64 Kw	✓	✓	3936	1024	2V-5.5V	40 MHz	8 MHz, 31 kHz	0	-	-	-	-	16	2	2	3	2	3	-	2	2	2	-	-	-	PBOR	SW0	-	-	\$8.44	TQFP (PT)	-
100-Pin	PIC18F96J60	R	100	70	PIC18	64 KB 32 Kw	✓	✓	3808	-	2V-3.6V	42 MHz	31 kHz	0	-	-	-	16	-	2	2	3	2	3	-	2	2	2	1	-	-	BOR	✓	-	-	\$3.84	TQFP (PT)	Integrated MAC, 10 Base T PHY
	PIC18F97J60	R	100	70	PIC18	128 KB 64 Kw	✓	✓	3808	-	2V-3.6V	42 MHz	31 kHz	0	-	-	-	16	-	2	2	3	2	3	-	2	2	2	1	-	-	BOR	✓	-	-	\$4.13	TQFP (PT), LQFP (PL)	Integrated MAC, 10 Base T PHY

16 bit PIC® Microcontrollers (PIC24F)

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory				Voltage Range	Operating Speed		Analog Sensing & Measurement				Graphics Controller	Output Compare/PWM	Input Capture	16-bit Timer ⁽¹⁾	Communication		PMP	RTCCRC	PPS	5 ku Pricing [†]	Monitors	Packages (Designator)		
					Program (KB)	Data RAM (B)	EEPROM	DMA #Ch		Maximum MIPS	Internal Oscillator	Charge Time Measurement Unit	10-bit ADC	10/12-bit ADC 1100/500 KSPS	Comparators					Digital Communication	FS USB OTG					System Mgmt. Features			
14-Pin	PIC24F04KA200		R	12	PIC24	4	512	AN1095 ⁽¹⁾	–	1.8V-3.6V	16	8 MHz, 32 kHz	✓	7	–	2	–	1	1	3	1 UART, 1 SPI, 1 I ² C	–	–	–	–	\$1.16	BOR, POR, WDT, Deep Sleep, XLP	SPDIP (SP),TSSOP (ST)	14-Pin
	PIC24F04KA201		R	18	PIC24	4	512	AN1095 ⁽¹⁾	–	1.8V-3.6V	16	8 MHz, 32 kHz	✓	9	–	2	–	1	1	3	1 UART, 1 SPI, 1 I ² C	–	–	–	–	\$1.25	BOR, POR, WDT, Deep Sleep, XLP	PDIP (P), SSOP (SS), SOIC (SO), QFN (MQL)	
20-Pin	PIC24F08KA101		R	18	PIC24	8	1536	512	–	1.8V-3.6V	16	8 MHz, 32 kHz	✓	9	–	2	–	1	1	3	2 UART, 1 SPI, 1 I ² C	–	–	✓	–	\$1.44	BOR, POR, WDT, Deep Sleep, XLP	PDIP (P), SSOP (SS), SOIC (SO), QFN (MQL)	20-Pin
	PIC24F16KA101		R	18	PIC24	16	1536	512	–	1.8V-3.6V	16	8 MHz, 32 kHz	✓	9	–	2	–	1	1	3	2 UART, 1 SPI, 1 I ² C	–	–	✓	–	\$1.51	BOR, POR, WDT, Deep Sleep, XLP	PDIP (P), SSOP (SS), SOIC (SO), QFN (MQL)	
	PIC24F16KA301		NR	18	PIC24	16	2048	512	–	1.8V-5.5V	16	8 MHz, 32 kHz	✓	–	9	3	–	3	3	5	2 UART, 2 SPI, 2 I ² C	–	–	✓	–	\$1.86	PWRT, HLVD, POR, OST, WDT	SPDIP (P), SSOP (SS), SOIC (SO)	
	PIC24F32KA301		NR	18	PIC24	32	2048	512	–	1.8V-5.5V	16	8 MHz, 32 kHz	✓	–	9	3	–	3	3	5	2 UART, 2 SPI, 2 I ² C	–	–	✓	–	\$2.00	PWRT, HLVD, POR, OST, WDT	SPDIP (P), SSOP (SS), SOIC (SO)	
28-Pin	PIC24F08KA102		R	24	PIC24	8	1536	512	–	1.8V-3.6V	16	8 MHz, 32 kHz	✓	9	–	2	–	1	1	3	2 UART, 1 SPI, 1 I ² C	–	–	✓	–	\$1.51	BOR, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	28-Pin
	PIC24F16KA102		R	24	PIC24	16	1536	512	–	1.8V-3.6V	16	8 MHz, 32 kHz	✓	9	–	2	–	1	1	3	2 UART, 1 SPI, 1 I ² C	–	–	✓	–	\$1.58	BOR, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	
	PIC24FJ16GA002		R	21	PIC24	16	4096	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	10	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$1.74	BOR, LVD, POR, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	
	PIC24FJ32GA002		R	21	PIC24	32	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	10	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.06	BOR, LVD, POR, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	
	PIC24F16KA302		NR	24	PIC24	16	2048	512	–	1.8V-5.5V	16	8 MHz, 32 kHz	✓	–	10	3	–	3	3	5	2 UART, 2 SPI, 2 I ² C	–	–	✓	–	\$2.06	PWRT, HLVD, POR, OST, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	
	PIC24F32KA302		NR	24	PIC24	32	2048	512	–	1.8V-5.5V	16	8 MHz, 32 kHz	✓	–	10	3	–	3	3	5	2 UART, 2 SPI, 2 I ² C	–	–	✓	–	\$2.20	PWRT, HLVD, POR, OST, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	
	PIC24FJ32GA102		R	21	PIC24	32	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	10	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.23	BOR, LVD, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SOIC (SO), QFN (ML)	
	PIC24FJ32GB002		R	19	PIC24	32	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	9	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	✓	✓	✓	✓	\$2.44	BOR, LVD, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SOIC (SO), QFN (ML)	
	PIC24FJ64GA002		R	21	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	10	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.48	BOR, LVD, POR, WDT	SPDIP (SP), SSOP (SS), SOIC (SO), QFN (ML)	
	PIC24FJ64GA102		R	21	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	10	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.65	BOR, LVD, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SOIC (SO), QFN (ML)	
	PIC24FJ64GB002		R	19	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	9	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	✓	✓	✓	✓	\$2.86	BOR, LVD, POR, WDT, Deep Sleep, XLP	SPDIP (SP), SOIC (SO), QFN (ML)	

*Parts available with High Temperature options (150°C).

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

2: Two 16-bit timers can be concatenated to form a 32-bit timer.

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

16 bit PIC® Microcontrollers (PIC24F)

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory				Voltage Range	Operating Speed		Analog Sensing & Measurement				Graphics Controller	Output Compare/PWM	Input Capture	16-bit Timer ⁽²⁾	Communication		PMP	RTCC/CRC	PPS	5 ku Pricing [†]	Monitors	Packages (Designator)
					Program (KB)	Data RAM (B)	EEPROM	DMA #Ch		Maximum MIPS	Internal Oscillator	Charge Time Measurement Unit	10-bit ADC	10/12-bit ADC 1100/600 KSPS	Comparators					Digital Communication	FS USB OTG					System Mgmt. Features	
44-Pin	PIC24FJ16GA004	R	35	PIC24	16	4096	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	13	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$1.93	BOR, LVD, POR, WDT	TQFP (PT), QFN (ML)
	PIC24FJ32GA004	R	35	PIC24	32	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	13	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.30	BOR, LVD, POR, WDT	TQFP (PT), QFN (ML)
	PIC24F16KA304	NR	38	PIC24	16	2048	512	–	1.8V-5.5V	16	8 MHz, 32 kHz	✓	–	16	3	–	3	3	5	2 UART, 2 SPI, 2 I ² C	–	–	✓	–	\$2.30	PWRT, HLVD, POR, OST, WDT	TQFP (PT), QFN (ML), UQFN (MV)
	PIC24FJ32GA104	 R	35	PIC24	32	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	13	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.44	BOR, LVD, POR, WDT, Deep Sleep, XLP	TQFP (PT), QFN (ML)
	PIC24F32KA304	NR	38	PIC24	32	2048	512	–	1.8V-5.5V	16	8 MHz, 32 kHz	✓	–	16	3	–	3	3	5	2 UART, 2 SPI, 2 I ² C	–	–	✓	–	\$2.44	PWRT, HLVD, POR, OST, WDT	TQFP (PT), QFN (ML), UQFN (MV)
	PIC24FJ32GB004	 R	33	PIC24	32	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	13	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	✓	✓	✓	✓	\$2.65	BOR, LVD, POR, WDT, Deep Sleep, XLP	TQFP (PT), QFN (ML)
	PIC24FJ64GA004	R	35	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	13	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.72	BOR, LVD, POR, WDT	TQFP (PT), QFN (ML)
	PIC24FJ64GA104	 R	35	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	13	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	✓	\$2.86	BOR, LVD, POR, WDT, Deep Sleep, XLP	TQFP (PT), QFN (ML)
PIC24FJ64GB004	 R	33	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	13	–	3	–	5	5	5	2 UART, 2 SPI, 2 I ² C	✓	✓	✓	✓	\$3.07	BOR, LVD, POR, WDT, Deep Sleep, XLP	TQFP (PT), QFN (ML)	
64-Pin	PIC24FJ64GA006	R	53	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.05	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA006	R	53	PIC24	128	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.35	BOR, POR, WDT	TQFP (PT)
	PIC24FJ128GA106	R	53	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$3.56	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ64GB106	R	52	PIC24	64	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$3.64	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GA106	R	53	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$3.77	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ128GB106	R	52	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$3.93	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GA106	R	53	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$3.98	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ192GB106	R	52	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.14	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ128GB206	R	52	PIC24	128	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.30	BOR, LVD, POR, WDT	TQFP (PT), QFN (MR)
	PIC24FJ128DA106	R	52	PIC24	128	24576	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	–	✓	✓	\$4.34	BOR, LVD, POR, WDT	TQFP (PT), QFN (MR)
	PIC24FJ256GB106	R	52	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.35	BOR, LVD, POR, WDT	TQFP (PT)
	PIC24FJ256GB206	R	52	PIC24	256	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.65	BOR, LVD, POR, WDT	TQFP (PT), QFN (MR)
	PIC24FJ256DA106	R	52	PIC24	256	24576	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	–	✓	✓	\$4.69	BOR, LVD, POR, WDT	TQFP (PT), QFN (MR)
	PIC24FJ128DA206	R	52	PIC24	128	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	–	✓	✓	\$4.76	BOR, LVD, POR, WDT	TQFP (PT), QFN (MR)
	PIC24FJ256DA206	R	52	PIC24	256	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	–	✓	✓	\$5.11	BOR, LVD, POR, WDT	TQFP (PT), QFN (MR)
	80-Pin	PIC24FJ64GA008	R	69	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.30	BOR, POR, WDT
PIC24FJ128GA008		R	69	PIC24	128	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.60	BOR, POR, WDT	TQFP (PT)
PIC24FJ128GA108		R	69	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$3.82	BOR, LVD, POR, WDT	TQFP (PT)
PIC24FJ64GB108		R	68	PIC24	64	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$3.91	BOR, LVD, POR, WDT	TQFP (PT)
PIC24FJ192GA108		R	69	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.03	BOR, LVD, POR, WDT	TQFP (PT)
PIC24FJ128GB108		R	68	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.20	BOR, LVD, POR, WDT	TQFP (PT)
PIC24FJ256GA108		R	69	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.24	BOR, LVD, POR, WDT	TQFP (PT)
PIC24FJ192GB108		R	68	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.41	BOR, LVD, POR, WDT	TQFP (PT)

*Parts available with High Temperature options (150°C).

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

2: Two 16-bit timers can be concatenated to form a 32-bit timer.

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

16 bit PIC® Microcontrollers (PIC24F)

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory				Voltage Range	Operating Speed		Analog Sensing & Measurement					Graphics Controller	Output Compare/PWM	Input Capture	16-bit Timer ⁽²⁾	Communication		PMP	RTCC/CRC	PPS	5 ku Pricing [†]	Monitors	Packages (Designator)
					Program (KB)	Data RAM (B)	EEPROM	DMA #Ch		Maximum MIPS	Internal Oscillator	Charge Time Measurement Unit	10-bit ADC	10/12-bit ADC 1100/500 KSPS	Comparators	Digital Communication					FS USB OTG	System Mgmt. Features						
80-pin (Cont.)	PIC24FJ64GA010	R	85	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.51	BOR, POR, WDT	TQFP (PT)	
	PIC24FJ128GA010	R	85	PIC24	128	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.81	BOR, POR, WDT	TQFP (PT)	
	PIC24FJ128GA110	R	85	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.03	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ64GB110	R	84	PIC24	64	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.12	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ192GA110	R	85	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.24	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ128GB110	R	84	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	16 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.41	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ256GA110	R	85	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.45	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ192GB110	R	84	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.62	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ128GB210	R	84	PIC24	128	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.79	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ128DA110	R	84	PIC24	128	24576	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.83	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ256GB110	R	84	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.83	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ256GB210	R	84	PIC24	256	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.14	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ256DA110	R	84	PIC24	256	24576	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.18	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ128DA210	R	84	PIC24	128	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.25	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ256DA210	R	84	PIC24	256	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.60	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ128GB108	R	68	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.20	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ256GA108	R	69	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.24	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ192GB108	R	68	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.41	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ256GB108	R	68	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.62	BOR, LVD, POR, WDT	TQFP (PT)	
100-Pin	PIC24FJ64GA010	R	85	PIC24	64	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.51	BOR, POR, WDT	TQFP (PT)	
	PIC24FJ128GA010	R	85	PIC24	128	8192	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	–	16	–	2	–	5	5	5	2 UART, 2 SPI, 2 I ² C	–	✓	✓	–	\$3.81	BOR, POR, WDT	TQFP (PT)	
	PIC24FJ128GA110	R	85	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.03	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ64GB110	R	84	PIC24	64	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.12	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ192GA110	R	85	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.24	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ128GB110	R	84	PIC24	128	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	16 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.41	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ256GA110	R	85	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	–	✓	✓	✓	\$4.45	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ192GB110	R	84	PIC24	192	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.62	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ128GB210	R	84	PIC24	128	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.79	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ128DA110	R	84	PIC24	128	24576	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.83	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ256GB110	R	84	PIC24	256	16384	AN1095 ⁽¹⁾	–	2V-3.6V	16	8 MHz, 32 kHz	✓	16	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$4.83	BOR, LVD, POR, WDT	TQFP (PT)	
	PIC24FJ256GB210	R	84	PIC24	256	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	–	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.14	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ256DA110	R	84	PIC24	256	24576	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.18	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ128DA210	R	84	PIC24	128	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.25	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	
	PIC24FJ256DA210	R	84	PIC24	256	98304	AN1095 ⁽¹⁾	–	2.2V-3.6V	16	8 MHz, 32 kHz	✓	24	–	3	✓	9	9	5	4 UART, 3 SPI, 3 I ² C	✓	✓	✓	✓	\$5.60	BOR, LVD, POR, WDT	TQFP (PT), BGA121 (BG)	

*Parts available with High Temperature options (150°C).

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

2: Two 16-bit timers can be concatenated to form a 32-bit timer.

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

◊ - Software PLVD implemented via ADC.

16-bit PIC® Microcontrollers (PIC24H)

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory				Voltage Range	Operating Speed		Analog Sensing & Measurement				Output Compare/PWM	Input Capture	16-bit Timer ⁽²⁾	Communication				PMP	RTCC/CRC	PPS	5-ku Pricing [†]	Monitors		Packages (Designator)
					Program KB	Data RAM (B)	EEPROM	DMA #Ch		Maximum MIPS	Internal Oscillator	Charge Time Measurement Unit	10-bit ADC	10/12-bit ADC 1100/500 KSPS	Comparators				Digital Communication	CAN	FS USB OTG	System Mgmt. Features							
18-Pin	PIC24HJ12GP201	R	13	PIC24	12	1024	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	6 ch	–	2	4	3	1 UART, 1 SPI, 1 I ² C	–	–	–	–	✓	\$2.09	PBOR, POR, WDT	PDIP (P), SOIC (SO)	18-Pin	
	PIC24HJ12GP202	R	21	PIC24	12	1024	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	10 ch	–	2	4	3	1 UART, 1 SPI, 1 I ² C	–	–	–	–	✓	\$2.24	PBOR, POR, WDT	SOIC (SO), SPDIP (SP), QFN (MM), SSOP (SS)		
28-Pin	PIC24HJ32GP202*	R	21	PIC24	32	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	10 ch	–	2	4	3	1 UART, 1 SPI, 1 I ² C	–	–	–	–	✓	\$2.40	PBOR, POR, WDT	SOIC (SO), SPDIP (SP), QFN (MM)	28-Pin	
	PIC24HJ32GP302	R	21	PIC24	32	4096	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	10 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	–	–	✓	✓	✓	\$2.76	PBOR, POR, WDT	SOIC (SO), SPDIP (SP), QFN (MM)		
	PIC24HJ36GP202	R	21	PIC24	64	4096	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	10 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	–	–	✓	✓	✓	\$3.12	PBOR, POR, WDT	SOIC (SO), SPDIP (SP), QFN (MM)		
	PIC24HJ36GP502*	R	21	PIC24	64	4096	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	10 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	1	–	✓	✓	✓	\$3.33	PBOR, POR, WDT	SOIC (SO), SPDIP (SP), QFN (MM)		
	PIC24HJ128GP202	R	21	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	10 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	–	–	✓	✓	✓	\$3.44	PBOR, POR, WDT	SOIC (SO), SPDIP (SP), QFN (MM)		
	PIC24HJ128GP502*	R	21	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	10 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	1	–	✓	✓	✓	\$3.65	PBOR, POR, WDT	SOIC (SO), SPDIP (SP), QFN (MM)		
	PIC24HJ16GP304*	R	35	PIC24	16	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	13 ch	–	2	4	3	1 UART, 1 SPI, 1 I ² C	–	–	–	–	✓	\$2.42	PBOR, POR, WDT	TQFP (PT), QFN (ML)		
44-Pin	PIC24HJ32GP204*	R	35	PIC24	32	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	13 ch	–	2	4	3	1 UART, 1 SPI, 1 I ² C	–	–	–	–	✓	\$2.49	PBOR, POR, WDT	TQFP (PT), QFN (ML)	44-Pin	
	PIC24HJ32GP304	R	35	PIC24	32	4096	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	13 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	–	–	✓	✓	✓	\$2.82	PBOR, POR, WDT	TQFP (PT), QFN (ML)		
	PIC24HJ36GP204	R	35	PIC24	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	13 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	–	–	✓	✓	✓	\$3.29	PBOR, POR, WDT	TQFP (PT), QFN (ML)		
	PIC24HJ36GP504*	R	35	PIC24	64	4096	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	13 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	1	–	✓	✓	✓	\$3.58	PBOR, POR, WDT	TQFP (PT), QFN (ML)		
	PIC24HJ128GP204	R	35	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	13 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	–	–	✓	✓	✓	\$3.58	PBOR, POR, WDT	TQFP (PT), QFN (ML)		
	PIC24HJ128GP504*	R	35	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	13 ch	2	4	4	5	2 UART, 2 SPI, 1 I ² C	1	–	✓	✓	✓	\$3.88	PBOR, POR, WDT	TQFP (PT), QFN (ML)		
	PIC24HJ64GP206A	R	53	PIC24	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	18 ch	–	8	8	9	2 UART, 2 SPI, 1 I ² C	–	–	–	–	–	\$3.39	PBOR, POR, WDT	TQFP (PT), QFN (MR)		
64-Pin	PIC24HJ64GP506A	R	53	PIC24	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	18 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	–	\$3.60	PBOR, POR, WDT	TQFP (PT), QFN (MR)	64-Pin	
	PIC24HJ128GP206A	R	53	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	18 ch	–	8	8	9	2 UART, 2 SPI, 1 I ² C	–	–	–	–	–	\$3.63	PBOR, POR, WDT	TQFP (PT), QFN (MR)		
	PIC24HJ128GP306A	R	53	PIC24	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	18 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	–	\$3.79	PBOR, POR, WDT	TQFP (PT), QFN (MR)		
	PIC24HJ128GP506A*	R	53	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	18 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	–	\$3.85	PBOR, POR, WDT	TQFP (PT), QFN (MR)		
	PIC24HJ256GP206A*	R	53	PIC24	256	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	18 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	–	\$4.05	PBOR, POR, WDT	TQFP (PT, PF)		
	PIC24HJ64GP210A	R	85	PIC24	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	32 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	–	\$3.88	PBOR, POR, WDT	TQFP (PT, PF)		
100-Pin	PIC24HJ64GP510A	R	85	PIC24	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	32 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	–	\$4.06	PBOR, POR, WDT	TQFP (PT, PF)	100-Pin	
	PIC24HJ128GP210A	R	85	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	32 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	–	\$4.14	PBOR, POR, WDT	TQFP (PT, PF)		
	PIC24HJ128GP310A	R	85	PIC24	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	32 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	–	\$4.26	PBOR, POR, WDT	TQFP (PT, PF)		
	PIC24HJ128GP510A*	R	85	PIC24	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	32 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	–	\$4.31	PBOR, POR, WDT	TQFP (PT, PF)		
	PIC24HJ256GP210A	R	85	PIC24	256	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	32 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	–	\$4.63	PBOR, POR, WDT	TQFP (PT, PF)		
	PIC24HJ256GP610A*	R	85	PIC24	256	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	–	–	2 ADC 32 ch	–	8	8	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	–	\$5.08	PBOR, POR, WDT	TQFP (PT, PF)		

*Parts available with High Temperature options (150°C).

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

2: Two 16-bit timers can be concatenated to form a 32-bit timer.

32-bit PIC32 Microcontrollers

Product	Released (R) Not Released (NR)	Core	Memory			DMA Channels General/Dedicated	Voltage Range	Operating Speed		Analog		I/O/C/PWM	Timers 16/32-bit	Communication						PMP	RTCC	5 ku Pricing*	Monitors	Packages (Designator)	
			Flash KB + Boot Flash	Data RAM (KB)	EEPROM			Maximum Speed MHz	Internal Oscillator	ADC 10-bit 1000 kbps	Comparators			SPI	I ² C™	UARTs	FS USB OTG	Ethernet	CAN				System Mgmt. Features		
64-Pin	PIC32MX320F032H	R	PIC32	32 + 12	8	AN1095 ⁽¹⁾	0/0	2.3V-3.6V	40	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$3.09	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX320F064H	R	PIC32	64 + 12	16	AN1095 ⁽¹⁾	0/0	2.3V-3.6V	40	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$3.36	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX420F032H	R	PIC32	32 + 12	8	AN1095 ⁽¹⁾	0/2	2.3V-3.6V	40	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	✓	–	–	✓	1	\$3.36	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX320F064H	R	PIC32	64 + 12	16	AN1095 ⁽¹⁾	0/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$3.51	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX320F128H	R	PIC32	128 + 12	16	AN1095 ⁽¹⁾	0/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$3.75	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX340F128H	R	PIC32	128 + 12	32	AN1095 ⁽¹⁾	4/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$3.96	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX440F128H	R	PIC32	128 + 12	32	AN1095 ⁽¹⁾	4/2	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	✓	–	–	✓	1	\$4.23	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX340F256H	R	PIC32	256 + 12	32	AN1095 ⁽¹⁾	4/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$4.31	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX440F256H	R	PIC32	256 + 12	32	AN1095 ⁽¹⁾	4/2	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	✓	–	–	✓	1	\$4.58	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX340F512H	R	PIC32	512 + 12	32	AN1095 ⁽¹⁾	4/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$4.77	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX575F256H	R	PIC32	256 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	–	1	✓	1	\$4.96	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX440F512H	R	PIC32	512 + 12	32	AN1095 ⁽¹⁾	4/2	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	✓	–	–	✓	1	\$5.04	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX675F256H	R	PIC32	256 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	–	✓	1	\$5.19	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX575F512H	R	PIC32	512 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	–	1	✓	1	\$5.42	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX775F256H	R	PIC32	256 + 12	64	AN1095 ⁽¹⁾	8/8	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	2	✓	1	\$5.42	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX675F512H	R	PIC32	512 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	–	✓	1	\$5.66	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX775F512H	R	PIC32	512 + 12	64	AN1095 ⁽¹⁾	8/8	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	2	✓	1	\$5.88	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX695F512H	R	PIC32	512 + 12	128	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	–	✓	1	\$6.13	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX795F512H	R	PIC32	512 + 12	128	AN1095 ⁽¹⁾	8/8	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	2	✓	1	\$6.36	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
	PIC32MX534F064H	NR	PIC32	64 + 12	16	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	–	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)
PIC32MX564F064H	NR	PIC32	64 + 12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	–	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)	
PIC32MX564F128H	NR	PIC32	128 + 12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	–	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)	
PIC32MX664F064H	NR	PIC32	64 + 12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	–	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)	
PIC32MX664F128H	NR	PIC32	128 + 12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	–	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)	
PIC32MX764F128H	NR	PIC32	128 + 12	32	AN1095 ⁽¹⁾	4/6	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	3	4	6	✓	10/100	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT), QFN (MR)	
100-Pin	PIC32MX320F128L	R	PIC32	128 + 12	16	AN1095 ⁽¹⁾	0/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$4.44	POR, BOR, LVD, WDT	TQFP (PT), XBGA (BG)
	PIC32MX340F128L	R	PIC32	128 + 12	32	AN1095 ⁽¹⁾	4/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$4.44	POR, BOR, LVD, WDT	TQFP (PT), XBGA (BG)
	PIC32MX440F128L	R	PIC32	128 + 12	32	AN1095 ⁽¹⁾	4/2	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	✓	–	–	✓	1	\$4.70	POR, BOR, LVD, WDT	TQFP (PT), XBGA (BG)
	PIC32MX360F256L	R	PIC32	256 + 12	32	AN1095 ⁽¹⁾	4/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$4.79	POR, BOR, LVD, WDT	TQFP (PT), XBGA (BG)
	PIC32MX460F256L	R	PIC32	256 + 12	32	AN1095 ⁽¹⁾	4/2	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	✓	–	–	✓	1	\$5.05	POR, BOR, LVD, WDT	TQFP (PT), XBGA (BG)
	PIC32MX360F512L	R	PIC32	512 + 12	32	AN1095 ⁽¹⁾	4/0	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	–	–	–	✓	1	\$5.25	POR, BOR, LVD, WDT	TQFP (PT), XBGA (BG)
	PIC32MX575F256L	R	PIC32	256 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	–	1	✓	1	\$5.43	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)
	PIC32MX460F512L	R	PIC32	512 + 12	32	AN1095 ⁽¹⁾	4/2	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	2	2	2	✓	–	–	✓	1	\$5.52	POR, BOR, LVD, WDT	TQFP (PT), XBGA (BG)
	PIC32MX675F256L	R	PIC32	256 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	–	✓	1	\$5.67	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)
	PIC32MX575F512L	R	PIC32	512 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	–	1	✓	1	\$5.89	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)
	PIC32MX775F256L	R	PIC32	256 + 12	64	AN1095 ⁽¹⁾	8/8	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	2	✓	1	\$5.89	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

32-bit PIC32 Microcontrollers

Product		Released (R) Not Released (NR)	Core	Memory			DMA Channels General/Dedicated	Voltage Range	Operating Speed		Analog		I/O/C/PWM	Timers 16/32-bit	Communication						PMP	RTCC	5 ku Pricing [†]	Monitors	Packages (Designator)	
				Flash KB + Boot Flash	Data RAM (KB)	EEPROM			Maximum Speed MHz	Internal Oscillator	ADC 10-bit 1000 kps	Comparators			SPI	I ² C™	UARTs	FS USB OTG	Ethernet	CAN				System Mgmt. Features		
100-Pin (Cont.)	PIC32MX675F512L	R	PIC32	512 + 12	64	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	–	✓	1	\$6.13	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	100-Pin (Cont.)
	PIC32MX775F512L	R	PIC32	512 + 12	64	AN1095 ⁽¹⁾	8/8	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	2	✓	1	\$6.36	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX695F512L	R	PIC32	512 + 12	128	AN1095 ⁽¹⁾	8/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	–	✓	1	\$6.61	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX795F512L	R	PIC32	512 + 12	128	AN1095 ⁽¹⁾	8/8	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	2	✓	1	\$6.83	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX534F064L	NR	PIC32	64+12	16	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	–	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX564F064L	NR	PIC32	64+12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	–	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX564F128L	NR	PIC32	128+12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	–	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX664F064L	NR	PIC32	64+12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	–	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX664F128L	NR	PIC32	128+12	32	AN1095 ⁽¹⁾	4/4	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	–	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	
	PIC32MX764F128L	NR	PIC32	128+12	32	AN1095 ⁽¹⁾	4/6	2.3V-3.6V	80	8 MHz, 32 kHz	16 ch	2	5/5/5	5/1	4	5	6	✓	10/100	1	✓	1	Call for Pricing	POR, BOR, LVD, WDT	TQFP (PT, PF), XBGA (BG)	

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

dsPIC30F DSC Families

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory			Voltage Range	Operating Speed		Analog			Output Compare/PWM	Input Capture	Motor Control PWM Ch	Power Supply PWM Ch	QEI	Codec (FS, AC97)	16-bit Timer ⁽¹⁾	Communication		5 ku Pricing [†]	Monitors	Packages (Designator)	
					Program KB	Data RAM (B)	EEPROM		Maximum Speed MIPS	Internal Oscillator	ADC	DAC	Comparators								Digital Communication	CAN		System Mgmt. Features		
18-Pin	dsPIC30F3012	R	12	dsPIC	24	2048	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	8 x 12-bit @ 200 (ksps)	–	–	2	2	–	–	–	–	3	1 UART, 1 SPI, 1 I ² C	–	\$2.68	PBOR, LVD, POR, WDT	PDIP (P), SOIC (SO), QFN (ML)	18-Pin
28-Pin	dsPIC30F2010	R	20	dsPIC	12	512	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	6 x 10-bit @ 1000 (ksps)	–	–	2	4	6	–	1	–	3	1 UART, 1 SPI, 1 I ² C	–	\$2.43	PBOR, LVD, POR, WDT	SOIC (SO), SPDIP (SP), QFN (ML), PDIP (P)	28-Pin
	dsPIC30F3013	R	20	dsPIC	24	2048	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	10 x 12-bit @ 200 (ksps)	–	–	2	2	–	–	–	–	3	2 UART, 1 SPI, 1 I ² C	–	\$2.77	PBOR, LVD, POR, WDT	SOIC (SO), SPDIP (SP), QFN (ML)	
	dsPIC30F4012	R	20	dsPIC	48	2048	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	6 x 10-bit @ 1000 (ksps)	–	–	2	4	6	–	1	–	5	1 UART, 1 SPI, 1 I ² C	1	\$3.71	PBOR, LVD, POR, WDT	SOIC (SO), SPDIP (SP), QFN (ML)	
40-Pin	dsPIC30F4013	R	30	dsPIC	48	2048	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	13 x 12-bit @ 200 (ksps)	–	–	4	4	–	–	–	1	5	2 UART, 1 SPI, 1 I ² C	1	\$3.91	PBOR, LVD, POR, WDT	PDIP (P), TQFP (PT), QFN (ML)	40-Pin
	dsPIC30F4011	R	30	dsPIC	48	2048	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	9 x 10-bit @ 1000 (ksps)	–	–	4	4	6	–	1	–	5	2 UART, 1 SPI, 1 I ² C	1	\$4.02	PBOR, LVD, POR, WDT	PDIP (P), TQFP (PT), QFN (ML)	
64-Pin	dsPIC30F5015	R	52	dsPIC	66	2048	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	16 x 10-bit @ 1000 (ksps)	–	–	4	4	8	–	1	–	5	1 UART, 2 SPI, 1 I ² C	1	\$5.08	PBOR, LVD, POR, WDT	TQFP (PT)	64-Pin
	dsPIC30F6011A	R	52	dsPIC	132	6144	2048	2.5V-5.5V	30	7.37 MHz, 32 kHz	16 x 12-bit @ 200 (ksps)	–	–	8	8	–	–	–	5	2 UART, 2 SPI, 1 I ² C	2	\$6.89	PBOR, LVD, POR, WDT	TQFP (PT)		
80-Pin	dsPIC30F5016	R	68	dsPIC	66	2048	1024	2.5V-5.5V	30	7.37 MHz, 32 kHz	16 x 10-bit @ 1000 (ksps)	–	–	4	4	8	–	1	–	5	1 UART, 2 SPI, 1 I ² C	1	\$5.59	PBOR, LVD, POR, WDT	TQFP (PF)	80-Pin
	dsPIC30F6014A	R	68	dsPIC	144	8192	4096	2.5V-5.5V	30	7.37 MHz, 32 kHz	16 x 12-bit @ 200 (ksps)	–	–	8	8	–	–	1	5	2 UART, 2 SPI, 1 I ² C	2	\$7.25	PBOR, LVD, POR, WDT	TQFP (PF)		
	dsPIC30F6010A	R	68	dsPIC	144	8192	4096	2.5V-5.5V	30	7.37 MHz, 32 kHz	16 x 10-bit @ 1000 (ksps)	–	–	8	8	8	–	1	–	5	2 UART, 2 SPI, 1 I ² C	2	\$7.36	PBOR, LVD, POR, WDT	TQFP (PF)	

Note 1: Two 16-bit timers can be concatenated to form a 32-bit timer.

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

dsPIC33 DSC General Purpose Family

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory				Voltage Range	Operating Speed		Analog			Output Compare/PWM	Input Capture	Codec (I ² S, AC97)	16-bit Timer ⁽²⁾	Communication		PMP	RTCC/CRC	PPS	5 ku Pricing [†]	Monitors	Packages (Designator)	
					Program KB	Data RAM (B)	EEPROM	DMA #Ch		Maximum Speed MIPS	Internal Oscillator	ADC 10/12-bit 1100/500 ksp/s	DAC	Comparators					Digital Communication	CAN					System Mgmt. Features		
18-Pin	dsPIC33FJ12GP201	R	13	dsPIC*	12	1024	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.09	PBOR, POR, WDT	PDIP (P), SOIC (SO)	18-Pin
	dsPIC33FJ12GP202	R	21	dsPIC	12	1024	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	10 ch	–	–	2	4	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.24	PBOR, POR, WDT	QFN (MM), SOIC(SO), SPDIP (SP), SSOP (SS)	
	dsPIC33FJ32GP202	R	21	dsPIC	32	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	10 ch	–	–	2	4	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.56	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
28-Pin	dsPIC33FJ32GP302	R	21	dsPIC	32	4096	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	10 ch	–	2	4	4	–	5	2 UART, 2 SPI, 1 I ² C	–	–	–	✓	\$2.76	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	28-Pin
	dsPIC33FJ64GP202	R	21	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	10 ch	–	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	–	✓	–	✓	\$3.12	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ64GP802*	R	21	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	10 ch	2 x 16-bit @ 100 (ksps)	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$3.42	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ128GP202	R	21	dsPIC	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	10 ch	–	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	–	✓	✓	✓	\$3.44	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ128GP802	R	21	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	10 ch	2 x 16-bit @ 100 (ksps)	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$3.72	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ16GP304	R	35	dsPIC	16	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	13 ch	–	–	2	4	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.58	BOR, POR, WDT	QFN (ML), TQFP (PT)	
44-Pin	dsPIC33FJ32GP204*	R	35	dsPIC	32	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	13 ch	–	–	2	4	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.66	PBOR, POR, WDT	QFN (ML), TQFP (PT)	44-Pin
	dsPIC33FJ32GP304	R	35	dsPIC	32	4096	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	13 ch	–	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	–	–	–	✓	\$3.01	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ64GP204	R	35	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	13 ch	–	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	–	✓	–	✓	\$3.29	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ128GP204	R	35	dsPIC	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	13 ch	–	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	–	✓	✓	✓	\$3.58	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ64GP804	R	35	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	13 ch	2 x 16-bit @ 100 (ksps)	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$3.65	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ128GP804*	R	35	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	13 ch	2 x 16-bit @ 100 (ksps)	2	4	4	1	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$3.96	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ64GP206A	R	53	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch	–	–	8	8	1	9	2 UART, 2 SPI, 1 I ² C	–	–	–	–	\$3.39	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
64-Pin	dsPIC33FJ64GP306A	R	53	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	\$3.53	PBOR, POR, WDT	QFN (MR), TQFP (PT)	64-Pin
	dsPIC33FJ128GP206A	R	53	dsPIC	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch	–	–	8	8	1	9	2 UART, 2 SPI, 1 I ² C	–	–	–	–	\$3.63	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ128GP306A	R	53	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	\$3.79	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ64GP706A	R	53	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch 2 ADC	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$4.14	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ256GP506A*	R	53	dsPIC	256	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.20	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ128GP706A*	R	53	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch 2 ADC	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$4.40	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
80-Pin	dsPIC33FJ64GP708A	R	69	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch 2 ADC	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$4.44	PBOR, POR, WDT	TQFP (PT)	80-Pin
	dsPIC33FJ128GP708A	R	69	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch 2 ADC	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$4.69	PBOR, POR, WDT	TQFP (PT)	
100-Pin	dsPIC33FJ64GP310A	R	85	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	32 ch	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	\$3.99	PBOR, POR, WDT	TQFP (PT, PF)	100-Pin
	dsPIC33FJ128GP310A	R	85	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	32 ch	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	–	–	–	–	\$4.26	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ64GP710A	R	85	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	32 ch 2 ADC	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$4.61	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ256GP510A	R	85	dsPIC	256	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	32 ch	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.66	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ128GP710A*	R	85	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	32 ch 2ADC	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$4.86	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ256GP710A*	R	85	dsPIC	256	30720	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	32 ch 2 ADC	–	–	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$5.32	PBOR, POR, WDT	TQFP (PT, PF)	

*Parts available with High Temperature options (150°C).

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

2: Two 16-bit timers can be concatenated to form a 32-bit timer.

dsPIC33 DSC Motor Control and Power Conversion Family

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory				Operating Speed		Analog			Output Compare/PWM	Input Capture	Motor Control PWM Ch	QEI	16-bit Timer ⁽²⁾	Communication		PMP	RTCC/CRC	PPS	5 ku Pricing [†]	Monitors	Packages (Designator)		
					Program KB	Data RAM (B)	EEPROM	DMA #Ch	Voltage Range	Maximum Speed MIPS	Internal Oscillator	ADC 10/12-bit 1100/500 ksp/s	DAC						Comparators	Digital Communication					CAN		System Mgmt. Features	
20-Pin	dsPIC33FJ12MC201	R	15	dsPIC*	12	1024	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	4 ch	–	–	2	4	8	1	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.09	PBOR, POR, WDT	PDIP (P), SOIC (SO), SSOP (SS)	
	dsPIC33FJ12MC202	R	21	dsPIC	12	1024	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	6+2	1	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.31	PBOR, POR, WDT	QFN (MM), SOIC(SO), SPDIP (SP), SSOP (SS)	
28-Pin	dsPIC33FJ32MC202*	R	21	dsPIC	32	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	6+2	1	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.63	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ32MC302	R	21	dsPIC	32	4096	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	–	✓	–	✓	\$2.87	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ64MC202	R	21	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	–	✓	✓	✓	\$3.29	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ64MC802*	R	21	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$3.50	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ128MC202	R	21	dsPIC	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	–	✓	✓	✓	\$3.57	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ128MC802*	R	21	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	2	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$3.82	PBOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)	
	dsPIC33FJ16MC304*	R	35	dsPIC	16	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	9 ch	–	–	2	4	6+2	1	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.65	BOR, POR, WDT	QFN (ML), TQFP (PT)	
44-Pin	dsPIC33FJ32MC204*	R	35	dsPIC	32	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	9 ch	–	–	2	4	6+2	1	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.76	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ32MC304	R	35	dsPIC	32	4096	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	9 ch	–	–	2	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	–	✓	–	✓	\$3.12	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ64MC204	R	35	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	9 ch	–	–	2	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	–	✓	✓	✓	\$3.39	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ128MC204	R	35	dsPIC	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	9 ch	–	–	2	4	8	2	5	2 UART, 2 SPI, 1 I ² C	–	✓	✓	✓	\$3.68	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ64MC804*	R	35	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	9 ch	2 x 16-bit @ 100 (ksps)	–	2	4	4	6+2	2	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$3.89	PBOR, POR, WDT	QFN (ML), TQFP (PT)
	dsPIC33FJ128MC804*	R	35	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	9 ch	2 x 16-bit @ 100 (ksps)	–	2	4	8	2	5	2 UART, 2 SPI, 1 I ² C	1	✓	✓	✓	\$4.23	PBOR, POR, WDT	QFN (ML), TQFP (PT)	
	dsPIC33FJ64MC506A*	R	53	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$3.84	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
64-Pin	dsPIC33FJ128MC506A*	R	53	dsPIC	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.10	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ64MC706A	R	53	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch 2 ADC	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.21	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ128MC706A*	R	53	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.3V	40	7.37 MHz, 32 kHz	16 ch 2 ADC	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.49	PBOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ64MC508A	R	69	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.14	PBOR, POR, WDT	TQFP (PT)	
100-Pin	dsPIC33FJ128MC708A	R	69	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch 2 ADC	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$5.00	PBOR, POR, WDT	TQFP (PT)	
	dsPIC33FJ64MC510A	R	85	dsPIC	64	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.33	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ128MC510A	R	85	dsPIC	128	8192	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.59	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ64MC710A	R	85	dsPIC	64	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch 2 ADC	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$4.91	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ256MC510A	R	85	dsPIC	256	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	1	–	–	–	\$4.97	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ128MC710A*	R	85	dsPIC	128	16384	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch 2 ADC	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$5.18	PBOR, POR, WDT	TQFP (PT, PF)	
	dsPIC33FJ256MC710A*	R	85	dsPIC	256	30720	AN1095 ⁽¹⁾	8	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch 2 ADC	–	–	8	8	8	1	9	2 UART, 2 SPI, 2 I ² C	2	–	–	–	\$5.67	PBOR, POR, WDT	TQFP (PT, PF)	

*Parts available with High Temperature options (150°C).

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

2: Two 16-bit timers can be concatenated to form a 32-bit timer.

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

dsPIC33 DSC SMPS and Digital Power Conversion Family

Product		Released (R) Not Released (NR)	I/O Pins	Core	Memory				Voltage Range	Operating Speed		Analog			Output Compare/PWM	Input Capture	Power Supply PWM Ch ⁽¹⁾	QEI	16-bit Timer ⁽²⁾	Communication		PMP	RTCC	PPS	5 ku Pricing [†]	Monitors	Packages (Designator)	
					Program KB	Data RAM (B)	EEPROM	DMA #Ch		Maximum Speed MIPS	Internal Oscillator	ADC 10-bit 2000/4000 ksps	DAC	Comparators						Digital Communication	CAN					System Mgmt. Features		
18-Pin	dsPIC33FJ06GS101	R	13	dsPIC*	6	256	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	1	–	4	–	2	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$1.96	BOR, POR, WDT	SOIC (SO)	18-Pin
	dsPIC33FJ06GS102	R	21	dsPIC	6	256	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	–	–	1	–	4	–	2	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.20	BOR, POR, WDT	QFN (MM), SOIC(SO), SPDIP (SP)	28-Pin
dsPIC33FJ06GS202	R	21	dsPIC	6	1024	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	6 ch	2 x 10-bit	2	1	1	4	–	2	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.38	BOR, POR, WDT	QFN (MM), SOIC(SO), SPDIP (SP)		
dsPIC33FJ16GS402	R	21	dsPIC	16	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	8 ch	–	–	2	2	6	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.52	BOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)		
dsPIC33FJ16GS502	R	21	dsPIC	16	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	8 ch, 2 ADC*	4 x 10-bit	4	2	2	8	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$3.04	BOR, POR, WDT	QFN (MM), SOIC (SO), SPDIP (SP)		
44-Pin	dsPIC33FJ16GS404	R	35	dsPIC	16	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	8 ch	–	–	2	2	6	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$2.77	BOR, POR, WDT	QFN (ML), TQFP (PT)	44-Pin
	dsPIC33FJ16GS504	R	35	dsPIC	16	2048	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	12 ch, 2 ADC*	4 x 10-bit	4	2	2	8	–	3	1 UART, 1 SPI, 1 I ² C	–	–	–	✓	\$3.42	BOR, POR, WDT	QFN (ML), TQFP (PT)	
64-Pin	dsPIC33FJ32GS406	R	58	dsPIC	32	4096	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch	–	–	4	4	12	1	5	2 UART, 2 SPI, 2 I ² C	–	–	–	–	Call for Pricing	BOR, POR, WDT	QFN (MR), TQFP (PT)	64-Pin
	dsPIC33FJ64GS406	R	58	dsPIC	64	8192	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch	–	–	4	4	12	1	5	2 UART, 2 SPI, 2 I ² C	–	–	–	–	Call for Pricing	BOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ32GS606	R	58	dsPIC	32	4096	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch, 2 ADC*	4 x 10-bit	4	4	4	12	2	5	2 UART, 2 SPI, 2 I ² C	–	–	–	–	Call for Pricing	BOR, POR, WDT	QFN (MR), TQFP (PT)	
	dsPIC33FJ64GS606	R	58	dsPIC	64	9216	AN1095 ⁽¹⁾	4	3V-3.6V	40	7.37 MHz, 32 kHz	16 ch, 2 ADC*	4 x 10-bit	4	4	4	12	2	5	2 UART, 2 SPI, 2 I ² C	1	–	–	–	Call for Pricing	BOR, POR, WDT	QFN (MR), TQFP (PT)	
80-Pin	dsPIC33FJ32GS608	R	74	dsPIC	32	4096	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch, 2 ADC*	4 x 10-bit	4	4	4	16	2	5	2 UART, 2 SPI, 2 I ² C	–	–	–	–	Call for Pricing	BOR, POR, WDT	TQFP (PT)	80-Pin
	dsPIC33FJ64GS608	R	74	dsPIC	64	9216	AN1095 ⁽¹⁾	4	3V-3.6V	40	7.37 MHz, 32 kHz	18 ch, 2 ADC*	4 x 10-bit	4	4	4	16	2	5	2 UART, 2 SPI, 2 I ² C	1	–	–	–	Call for Pricing	BOR, POR, WDT	TQFP (PT)	
100-Pin	dsPIC33FJ32GS610	R	85	dsPIC	32	4096	AN1095 ⁽¹⁾	–	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch, 2 ADC*	4 x 10-bit	4	4	4	18	2	5	2 UART, 2 SPI, 2 I ² C	–	–	–	–	Call for Pricing	BOR, POR, WDT	TQFP (PF, PT)	100-Pin
	dsPIC33FJ64GS610	R	85	dsPIC	64	9216	AN1095 ⁽¹⁾	4	3V-3.6V	40	7.37 MHz, 32 kHz	24 ch, 2 ADC*	4 x 10-bit	4	4	4	18	2	5	2 UART, 2 SPI, 2 I ² C	1	–	–	–	Call for Pricing	BOR, POR, WDT	TQFP (PF, PT)	

*Parts available with High Temperature options (150°C).

Note 1: See Application Note "AN1095 - Emulating Data EEPROM".

2: Two 16-bit timers can be concatenated to form a 32-bit timer.

Thermal Management – Temperature Sensors

Product	Typical Accuracy (°C)	Max. Accuracy @ 25°C (°C)	Max. Temperature Range (°C)	Vcc Range (V)	Max. Op Current (µA)	Features	Packages
MCP9501/2/3/4	±0.5	±3	-55 to +125	+2.7 to +5.5	40	Cross to MAX6501/2/3/4, Open-drain and push-pull output options	SOT-23A
MCP9509/10	±0.5	NS	-40 to +125	+2.7 to +5.5	50	Resistor-programmable temperature switch	SOT-23A
MCP9700/01	±1	±4	-40 to +125	+2.3 to +5.5	12	Linear Active Thermistor® IC	SOT-23A, TO-92, SC70
MCP9700/01A	±1	±2	-40 to +125	+2.3 to +5.5	12	Linear Active Thermistor® IC	SOT-23A, TO-92, SC70
TC1046	±0.5	±2	-40 to +125	+2.7 to +4.4	60	High precision temperature-to-voltage converter, 6.25 mV/°C	SOT-23A
TC1047A	±0.5	±2	-40 to +125	+2.5 to +5.5	60	High precision temperature-to-voltage converter, 10 mV/°C	SOT-23A
MCP9800/1/2/3	±0.5	±1	-55 to +125	+2.7 to +5.5	400	SMbus/I ² C™ compatible interface, 0.0625°C to 0.5°C adj. resolution, power-saving one-shot temperature measurement	SOIC, MSOP, SOT-23A
MCP9804	±0.25	±1	-40 to +125	+2.7 to +5.5	400	User programmable temperature limits with alert output, 1°C temp. accuracy from -40°C to +125°C	MSOP, DFN
MCP9843	±0.5	±1	-20 to +125	+3.0 to +3.6	400	JEDEC compatible register set, SMbus/I ² C™ compatible interface, programmable, shut-down modes and EVENT output	TSSOP, DFN
MCP98243	±1	±3	-40 to +125	+3.0 to +3.6	500	Serial output temperature sensor with integrated EEPROM	TSSOP, DFN, TDFN
TCN75A	±0.5	±2	-40 to +125	+2.7 to +5.5	500	SMbus/I ² C™ compatible interface, power-saving one-shot temperature measurement, multi-drop capability, 0.0625°C to 0.5°C adjustable temperature resolution	SOIC, MSOP

Power Management – Switching Regulators/PWM Controllers

Product	Input Voltage Range (V)	Output Voltage (V)	Operating Temperature Range (°C)	Control Scheme	Switching Frequency (kHz)	Typical Active Current (µA)	Output Current (mA)	Features	Packages
MCP1630/V 1631/V	3.0 to 5.5	–	-40 to +125	PWM	1000/2000	2800/3700	Ext	Current/Voltage mode PWM controller, UVLO, Short Circuit and Over-temperature Protection, Integrated MOSFET driver	MSOP, SSOP, TSSOP, DFN
MCP1631HV/VHV	3.5 to 16	–	-40 to +125	PWM	2000	3700	Ext	Current/Voltage mode PWM controller with integrated 16V LDO, UVLO, Integrated error, current and voltage sense amplifier, overvoltage comparator and MOSFET driver	SSOP, TSSOP
TC1303/04/13	2.7 to 5.5	DC/DC: 0.8 to 4.5 LDO: 1.5 to 3.3	-40 to +85	PFM/PWM	2000	65/600	DC/DC: 500 mA LDO: 300 mA	Synchronous Buck Regulator, LDO w/Power Good with PFM/PWM auto-switching, Power Good output or Power Sequencing	MSOP, DFN
MCP1602/3	2.7 to 5.5	0.8 to 4.5 /4.0	-40 to +85	PFM/PWM	2000	35/45	500	Synchronous Buck Regulator PFM, PWM auto-switching, UVLO, soft start, Power Good indicator, Over-temperature/current protection	MSOP, DFN, TSOT
MCP1640/B/C/D	0.65 to 6	2.0 to 5.5	-40 to +85	PWM or PWM/PFM	500	19	350	Integrated synchronous boost regulator, -65V start-up voltage, soft-start, True load disconnect or input-to-output bypass option	SOT-23, DFN
MCP1650/1/2/3	2.7 to 5.5	2.5 to ext. tx limited	-40 to +125	Constant Frequency	750	120	560/440	Step-up DC/DC Controller with shutdown control, low battery detect, Power Good indicator, UVLO, soft start	MSOP

Power Management – Linear Regulators

Product	Max. Input Voltage (V)	Output Voltage (V)	Output Current (mA)	Typical Active Current (µA)	Typical Dropout Voltage @ Max. I _{OUT} (mV)	Typical Output Voltage Accuracy (%)	Features	Packages
TC1016/17	6	1.8 to 4.0	80/150	53	150/285	±0.5	Shutdown	SOT-23A, SC70
TC2014/5, TC2185	6	1.8 to 5.0	50/100/150	55	45/90/140	±0.4	Shutdown, Reference bypass input	SOT-23A
TC2054/5, TC2186	6	1.8 to 5.0	50/100/150	55	45/90/140	±0.4	Shutdown, Error output	SOT-23A
MCP1790/1	30	3.0, 3.3, 5.0	70	70	500	±0.2	Load dump, Shutdown, PowerGood	SOT-223, DDPK
MCP1801/2	10	0.9 to 6.0	150/300	25	250/800	±0.4	Shutdown, High PSRR	SOT-23A
MCP1804	28	1.8 to 18	150	50	300	±0.5	Shutdown, High PSRR	SOT-23, SOT-89, SOT-223
MCP1700	6	1.2 to 5.0	250	1.6	300	±0.4	Very low I _Q	SOT-23A, SOT-89, TO-92
MCP1702/3	13.2/16	1.2 to 5.0	250	2	330/625	±0.4	Very low I _Q	DFN, TO-92, SOT-23A, SOT-89, SOT-223
MCP1824/5/6/7	6	0.8 to 5.0	300/500/1000/1500	120/120/140/140	200/210/300/330	±0.5	Fixed and Adjustable output, Shutdown, Power Good	SOT-23, SOT-223, TO-220, DDPK
MCP1824S/5S/6S/7S	6	0.8 to 5.0	300/500/1000/1500	120/120/140/140	200/210/300/330	±0.5	3-pin high current LDOs	SOIC, DFN, SOT-223, TO-220, DDPK
MCP1725/6/7	6	0.8 to 5.0	500/1000/1500	120/140/140	210/300/330	±0.5	Shutdown, C _{DELAY} , Power Good	SOIC, DFN
TC1301A/B	6	1.5 to 3.3	LDO1: 300 LDO2: 150	103/114	LDO1: 104 LDO2: 150	±0.5	Dual LDO plus Reset output, Shutdown, Reference bypass, Voltage detect	MSOP, DFN
TC1302AB	6	1.5 to 3.3	LDO1: 300 LDO2: 150	103/114	LDO1: 104 LDO2: 150	±0.5	Dual LDO, Shutdown, reference bypass, Voltage detect	MSOP, DFN

Products sorted by pin count followed by pricing.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

Power Management – Charge Pump DC-to-DC Converters

Product	Input Voltage Range (V)	Output Voltage (V)	Operating Temp Range (°C)	Max. Input Current (μA)	Typical Output Current (mA)	Features	Packages
TC1044S	1.5 to 12	-V _{IN} or 2*V _{IN}	-40 to +85	160	20	85 kHz oscillator Boost mode	PDIP, SOIC
TC7660	1.5 to 10	-V _{IN} or 2*V _{IN}	-40 to +85	180	20	10 kHz oscillator	PDIP, SOIC
TC7660H	1.5 to 10	-V _{IN} or 2*V _{IN}	-40 to +85	1000	20	120 kHz oscillator	PDIP, SOIC
TC7660S	1.5 to 12	-V _{IN} or 2*V _{IN}	-40 to +85	160	20	45 kHz oscillator Boost mode	PDIP, SOIC
TC7662B	1.5 to 15	-V _{IN} or 2*V _{IN}	-40 to +85	180	20	35 kHz oscillator Boost mode	PDIP, SOIC
TC7662A	3.0 to 18	-V _{IN} or 2*V _{IN}	-40 to +85	200	40	12 kHz oscillator	PDIP, SOIC
MCP1256	1.8 to 3.6	3.3	-40 to +85	100	100	Power Good Sleep mode	MSOP, DFN
MCP1257	1.8 to 3.6	3.3	-40 to +85	100	100	Sleep mode low battery indication	MSOP, DFN
MCP1258	1.8 to 3.6	3.3	-40 to +85	100	100	Low battery indication input/output bypass 1	MSOP, DFN

Power Management – CPU/System Supervisors

Product	Description	Operating Temp Range (°C)	Features	Packages
MCP111(1/2) TC5(1/2/3/4)	System Voltage Detectors (No Reset Delay)	-40 to +125 -40 to +85	Wide Vcc Input Range, Wide Detection Range (Custom Options Available), Low Current, CMOS/Push-Pull Active Low Reset Options	3/SOT-23A, 3/SOT-89, 3/TO-92, 5/SOT-23, 3/SC-70
MCP809, MCP100, MCP130, MCP120 MCP13XX, TC1270A and more	System Voltage Supervisors (Available Reset Delays)	-40 to +125 -40 to +85	Wide Detection Range (Custom Options Available), Low Current, Push-Pull/Open Drain, Active High/Low, Watchdog, Manual Reset, Dual Output Options, Multiple Reset Delay Options	3/SOT-23, 3/TO-92, 3/SC-70, 8/SOIC 150mil, 5/SOT-23, 4/SOT-143

Power Management – Power MOSFET Drivers

Product	Configuration	Operating Temp Range (°C)	Peak Output Current (A)	Output Resistance (Max.@ 25°C)	Max Supply Voltage (V)	Input/Output Delay (ns)	Packages
MCP1401/02 Single	Inverting/Non-inverting	-40 to +125	0.5	18/16	18	40/40	SOT-23
MCP1415/16 Single	Inverting/Non-inverting	-40 to +125	1.5	7.5/5.5	18	50/55	SOT-23
TC4467/8/9 Quad	Inverting/ Non-inverting	-40 to +85	1.2	15/15	18	40/40	PDIP, SOIC
TC4426A/27A/28A Dual	Inverting/Non-inverting	-40 to +125	1.5	9/9	18	30/30	PDIP, SOIC, DFN
TC4423A/24A/25A Dual	Inverting/Non-inverting	-40 to +125	3	3 (typ.)/4 (typ.)	18	40 (typ.)/40 (typ.)	PDIP, SOIC, DFN
MCP14E3/E4/E5 Dual	Inverting/Non-inverting	-40 to +125	4	3.5/3.0	18	55/55	PDIP, SOIC, DFN
MCP1406/07 Single	Inverting/Non-inverting	-40 to +125	6	1.8/2.0 (typ.)	18	30/30	TO-220, PDIP, DFN, SOIC
TC4420/29	Inverting/Non-inverting	-40 to +125	6	2.8/2.5	18	55/55	TO-220, PDIP, DFN, SOIC
TC4421A/22A Single	Inverting /Non-inverting	-40 to +125	9	1.25 (typ.)/1.5	18	38/42	PDIP, SOIC, TO-220, DFN
TC4451/52 Single	Inverting /Non-inverting	-40 to +125	12	0.6 (typ.)/1.5	18	15/15	SOIC, PDIP, DFN, TO-220, DDPK
TC4431/32 Single	Inverting /Non-inverting	-40 to +85	1.5	10/10	30	62/78	PDIP, SOIC

Power Management – Synchronous Buck High-Side Driver

Product	Configuration	Operating Temp Range (°C)	Peak Output Current (A)	Output Resistance (Max.@ 25°C)	Max Supply Voltage (V)	Input/Output Delay (ns)	Packages
MCP14700/14628	Dual input/Single input	-40 to +85	2	2.5/2.5	5 (V _{DD}), 36 (Boot Pin)	18/20	SOIC, DFN

Power Management – Battery Chargers

Product	Mode	Cell Type	# of Cells	Vcc Range (V)	Cell Voltage (V)	Max. Charging Current (mA)	Max. Voltage Regulation (%)	Int/Ext FET	Features	Packages
MCP73113/14/23	Linear	Li-Ion/Li-Polymer and LiFePO4	1	4 to 16	3.6, 4.1, 4.2, 4.35, 4.4	1100	±0.5	Int	6.5/5.8V Overvoltage Protection, UVLO, Thermal regulation	10-pin 3x3 DFN
MCP73213/23	Linear	Li-Ion/Li-Polymer and LiFePO4	2	4 to 16	7.2, 8.2, 8.4, 8.7, 8.8	1100	±0.6	Int	13V Overvoltage Protection	10-pin 3x3 DFN
MCP73831/2	Linear	Li-Ion/Li-Polymer	1	3.7 to 6.0	4.2, 4.35, 4.4, 4.5	500	±0.75	Int	UVLO, Thermal regulation, Programmable charge current, tri-state or open-drain STAT pin	8-pin 2x3 DFN, 5-pin SOT-23
MCP73837/8	Linear	Li-Ion/Li-Polymer	1	3.7 to 6.0	4.2, 4.35, 4.4, 4.5	1000	±0.75	Int	Dual input (USB/DC) auto-switching, Thermistor input, Power Good output or Timer enable input	10-pin MSOP, 10-pin 3x3 DFN
MCP73871	Linear	Li-Ion/Li-Polymer	1	3.75 to 6.0	4.2, 4.35, 4.4, 4.5	1500 (A/C Adapter) 500 (USB)	±0.5	Int	Simultaneous charging of load and battery, load-dependent charging, multiple programmable charge currents	20-pin SSOP, 20-pin 4x4 QFN

Linear – Op Amps

Product	# per Package	GBWP (MHz)	I _Q Typical (μA)	V _{os} Max (mV)	Operating Voltage (V)	Packages	Product	# per Package	GBWP (MHz)	I _Q Typical (μA)	V _{os} Max (mV)	Operating Voltage (V)	Packages
MCP661/2/3/5	1/2/1/2	60	6000	8	2.5 to 5.5	SOIC, MSOP, DFN	MCP6071/2/4	1/2/4	1.2	110	0.15	1.8 to 6.0	SOIC, TSSOP, DFN
MCP651/2/5	1/2/2	50	6000	0.2	2.5 to 5.5	SOIC, MSOP, DFN	MCP6H01/2	1/2	1.2	135	4.5	3.5 to 16	SOIC, TDFN
MCP631/2/3/5	1/2/1/2	24	2500	8	2.5 to 5.5	SOIC, MSOP, DFN	MCP6001/2/4	1/2/4	1	100	4.5	1.8 to 6.0	PDIP, SOIC, MSOP, TSSOP, TDFN, SOT, SC70
MCP621/2/5	1/2/2	20	2500	0.2	2.5 to 5.5	SOIC, MSOP, DFN	MCP6401/2/4	1/2/4	1	45	4.5	1.8 to 6.0	SOIC, TSSOP, TDFN, SOT, SC70
MCP6021/2/3/4	1/2/1/4	10	1000	0.5	2.5 to 5.5	PDIP, SOIC, MSOP, TSSOP, SOT	MCP6L01/2/4	1/2/4	1	85	5	1.8 to 6.0	SOIC, MSOP, TSSOP, SOT, SC70
MCP6291/2/3/4/5	1/2/1/4/2	10	1000	3	2.4 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT	MCP6061/2/4	1/2/4	0.73	60	0.15	1.8 to 6.0	SOIC, TSSOP, DFN
MCP6L91/2/4	1/2/4	10	850	4	2.4 to 6.0	SOIC, MSOP, TSSOP, SOT	MCP6241/2/4	1/2/4	0.55	50	5	1.8 to 5.5	PDIP, SOIC, MSOP, TSSOP, TDFN, SOT, SC70
MCP6281/2/3/4/5	1/2/1/4/2	5	445	3	2.2 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT	MCP6051/2/4	1/2/4	0.385	30	0.15	1.8 to 6.0	SOIC, TSSOP, DFN
MCP6286	1	3.5	540	1.5	2.2 to 5.5	SOT	MCP6231/2/4	1/2/4	0.3	20	5	1.8 to 6.0	PDIP, SOIC, MSOP, TSSOP, TDFN, SOT, SC70
MCP601/2/3/4	1/2/1/4	2.8	230	2	2.7 to 6.0	PDIP, SOIC, TSSOP, SOT	MCP6161/7/8/9	1/2/1/4	0.19	19	0.15	2.3 to 5.5	PDIP, SOIC, MSOP, TSSOP
MCP6L1/2/4	1/2/4	2.8	200	3	2.7 to 6.0	SOIC, MSOP, TSSOP, SOT	MCP6061/7/8/9	1/2/1/4	0.155	19	0.25	2.5 to 6.0	PDIP, SOIC, TSSOP, SOT
MCP6271/2/3/4/5	1/2/1/4/2	2	170	3	2.0 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT	MCP6141/2/3/4	1/2/1/4	0.1	0.6	3	1.4 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT
MCP6L71/2/4	1/2/4	2	150	4	2.0 to 6.0	SOIC, MSOP, TSSOP, SOT	MCP6041/2/3/4	1/2/1/4	0.014	0.6	3	1.4 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT
MCP6V01/2/3	1/2/1	1.3	300	0.002	1.8 to 5.5	SOIC, DFN, TDFN	MCP6031/2/3/4	1/2/1/4	0.01	0.9	0.15	1.8 to 5.5	SOIC, MSOP, TSSOP, DFN, SOT
MCP6V06/7/8	1/2/1	1.3	300	0.003	1.8 to 5.5	SOIC, DFN, TDFN	MCP6441	1	0.009	0.45	4.5	1.4 to 6.0	SOT, SC70

Linear – Comparators

Product	# per Package	Typical Propagation Delay (μs)	I _Q Typical (μA)	V _{os} Max (mV)	Operating Voltage (V)	Temperature Range (°C)	Features	Packages
MCP6541/2/3/4	1/2/1/4	4	1	5	1.6 to 5.5	-40 to +125	Push-Pull, Rail-to-Rail Input/Output	PDIP, SOIC, MSOP, TSSOP, SOT, SC70
MCP6546/7/8/9	1/2/1/4	4	1	5	1.6 to 5.5	-40 to +125	Open-drain, 9V, Rail-to-Rail Input/Output	PDIP, SOIC, MSOP, TSSOP, SOT, SC70
MCP6561/2/4	1/2/4	0.047	100	10	1.8 to 5.5	-40 to +125	Push-Pull, Rail-to-Rail Input/Output	SOIC, MSOP, TSSOP, SOT, SC70
MCP6566/7/9	1/2/4	0.047	100	10	1.8 to 5.5	-40 to +125	Open-Drain, Rail-to-Rail Input/Output	SOIC, MSOP, TSSOP, SOT, SC70

Mixed Signal – Successive Approximation Register (SAR) Analog-to-Digital Converters

Product	Resolution (bits)	Maximum Sampling Rate (ksamples/sec)	# of Input Channels	Input Type	Interface	Max. Supply Current (μA)	Temperature Range (°C)	Packages
MCP3021/3221	10/12	22	1	Single-ended	I ² C™	250	-40 to +125	SOT-23A
MCP3001/2/4/8	10	200	1/2/4/8	Single-ended	SPI	500-550	-40 to +85	PDIP, SOIC, MSOP, TSSOP
MCP3201/2/4/8	12	100	1/2/4/8	Single-ended	SPI	400-550	-40 to +85	PDIP, SOIC, MSOP, TSSOP
MCP3301/2/4	13	100	1/2/4	Differential	SPI	450	-40 to +85	PDIP, SOIC, MSOP, TSSOP

Mixed Signal – Digital Potentiometers

Product	# of Taps	Memory	Channels	Interface	Resistance (kΩ)	Temperature Range (°C)	Packages	Product	# of Taps	Memory	Channels	Interface	Resistance (kΩ)	Temperature Range (°C)	Packages
MCP4011/12/13/14	64	Volatile	1	Up/Down	2.1, 5, 10, 50	-40 to +125	DFN, SOT-23	MCP4341/42	129	Nonvolatile	4	I ² C™	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4017/18/19	128	Volatile	1	I ² C™	5, 10, 50, 100	-40 to +125	SC-70	MCP4361/62	257	Nonvolatile	4	I ² C™	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP40D17/D18/D19	128	Volatile	1	I ² C™	5, 10, 50, 100	-40 to +125	SC-70	MCP4331/32	129	Volatile	4	I ² C™	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4021/22/23/24	64	Nonvolatile	1	Up/Down	2.1, 5, 10, 50	-40 to +125	DFN, SOT-23	MCP4351/52	257	Volatile	4	I ² C™	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4141/42	128	Nonvolatile	1	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN	MCP4531/32	128	Volatile	1	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4241/42	128	Nonvolatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN	MCP4631/32	128	Volatile	2	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4131/32	128	Volatile	1	SPI	5, 10, 50, 100	-40 to +125	QFN, DFN	MCP4541/42	128	Nonvolatile	1	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4231/32	128	Volatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN	MCP4641/42	128	Nonvolatile	2	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4151/52	256	Volatile	1	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN	MCP4551/52	256	Volatile	1	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4161/62	256	Nonvolatile	1	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN	MCP4651/52	256	Volatile	2	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4251/52	256	Volatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN	MCP4561/62	256	Nonvolatile	1	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4261/62	256	Nonvolatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN	MCP4661/62	256	Nonvolatile	2	I ² C™	5, 10, 50, 100	-40 to +125	MSOP, DFN

Mixed Signal – Delta Sigma Analog-to-Digital Converters

Product	Resolution (bits)	Maximum Sampling Rate (samples/sec)	# of Input Channels	Interface	Typical Supply Current (µA)	Temperature Range (°C)	Features	Packages
MCP3421/2/3/4	18 to 12	4 to 240	1/2/2/4 Diff	I ² C™	155	-40 to +125	PGA, V _{REF}	SOT, DFN, MSOP, SOIC, TSSOP
MCP3425/6/7/8	16 to 12	15 to 240	1/2/2/4 Diff	I ² C™	155	-40 to +125	PGA, V _{REF}	SOT, DFN, MSOP, SOIC, TSSOP
MCP3550/1/3	22	13/14/60	1 Diff	SPI	120	-40 to +125	50 & 60 Hz Rejection	SOIC, MSOP

Mixed Signal – Energy Measurement ICs

Product	Dynamic Range	Typical Accuracy	Gain	Output Type	Typical Supply Current	Supply Voltage Range (V)	Temperature Range (°C)	Packages
MCP3901	24-bit resolution	–	up to 32	SPI	3.6 mA	4.5 to 5.5	-40 to +125	SSOP, QFN
MCP3905A/06A	500:1 / 1000:1	0.1%	up to 32	Active power pulse	3.9 mA	4.5 to 5.5	-40 to +85	SSOP
MCP3909	1000:1	0.1%	1, 2, 8, 16	SPI	3.9 mA	4.5 to 5.5	-40 to +85	SSOP

Mixed Signal – Digital-to-Analog Converters

Product	Resolution (Bits)	DAC Channels	Interface	Voltage Reference	Output Settling Time (µs)	DNL (±LSB)	Typical Operating Current (µA)	Temperature Range (°C)	Packages
MCP4725	12	1	I ² C™	V _{DD}	6	0.75	175	-40 to +125	SOT-23
MCP4728	12	4	I ² C™	Int	6	0.75	250	-40 to +125	MSOP
MCP4801/11/21	8/10/12	1	SPI	Int	4.5	0.5/0.5/0.75	330	-40 to +125	2x3 DFN, MSOP, PDIP, SOIC
MCP4802/12/22	8/10/12	2	SPI	Int	4.5	0.5/0.5/0.75	415	-40 to +125	MSOP, PDIP, SOIC
MCP4901/11/21	8/10/12	1	SPI	Ext	4.5	0.5/0.5/0.75	175	-40 to +125	2x3 DFN, MSOP, PDIP, SOIC
MCP4902/12/22	8/10/12	2	SPI	Ext	4.5	0.5/0.5/0.75	350	-40 to +125	PDIP, SOIC, TSSOP
TC1320/1	8/10	1	SMbus	Ext	10	0.8/2	350	-40 to +85	MSOP, SOIC

Interface – mTouch™ AR1000 Resistive Touch Screen Controllers

Product	Type	Communication	Touch Screens Supported	A/D	Resolution	Power	Points per second	Baud Rate	Operating Temperature Range (°C)	Static Protection	5 ku Pricing ¹	Special Features	Package
AR1010	Analog Resistive	UART	All Manufacturers 4, 5 and 8 wire	Internal 10-bit Ratiometric	1024 X 1024	3.3V DC ±5% 5.5V DC ±5%	140 pps	Standard 9600	-40 to +85	Per schematic	\$1.39	Controller driven calibration & Universal for all touch screens	20-pin SSOP (SS), SOIC (SO), QFN (ML)
AR1020	Analog Resistive	SPI, I ² C™	All Manufacturers 4, 5 and 8 wire	Internal 10-bit Ratiometric	1024 X 1024	3.3V DC ±5% 5.5V DC ±5%	140 pps	Standard 9600	-40 to +85	Per schematic	\$1.39	Controller driven calibration & Universal for all touch screens	20-pin SSOP (SS), SOIC (SO), QFN (ML)

Interface – Controller Area Network (CAN), Infrared, LIN Transceivers, Ethernet, Serial Peripherals, USB

Product	Description	Operating Temperature Range (°C)	Other Features	Packages
MCP2515	Stand-Alone CAN Controller with SPI Interface	-40 to +125	3 TX Buffers, 2 RX Buffers, 6 Filters, 2 Masks, Interrupt output, MCP2510 upgrade	PDIP, SOIC, TSSOP
MCP2551	CAN (Controller Area Network), High-Speed CAN Transceiver	-40 to +125	1 Mbps max. CAN bus speed, ISO11898 compatible, Industry standard pinout	PDIP, SOIC
MCP202(1/2)	LIN (Local Interconnect Network), LIN Transceiver with Voltage Regulator	-40 to +125	V _{REG} = 5.0 ± 3%, 3.3 ± 3% @ 50 mA, V _{CC} Range = 7.4 to 18V, Max Baud Rate = 20 Kbaud, Supports LIN Specs; 1.3, 2.0, 2.1, SAE J2602, Exceeds Automotive OEM ESD/EMC Requirements	PDIP, SOIC, TSSOP, DFN
MCP200(3/4)	Stand-alone LIN Transceiver	-40 to +125	V _{CC} Range = 6 to 27V, Max Baud Rate = 20 Kbaud, Supports LIN Specs 1.3, 2.0, 2.1, SAE J2602, Exceeds Automotive OEM ESD/EMC Requirements	PDIP, SOIC, DFN
MCP23X09/18	8-bit I/O Port Expander, 16-bit I/O Port Expander	-40 to +125	I ² C (up to 3.4 MHz) or SPI (up to 10 MHz) interface, 25 mA source/sink per I/O	PDIP, SDIP, SOIC, SSOP
MCP212(0/2), MCP2140A, MCP215(0/5)	Infrared IrDA Encoders, Decoders, Protocol Handlers	-40 to +85	UART to IR encoder/decoder w/hardware & software baud rate selection, IrDA® Standard protocol handler plus encoder/decoder	PDIP, SDIP, SOIC, SSOP
MCP2200	UART to USB Protocol Converter	-40 to +85	USB 2.0 Compliant, 8 GPIO, Supports High-speed USB (12 Mbps)	SOIC, SSOP, QFN
ENC28J60	Stand-Alone 10 Base-T Ethernet Controller with SPI Interface	-40 to +85	Ethernet Controller, 8 KB RAM Buffer, Integrated 10 BASE-T PHY	SPDIP, SOIC, SSOP, QFN
ENC424J600	Stand-Alone 10/100 Base-T Ethernet Controller with SPI and Parallel Interface	-40 to +85	Ethernet Controller, 24 KB RAM Buffer, Cryptographic Security Engine, 10/100 Base-T PHY	TQFP, QFN
ENC624J600	Stand-Alone 10/100 Base-T Ethernet Controller with SPI and Parallel Interface	-40 to +85	Ethernet Controller, 24 KB RAM Buffer, Cryptographic Security Engine, 10/100 Base-T PHY	TQFP

Safety & Security – Smoke Detector and Horn Driver ICs

Product	Horn Driver	Detection Method	Low Battery Detection	Alarm Memory	Alarm Interconnect	Hush/Sensitivity Timer	Operating Temperature Range (°C)	Packages
RE46C140/1/3/4/5	Yes	Photo	Yes	No	Yes	140/4/5	-25 to +75	PDIP, SOIC
RE46C12X & 152	Yes	Ion	Yes	No	Not 120	122/7,152	-10 to +60	PDIP
RE46C10X & 11X	Yes	Just Driver	5/7/9/19	NA	9/19	None	See Datasheet	See Datasheet
RE46C162/3, 5/6/7/8	Yes	Ion/Photo	Yes	Yes	Yes	Yes	-25 to +75	PDIP, SOIC

Motor Drivers - Stepper Motors, DC Motors and 3 Phase BLDC Fan Controllers

Product	Motor Type	Input Voltage Range (V)	Internal/External FETs	Output Current (mA)	Control Scheme	Motor Speed Output	Shutdown Protection	Temperature Operating Range (°C)	Features	Packages
MTS62C19A	One Bipolar Stepper Motor or Two DC Motors	10.0 to 40.0	Internal	750	Direct PWM Input, Current Limit Control, Microstepping	No	Overcurrent, Overtemperature, Under Voltage	-20 to +85	Dual Full Bridge Motor Driver for Stepper Motors, Pin Compatible with Allegro 6219	24-pin SOP
MTS2916A	One Bipolar Stepper Motor or Two DC Motors	10.0 to 40.0	Internal	750	Direct PWM Input, Current Limit Control, Microstepping	No	Overcurrent, Overtemperature, Under Voltage	-20 to +85	Dual Full Bridge Motor Driver for Stepper Motors, Pin Compatible with Allegro 2916	24-pin SOP
MTD6501C	3 Phase Brushless Fan	2.0 to 14.0	Internal	800	Sensorless Sinusoidal	Frequency Generator	Overcurrent, Short Circuit, Overtemperature, Motor Lock-up	-10 to +85	3-Phase BLDC Sinusoidal Sensorless Fan Motor Driver	8-pin SOP
MTD6501D	3 Phase Brushless Fan	2.0 to 14.0	Internal	500	Sensorless Sinusoidal	Frequency Generator	Overcurrent, Short Circuit, Overtemperature, Motor Lock-up	-30 to +95	3-Phase BLDC Sinusoidal Sensorless Fan Motor Driver, Boost Mode	10-pin MSOP

RF Products

WLAN Power Amplifiers

Product	Description	Frequency	Linear Power (dBm) @ 3% EVM	Package
SST11LP12-QCF	802.11a/n, High Power	4.9-5.8 GHz	21	3x3 QFN
SST11CP15-QUBE	802.11a/n, Low DC Current	4.9-5.8 GHz	19	2x2 QFN
SST12CP11-QVCE	802.11g/n, Ultra High Power	2.4-2.5 GHz	25.5	3x3 QFN
SST12LP07-QVCE-MM007	802.11g, High Power (Pin Compatible with TQP777002)	2.4-2.5 GHz	21.5	3x3 QFN
SST12LP07A-QXBE	802.11b/g/n	2.4-2.5 GHz	21	12-pin 2x2 QFN
SST12LP07E-QX8E	802.11b/g	2.4-2.5 GHz	20.5	8-pin 2x2 XSON
SST12LP08-QX6E	802.11b/g/n	2.4-2.5 GHz	20	6-pin 1.5x1.5 QFN
SST12LP08-QXBE	802.11b/g/n	2.4-2.5 GHz	20	12-pin 2x2 QFN
SST12LP08A-QX8E	802.11b/g/n	2.4-2.5 GHz	20.5	8-pin 2x2 XSON
SST12LP14A-QVCE	802.11g (General Purpose)	2.4-2.5 GHz	21.5	3x3 QFN
SST12LP14C-QVCE	802.11g (Pin Compatible with 12LP14)	2.4-2.5 GHz	18	3x3 QFN
SST12LP14E-QX6E	802.11b/g/n (Low DC Current for Embedded)	2.4-2.5 GHz	18.5	6-pin 1.5x1.5 QFN
SST12LP14E-QX8E	802.11b/g/n (Low DC Current for Embedded)	2.4-2.5 GHz	18.5	8-pin 2x2 QFN
SST12LP15A-QVCE	802.11b/g/n, High Power	2.4-2.5 GHz	22.5	3x3 QFN
SST12LP15B-QVCE	802.11b/g/n, High Power	2.4-2.5 GHz	22.5	3x3 QFN
SST12LP15B-QXBE	802.11b/g/n, High Power	2.4-2.5 GHz	22.5	2x2 QFN
SST12LP17E-QU8E	802.11b/g/n, Fully Matched	2.4-2.5 GHz	18	2x2 QFN
SST12LP19E-QX6E	802.11b/g/n (Low DC Current for Embedded)	2.4-2.5 GHz	19	6-pin 1.5x1.5 QFN
SST12LP19E-QX8E	802.11b/g/n (Low DC Current for Embedded)	2.4-2.5 GHz	19	8-pin 2x2 QFN
SST13LP05-MLCF	802.11a/b/g Dual-Band (Fully Matched)	2.4-2.5 GHz 5.1-5.8 GHz	18.5 17.5	4x4 LGA

Front End Modules

Product	Description	Frequency	NF (dB)/PA Linear Power (dBm) @ 3% EVM	Package
SST12LF01-QDE	802.11b/g Front End Module PA+LNA	2.4-2.5 GHz	1.5 / 21.5	4x4 QFN
SST12LF02-QXCE	802.11b/g/n Front End Module PA (Fully Matched) + SP3T SW	2.4-2.5 GHz	18.5	3x3 QFN

Low-Noise Amplifiers

Product	Description	Frequency	NF (dB)	Package
SST12LN01-QU6F	Low-Noise Amplifier (Fully Matched)	2.4 GHz	1.5	3x1.6 QFN

Real-Time Clocks

Bus	Product	Alarm Settings ⁽¹⁾	Outputs	Digital Trim (Adj/Range)	SRAM ⁽³⁾ (Bytes)	EEPROM (Kbits)	ID ⁽²⁾ /MAC	Minimum Voltage	I _{BAT} (nA)	Additional Features	Pins	Packages	Bus
I ² C™	MCP79410	2	1 MFP (IRQ/CLK)	+1 ppm/±127 ppm	64	1	Blank ID	V _{CC} : 1.8V, V _{BAT} : 1.3V	700	Battery switchover, Power-fail timestamp	8	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)	I ² C™
	MCP79411	2	1 MFP (IRQ/CLK)	+1 ppm/±127 ppm	64	1	EUI-48	V _{CC} : 1.8V, V _{BAT} : 1.3V	700	Battery switchover, Power-fail timestamp	8	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)	
	MCP79412	2	1 MFP (IRQ/CLK)	+1 ppm/±127 ppm	64	1	EUI-64	V _{CC} : 1.8V, V _{BAT} : 1.3V	700	Battery switchover, Power-fail timestamp	8	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)	
	MCP79400	2	1 MFP (IRQ/CLK)	+1 ppm/±127 ppm	64	0	Blank ID	V _{CC} : 1.8V, V _{BAT} : 1.3V	700	Battery switchover, Power-fail timestamp	8	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)	
	MCP79401	2	1 MFP (IRQ/CLK)	+1 ppm/±127 ppm	64	0	EUI-48	V _{CC} : 1.8V, V _{BAT} : 1.3V	700	Battery switchover, Power-fail timestamp	8	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)	
	MCP79402	2	1 MFP (IRQ/CLK)	+1 ppm/±127 ppm	64	0	EUI-64	V _{CC} : 1.8V, V _{BAT} : 1.3V	700	Battery switchover, Power-fail timestamp	8	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)	

1. Alarm settings on 1 second count.

2. Unique ID is 64 bits of protected EEPROM.

3. Battery backed SRAM.

Serial Memory Products

Bus	Product	Released (R) Not Released (NR)	Density	Organization	Max. Clock Frequency	Operating Voltage	Temperature Range	EW Endurance (Minimum)	Data Retention (Minimum)	Max. Write Speeds	Max. Standby Current (@5.5V, 85°C)	Write Protect		Protected Array Size	5 kV Pricing [†]	Special/Unique Features	Packages	Bus
Serial SRAM																		
SPI	23X640	R	64 Kb	x8	20 MHz	1.5V-1.95V 2.7V-3.6V	-40°C to +125°C	∞	Volatile	0 ms	4 μA	–	–	–	\$0.51	20 MHz @ 3V, 32 byte page buffer, Zero write cycle time, Infinite endurance	SOIC (SN), PDIP (P), TSSOP (ST)	SPI
	23X256	R	256 Kb	x8	20 MHz	1.5V-1.95V 2.7V-3.6V	-40°C to +125°C	∞	Volatile	0 ms	4 μA	–	–	–	\$0.96	20 MHz @ 3V, 32 byte page buffer, Zero write cycle time, Infinite endurance	SOIC (SN), PDIP (P), TSSOP (ST)	
Serial EEPROM																		
UNI/O [®] Bus	11XX010	R	1 Kb	x8	100 kHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	–	✓	W, ½, ¼	\$0.23	Single I/O for all clock, data, control and write protection	3-SOT-23 (TT), SOIC (SN), PDIP (P), DFN (MNY), MSOP (MS), TO-92 (TO), WLCSP (CS)	UNI/O [®] Bus
	11XX020/E48	R	2 Kb	x8	100 kHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	–	✓	W, ½, ¼	\$0.25	Single I/O for all clock, data, control and write protection, Unique EUI-48™/EUI-64™, MAC address option available	3-SOT-23 (TT), SOIC (SN), PDIP (P), DFN (MNY), MSOP (MS), TO-92 (TO), WLCSP (CS)	
	11XX040	R	4 Kb	x8	100 kHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	–	✓	W, ½, ¼	\$0.26	Single I/O for all clock, data, control and write protection	3-SOT-23 (TT), SOIC (SN), PDIP (P), DFN (MNY), MSOP (MS), TO-92 (TO), WLCSP (CS)	
	11XX080	R	8 Kb	x8	100 kHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	–	✓	W, ½, ¼	\$0.30	Single I/O for all clock, data, control and write protection	3-SOT-23 (TT), SOIC (SN), PDIP (P), DFN (MNY), MSOP (MS), TO-92 (TO), WLCSP (CS)	
	11XX160	R	16 Kb	x8	100 kHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	–	✓	W, ½, ¼	\$0.33	Single I/O for all clock, data, control and write protection	3-SOT-23 (TT), SOIC (SN), PDIP (P), DFN (MNY), MSOP (MS), TO-92 (TO), WLCSP (CS)	
	24XX00	R	128 b	x8	400 kHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	4 ms	1 μA	–	–	–	\$0.17	100 KHz operation from 1.7V to 4.5V	SOIC (SN), TSSOP (ST), 5-SOT-23 (OT), DFN (MC), PDIP (P)	
I ² C™	24XX01/014	R	1 Kb	x8	400 kHz	1.7V-5.5V 1.5V-3.6V	-40°C to +150°C	1M	200 Years	5 ms	1 μA	✓	–	W, ½	\$0.18	Address pin option - connect up to 8 devices on bus, Very low voltage option	SOIC (SN), TSSOP (ST), PDIP (P), 5-SOT-23 (OT), DFN (MNY), MSOP (MS), SC70 (LT)	I ² C™
	24XX02/024/E48	R	2 Kb	x8	400 kHz	1.7V-5.5V 1.5V-3.6V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W, ½	\$0.20	Address pin option - connect up to 8 devices on bus, Very low voltage option, Unique EUI-48™/EUI-64™, MAC address option available	SOIC (SN), TSSOP (ST), PDIP (P), 5-SOT-23 (OT), DFN (MNY), MSOP (MS), SC70 (LT)	
	34XX02	R	2 Kb	x8	1 MHz	1.7V-5.5V 1.5V-3.6V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	✓	W, ½	\$0.18	1 MHz @ 2.5V, Permanent and restable software WP - DIMM-DDR2/3	SOIC (SN), TSSOP (ST), PDIP (P), 6-SOT-23 (OT), DFN (MNY), MSOP (MS)	
	24XX04	R	4 Kb	x8	400 kHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W, ½	\$0.21	400 KHz @ 2.5V, 16 byte page write buffer, No address pins	SOIC (SN), PDIP (P), TSSOP (ST), 5-SOT-23 (OT), DFN (MNY), MSOP (MS), WLCSP (CS)	
	24XX08	R	8 Kb	x8	400 kHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W, ½	\$0.23	400 KHz @ 2.5V, 16 byte page write buffer, No address pins	SOIC (SN), TSSOP (ST), 5-SOT-23 (OT), PDIP (P), DFN (MNY), MSOP (MS)	
	24XX16	R	16 Kb	x8	400 kHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W, ½	\$0.25	400 KHz @ 2.5V, 16 byte page write buffer, No address pins	SOIC (SN), TSSOP (ST), PDIP (P), 5-SOT-23 (OT), DFN (MNY), MSOP (MS), WLCSP (CS)	
	24XX32A	R	32 Kb	x8	400 kHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W, ¼	\$0.31	400 KHz @ 2.5V, 32 byte page write buffer, connect up to 8 devices on bus	SOIC (SN), TSSOP (ST), PDIP (P), 5-SOT-23 (OT), DFN (MNY), MSOP (MS), WLCSP (CS)	
	24XX64/65	R	64 Kb	x8	1 MHz	1.7V-5.5V	-40°C to +125°C	1M, 10M	200 Years	5 ms	1 μA	✓	–	W, ¼	\$0.38	1 MHz @ 2.5V, 32/64 byte page, Relocatable 4 Kb block with 10M cycles endurance	SOIC (SN), TSSOP (ST), PDIP (P), 5-SOT-23 (OT), DFN (MNY), MSOP (MS), WLCSP (CS)	
	24XX128	R	128 Kb	x8	1 MHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W	\$0.54	1 MHz @ 2.5V, 64 byte page, connect up to 8 devices on bus	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MNY), MSOP (MS), WLCSP (CS)	
	24XX256	R	256 Kb	x8	1 MHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W	\$0.83	1 MHz @ 2.5V, 64 byte page, connect up to 8 devices on bus	SOIC (SN), TSSOP (ST), SOIJ (SM), PDIP (P), DFN (MF), MSOP (MS), WLCSP (CS)	
	24XX512	R	512 Kb	x8	1 MHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	1 μA	✓	–	W	\$1.50	1 MHz @ 2.5V, 128 byte page, connect up to 8 devices on bus	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MF), SOIJ (SM), WLCSP (CS)	
	24XX1025	R	1 Mb	x8	1 MHz	1.7V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	5 μA	✓	–	W	\$3.14	1 MHz @ 2.5V, 128 byte page, connect up to 4 devices on bus	SOIC (SN), SOIJ (SM), PDIP (P)	

1. All devices are Pb-Free and RoHS compliant.

2. ESD protection > 4 kV (HBM); >400V (MM) on all pins.

3. Write Protect (WP): W = Whole Array, ½ = Half Array, ¼ = Quarter Array.

4. Factory program and unique ID options available.

5. Die and wafer options available on all devices.

† - Pricing subject to change; please contact your Microchip representative for most current pricing.

Serial Memory Products

Bus	Product	Released (R) Not Released (NR)	Density	Organization	Max. Clock Frequency	Operating Voltage	Temperature Range	EW Endurance (Minimum)	Data Retention (Minimum)	Max. Write Speeds	Max. Standby Current (@5.5V, 85°C)	Write Protect		Protected Array Size	5-yr Pricing†	Special/Unique Features	Packages	Bus
												Hardware	Software					
Microwire	93XX46A/B/C	R	1 Kb	x8/x16	3 MHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	6 ms	1 µA	–	–	–	\$0.18	ORG pin to select word size on 46C version	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	Microwire
	93XX56A/B/C	R	2 Kb	x8 / x16	3 MHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	6 ms	1 µA	–	–	–	\$0.20	ORG pin to select word size in 56C version	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	
	93XX66A/B/C	R	4 Kb	x8 / x16	3 MHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	6 ms	1 µA	–	–	–	\$0.21	ORG pin to select word size in 66C version	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	
	93XX76A/B/C	R	8 Kb	x8 / x16	3 MHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	6 ms	1 µA	✓	–	W	\$0.30	ORG pin to select word size in 76C version	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	
	93XX86A/B/C	R	16 Kb	x8 / x16	3 MHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	6 ms	1 µA	✓	–	W	\$0.33	ORG pin to select word size in 86C version	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	
SPI	25XX010A	R	1 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.30	5 MHz @ 2.5V, Status register, 16 byte page	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	SPI
	25XX020A/E48	R	2 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.31	5 MHz @ 2.5V, Status register, 16 byte page, Unique EUI-48™/EUI-64™ MAC address option available	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	
	25XX040A	R	4 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.33	5 MHz @ 2.5V, Status register, 16 byte page	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MC), MSOP (MS), 6-SOT-23 (OT)	
	25XX080C/D	R	8 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.40	16/32 byte page, 5 MHz @ 2.5V, Status register	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MNY), MSOP (MS)	
	25XX160C/D	R	16 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.41	16/32 byte page, 5 MHz @ 2.5V, Status register	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MNY), MSOP (MS)	
	25XX320A	R	32 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.45	5 MHz @ 2.5V, Status register, 32 byte page	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MNY), MSOP (MS)	
	25XX640A	R	64 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.46	5 MHz @ 2.5V, Status register, 32 byte page	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MNY, MF), MSOP (MS)	
	25XX128	R	128 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$0.74	5 MHz @ 2.5V, Status register, 64 byte page	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MF)	
	25XX256	R	256 Kb	x8	10 MHz	1.8V-5.5V	-40°C to +150°C	1M	200 Years	5 ms	1 µA	✓	✓	W, ½, ¼	\$1.01	5 MHz @ 2.5V, Status register, 64 byte page	SOIC (SN), TSSOP (ST), PDIP (P), DFN (MF), SOIJ (SM)	
	25XX512	R	512 Kb	x8	20 MHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	5 ms	10 µA	✓	✓	W, ½, ¼	\$1.53	10 MHz @ 2.5V, Deep power down, Status register, Page/Sector/Chip erase	SOIC (SN), PDIP (P), DFN (MF), SOIJ (SM)	
	25XX1024	R	1 Mb	x8	20 MHz	1.8V-5.5V	-40°C to +125°C	1M	200 Years	6 ms	12 µA	✓	✓	W, ½, ¼	\$2.59	10 MHz @ 2.5V, Deep power down, Status register, Page/Sector/Chip erase	PDIP (P), DFN (MF), SOIJ (SM)	

- All devices are Pb-Free and RoHS compliant.
 - ESD protection > 4 kV (HBM); >400V (MM) on all pins.
 - Write Protect (WP): W = Whole Array; ½ = Half Array; ¼ = Quarter Array.
 - Factory program and unique ID options available.
 - Die and wafer options available on all devices.
- † - Pricing subject to change; please contact your Microchip representative for most current pricing.

SST NOR Flash Memory

Voltage	Density	Parallel	SPI (Serial)	SQI™ (Quad-bit)	FWH/LPC	Voltage	Density	Parallel	SPI (Serial)	SQI™ (Quad-bit)	FWH/LPC
5V	512 Kbit	–	–	–	–	1.8V	512 Kbit	–	25WF512	–	–
	1 Mbit	39SF010A	–	–	–		1 Mbit	–	25WF010	–	–
	2 Mbit	39SF020A	–	–	–		2 Mbit	–	25WF020	–	–
	4 Mbit	39SF040	–	–	–		4 Mbit	39WF400B	25WF040	–	–
3V	512 Kbit	39VF512	25VF512A	–	–		8 Mbit	39WF800B	25WF080	26WF080B	–
	1 Mbit	39VF010	25VF010A	–	–		16 Mbit	39WF160X	–	26WF016B	–
	2 Mbit	39VF020, 39VF200A	25VF020B	–	–		32 Mbit	–	–	26WF032/26WF032B	–
	4 Mbit	39VF040, 39VF400A	25VF040B	–	–		64 Mbit	–	–	26WF064B	–
	8 Mbit	39VF800A	25VF080B	–	49LF008B, 49LF080B						
	16 Mbit	39VF160XC, 39VF168X	25VF016B	26VF016/26VF016B	49LF016C, 49LF160C						
	32 Mbit	39VF320XB	25VF032B	26VF032/26VF032B	–						
	64 Mbit	39VF640XB, 38VF640X	25VF064C	26VF064B	–						

X = 1 or 2 for 39 Series
X = 1, 2, 3 or 4 for 36 and 38 Series

Wireless Products

IEEE 802.11 Modules

Product	Pin Count	Frequency Range (GHz)	Sensitivity (dBm)	Power Output (dBm)	RSSI	TX Power Consumption (mA)	RX Power Consumption (mA)	Clock	Sleep	MAC	MAC Features	Encryption	Interface	Volume Pricing†	Packages
ZG2100MC	36	2.412-2.484	-91	10	Yes	156	85	25 MHz	0.1	Yes	802.11	WPA, WPA2, WEP	4-wire SPI	\$26.57	36 Module
ZG2101MC	36	2.412-2.484	-91	10	Yes	156	85	25 MHz	0.1	Yes	802.11	WPA, WPA2, WEP	4-wire SPI	\$26.57	36 Module

IEEE 802.15.4 Transceivers/Modules

Product	Pin Count	Frequency Range (GHz)	Sensitivity (dBm)	Power Output (dBm)	RSSI	TX Power Consumption (mA)	RX Power Consumption (mA)	Clock	Sleep	MAC	MAC Features	Encryption	Interface	Volume Pricing†	Packages
MRF24J40	40	2.405-2.48	-95	0	Yes	23	19	20 MHz	Yes	Yes	CSMA-CA	AES128	4-wire SPI	\$2.36	40/QFN
MRF24J40MA	12	2.405-2.48	-95	0	Yes	23	19	20 MHz	Yes	Yes	CSMA-CA	AES128	4-wire SPI	\$8.99	12/Module
MRF24J40MB	12	2.405-2.475	-102	20	Yes	130	25	20 MHz	Yes	Yes	CSMA-CA	AES128	4-wire SPI	\$15.70	12/Module
MRF24J40MC	12	2.405-2.475	-102	20	Yes	130	25	20 MHz	Yes	Yes	CSMA-CA	AES128	4-wire SPI	\$15.70	12/Module

Sub-GHz Transceivers/Modules

Product	Pin Count	Frequency Range (MHz)	Sensitivity (dBm)	Power Output (dBm)	RSSI	TX Power Consumption (mA)	RX Power Consumption (mA)	Clock	Sleep	Interface	Volume Pricing†	Packages
MRF49XA	16	433/868/915	-110	7	Yes	15 mA @ 0 dBm	11	10 MHz	Yes	4-wire SPI	\$1.71	16/TSSOP
MRF89XA	32	868/915/950	-113	12.5	Yes	25 mA @ 10 dBm	3	12.8 MHz	Yes	4-wire SPI	\$2.05	32/TQFN

rfPIC™ Transmitters + PIC® MCUs

Product	I/O Pins	Frequency Range (MHz)	Program Bytes	Program Words	EEPROM	RAM (bytes)	Digital Timer	Watch Dog Timer	Max. Speed (MHz)	ICSP™	Modulation	Data Rate (kbps)	Output Power (dBm)	Operating Voltage	Other Features	Volume Pricing†	Packages
rfPIC12F675F	6	380-450	1792	1024 x 12	128	64	1	1	20	Yes	ASK/FSK	40	10	2.0-5.5	4x10-bit A/D, Comparator	\$2.11	20/SSOP 208 mil
rfPIC12F675H	6	850-930	1792	1024 x 12	128	64	1	1	20	Yes	ASK/FSK	40	10	2.0-5.5	4x10-bit A/D, Comparator	\$2.11	20/SSOP 208 mil
rfPIC12F675K	6	290-350	1792	1024 x 12	128	64	1	1	20	Yes	ASK/FSK	40	10	2.0-5.5	4x10-bit A/D, Comparator	\$2.11	20/SSOP 208 mil

RF Receivers

Product	Frequency Range (MHz)	Modulation	Data Rate (kbps)	Sensitivity (dBm)	IF Frequency Range (MHz)	Operating Voltage	RSSI	Selectable LNA Gain	Volume Pricing†	Packages
rfRXD0420	300-450	ASK, FSK, FM	80	-111	0.455-21.4	2.5-5.5	Yes	Yes	\$1.71	32/LQFP
rfRXD0920	800-930	ASK, FSK, FM	80	-109	0.455-21.4	2.5-5.5	Yes	Yes	\$2.62	32/LQFP


† - Pricing subject to change; please contact your Microchip representative for most current pricing.

Terms and Definitions


1 KB	1024 bytes	EEPROM	Electrically Erasable Programmable Read Only Memory	mTouch™	Proprietary Touch Sensing Technology
1 Kw	1024 words	EFT	Electrical Fast Transient	PIC24	16-bit Core
18F/PIC18	16-bit instruction word – 75/83 instructions	EMC	Electromagnetic Compatibility	PIC32	32-bit Core
ADC	Analog to Digital Converter	EMI	Electromagnetic Interference	PLVD	Programmable Low Voltage Detect
AUSART	Addressable Universal Synchronous Asynchronous Receiver Transceiver	EMR/Enhanced-MidRange	14-bit instruction word – 49 instructions (denoted as PIC1XF1XXX)	POR/POOR	Power ON Reset/Power ON/OFF Reset
BL/Baseline	12-bit instruction word – 33 instructions	ESD	Electrostatic Discharge	PWM	Pulse Width Modulation
BOR/PBOR	Brown Out Reset/Programmable Brown Out Reset	EUSART	Enhanced Universal Synchronous Asynchronous Receiver Transceiver	RAM	Random Access Memory
CCP/ECPP	Capture Compare PWM/Enhanced Capture Compare PWM	EWDT/WDT	Extended Watch Dog Timer/Watch Dog Timer	RTCC	Real-Time Clock Calendar
CLC	Configurable Logic Cell	HV	High Voltage	Source/Sink Current	All Products Support 25 mA per I/O
Comp	Capacitive Sensing implemented via Comparator	ICD	In-Circuit Debug	SR Latch	Set Reset Latch
CRC	Cyclical Redundancy Check	ICE	In-Circuit Emulation	SRAM	Static Random Access Memory
CSM	mTouch – Capacitive Sensing Module	ICSP™	In-Circuit Serial Programming™	SPI	Serial Peripheral Interface
CSP	Chip Scale Package	IDE	Integrated Development Environment	T1G	Timer 1 Gate
CTMU	mTouch – Charge Time Measurement Unit	LCD	Liquid Crystal Display	USART	Universal Synchronous Asynchronous Receiver Transceiver
CVD	Charge Voltage Divide (Capacitive Sensing Implemented via ADC)	LDO	Low Drop-Out voltage regulator	USB	Universal Serial Bus
CWG	Complimentary Waveform Generator	LF	Low Power Flash	USB (Full Speed)	12 Mb/s Data Rate
DDS	Direct Digital Synthesis	MiC/iC	Master Inter-Integrated Circuit bus/Inter-Integrated Circuit bus	USB OTG	USB On-The-Go
DSM	Data Signal Modulator	MIPS	Million Instructions Per Second	XLP	nanoWatt XLP eXtreme Low Power Technology
dsPIC	16-bit Core with DSP	MR/Mid-Range	14-bit instruction word – 35 instructions		
ECAN	Enhanced Controller Area Network	MSSP/SSP	Master/Synchronous Serial Port (I²C & SPI Peripheral)		

Product Packages


Small Outline



Dual Flat No Lead DFN




Quad Flat No Lead QFN



Plastic Shrink Small Outline SSOP



Plastic Thin Shrink Small Outline TSSOP



Plastic Small Outline SOIC




Packages are shown approximate size.

Additional packages are available – contact your local Microchip sales office for additional information.

For detailed dimensions, view our Package Drawing and Dimensions Specification at: www.microchip.com/packaging

Product Packages


Plastic Thin Quad Flatpack TQFP




Plastic Quad Flatpack QFP



Ball Grid Array BGA




Plastic Dual In-Line PDIP




Additional SST Package Options

NOR Flash Memory



RF Devices



8051-based Microcontrollers



Packages are shown approximate size.

Additional packages are available – contact your local Microchip sales office for additional information.

For detailed dimensions, view our Package Drawing and Dimensions Specification at: www.microchip.com/packaging

Support

Microchip is committed to supporting its customers in developing products faster and more efficiently. We maintain a worldwide network of field applications engineers and technical support ready to provide product and system assistance. In addition, the following service areas are available at www.microchip.com:

- **Support** link provides a way to get questions answered fast: <http://support.microchip.com>
- **Sample** link offers evaluation samples of any Microchip device: <http://sample.microchip.com>
- **Forum** link provides access to knowledge base and peer help: <http://forum.microchip.com>
- **Buy** link provides locations of Microchip Sales Channel Partners: www.microchip.com/sales

Sales Office Listing

AMERICAS

Atlanta
Tel: 678-957-9614

Boston
Tel: 774-760-0087

Chicago
Tel: 630-285-0071

Cleveland
Tel: 216-447-0464

Dallas
Tel: 972-818-7423

Detroit
Tel: 248-538-2250

Kokomo
Tel: 765-864-8360

Los Angeles
Tel: 949-462-9523

Santa Clara
Tel: 408-961-6444

Toronto
Mississauga, Ontario
Tel: 905-673-0699

EUROPE

Austria - Wels
Tel: 43-7242-2244-39

Denmark - Copenhagen
Tel: 45-4450-2828

France - Paris
Tel: 33-1-69-53-63-20

Germany - Munich
Tel: 49-89-627-144-0

Italy - Milan
Tel: 39-0331-742611

Netherlands - Drunen
Tel: 31-416-690399

Spain - Madrid
Tel: 34-91-708-08-90

UK - Wokingham
Tel: 44-118-921-5869

Training

If additional training interests you, then Microchip can help. We continue to expand our technical training options, offering a growing list of courses and in-depth curriculum locally, as well as significant online resources – whenever you want to use them.

- Regional Training Centers: www.microchip.com/rtc
- MASTERS Conferences: www.microchip.com/masters
- Worldwide Seminars: www.microchip.com/seminars
- eLearning: www.microchip.com/webseminars
- Resources from our Distribution and Third Party Partners
www.microchip.com/training

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733

China - Beijing
Tel: 86-10-8528-2100

China - Chengdu
Tel: 86-28-8665-5511

China - Chongqing
Tel: 86-23-8980-9588

China - Hong Kong SAR
Tel: 852-2401-1200

China - Nanjing
Tel: 86-25-8473-2460

China - Qingdao
Tel: 86-532-8502-7355

China - Shanghai
Tel: 86-21-5407-5533

China - Shenyang
Tel: 86-24-2334-2829

China - Shenzhen
Tel: 86-755-8203-2660

China - Wuhan
Tel: 86-27-5980-5300

China - Xiamen
Tel: 86-592-2388138

China - Xian
Tel: 86-29-8833-7252

China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444

India - New Delhi
Tel: 91-11-4160-8631

India - Pune
Tel: 91-20-2566-1512

Japan - Yokohama
Tel: 81-45-471- 6166

Korea - Daegu
Tel: 82-53-744-4301

Korea - Seoul
Tel: 82-2-554-7200

Malaysia - Kuala Lumpur
Tel: 60-3-6201-9857

Malaysia - Penang
Tel: 60-4-227-8870

Philippines - Manila
Tel: 63-2-634-9065

Singapore
Tel: 65-6334-8870

Taiwan - Hsin Chu
Tel: 886-3-6578-300

Taiwan - Kaohsiung
Tel: 886-7-536-4818

Taiwan - Taipei
Tel: 886-2-2500-6610

Thailand - Bangkok
Tel: 66-2-694-1351

7/21/09

Microcontrollers • Digital Signal Controllers • Analog • Memory • Wireless

Information subject to change. The Microchip name and logo, the Microchip logo, dsPIC, MPLAB and PIC are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries. All other trademarks mentioned herein are property of their respective companies. © 2010, Microchip Technology Incorporated. All Rights Reserved. Printed in the U.S.A. 11/10
DS01308D




MICROCHIP
www.microchip.com

Microchip Technology Inc.
2355 W. Chandler Blvd.
Chandler, AZ 85224-6199