



SECTION 1D

FUSED TERMINAL BLOCKS

Mouldings:	Nylon 6.6, grey, UL94 V2, (fuseholder black)
Inserts:	Tinned brass
Fuse contacts:	Stainless steel
Screws:	M3 x 6, steel, zinc plated and yellow chromated
Wire protectors:	Stainless steel
Maximum working temp:	100°C continuous
Current rating:	10 amp to EN60335-1
Voltage rating:	Terminal block - 380V Fuseholder - 250V
Conductor size:	
Without wire protector:	Up to 6mm ²
With wire protector :	Up to 2.5mm ²
Fuse size:	20mm x 5mm
Fixing centres:	Peg to earth screw - 15mm Peg to fixing hole - 20mm

Marking: special printing available. Please provide sketch.

Fuses: see catalogue 2 section I for details.

High Temperature: details upon request.

Series 503SI fused terminal blocks are available in unearthed versions from 1 to 5 pole and earthed versions from 3 to 5 pole. A common dovetail enables mixed assemblies to be constructed by clipping on additional 1 pole lengths to provide multiple versions of fused and unfused terminals. All variations can be supplied with or without wire protectors.

Screws: 503SIES - M3x12, Posi
Washers: 503SITW - M3

 (Not "E" types)

PART NUMBER CODE

With earth protectors
Enter E

Without protectors
Leave blank

Number of poles
Enter 01 - 05

Without protectors
Enter DS

5 0 3 S 1 - - - -

The logo for Metway Networks, featuring the word "metway" in a large, lowercase, serif font, with "CONNECT" in a smaller, uppercase, sans-serif font above it and "NET-WORKS" in a smaller, uppercase, sans-serif font below it. A blue wavy line is positioned to the right of the word "metway".

01273 431600

01273 439288

e

sales@metway.co.uk