

To all our customers

Regarding the change of names mentioned in the document, such as Mitsubishi Electric and Mitsubishi XX, to Renesas Technology Corp.

The semiconductor operations of Hitachi and Mitsubishi Electric were transferred to Renesas Technology Corporation on April 1st 2003. These operations include microcomputer, logic, analog and discrete devices, and memory chips other than DRAMs (flash memory, SRAMs etc.)

Accordingly, although Mitsubishi Electric, Mitsubishi Electric Corporation, Mitsubishi Semiconductors, and other Mitsubishi brand names are mentioned in the document, these names have in fact all been changed to Renesas Technology Corp. Thank you for your understanding. Except for our corporate trademark, logo and corporate statement, no changes whatsoever have been made to the contents of the document, and these changes do not constitute any alteration to the contents of the document itself.

Note : Mitsubishi Electric will continue the business operations of high frequency & optical devices and power devices.

Renesas Technology Corp.
Customer Support Dept.
April 1, 2003

4-28


M5278LXX, M5278LXXM

**(5V, 5.6V, 8V, 9V, 10V, 12V, 15V) 3-TERMINAL FIXED POSITIVE
OUTPUT VOLTAGE REGULATOR (WITH FOLD-BACK PROTECTION CIRCUIT)**

ABSOLUTE MAXIMUM RATINGS ($T_A=25^{\circ}\text{C}$)

Symbol	Parameter	Ratings	Unit
V_I	Input voltage	36	V
I_L	Load current	100	mA
P_d	Power dissipation	900(3P5)/500(3P2)	mW
T_{opr}	Operating temperature	$-20 \sim +75$	$^{\circ}\text{C}$
T_{stg}	Storage temperature	$-55 \sim +150$	$^{\circ}\text{C}$

STANDARD CONNECTION



C_I , C_O are capacitors to prevent oscillation.
Make connections as close to the IC as possible.

ELECTRICAL CHARACTERISTICS

M5278L05 ($V_I=10\text{V}$, $I_L=40\text{mA}$, $T_A=25^{\circ}\text{C}$, $C_I=0.33\mu\text{F}$, $C_O=0.1\mu\text{F}$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V_O	Output voltage		4.75	5.0	5.25	V
$R_{reg.in}$	Input regulation	$7.5\text{V} \leq V_I \leq 20\text{V}$		50	200	mV
		$8\text{V} \leq V_I \leq 20\text{V}$		30	150	
$R_{reg.L}$	Load regulation	$1\text{mA} \leq I_L \leq 100\text{mA}$		10	60	mV
		$1\text{mA} \leq I_L \leq 40\text{mA}$		5	30	
V_O	Output voltage	$7.5\text{V} \leq V_I \leq 20\text{V}$, $1\text{mA} \leq I_L \leq 40\text{mA}$	4.7	5.0	5.3	V
		$V_I=10\text{V}$, $1\text{mA} \leq I_L \leq 70\text{mA}$	4.7	5.0	5.3	
I_B	Bias current	$I_L=0$		4.8	6.7	mA
ΔI_B	Bias current variability	$8\text{V} \leq V_I \leq 20\text{V}$, $I_L=40\text{mA}$		0.1	1.5	mA
		$V_I=10\text{V}$, $1\text{mA} \leq I_L \leq 40\text{mA}$			0.2	
V_{NO}	Output noise voltage	BW: 10Hz~100kHz		49		μVrms
RR	Ripple rejection ratio	$f=120\text{Hz}$, $V_{in}=0\text{dBm}$	63	73		dB
V_I-V_O	Minimum input-output voltage difference			2.0		V
I_{LP}	Peak load current			130		mA
I_{OS}	Output short holding current			16.5		mA
TC_{VO}	Temperature coefficient of output voltage	$I_L=5\text{mA}$		-0.6		mV/ $^{\circ}\text{C}$

M5278LXX, M5278LXXM

(5V, 5.6V, 8V, 9V, 10V, 12V, 15V) 3-TERMINAL FIXED POSITIVE OUTPUT VOLTAGE REGULATOR (WITH FOLD-BACK PROTECTION CIRCUIT)

M5278L56 ($V_i=11\text{V}$, $I_L=40\text{mA}$, $T_a=25^\circ\text{C}$, $C_i=0.33\mu\text{F}$, $C_O=0.1\mu\text{F}$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V_O	Output voltage		5.32	5.6	5.88	V
Reg-in	Input regulation	$8.5\text{V} \leq V_i \leq 21\text{V}$		50	200	mV
		$9\text{V} \leq V_i \leq 21\text{V}$		30	150	
Reg-L	Load regulation	$1\text{mA} \leq I_L \leq 100\text{mA}$		10	60	mV
		$1\text{mA} \leq I_L \leq 40\text{mA}$		5	30	
V_O	Output voltage	$8.5\text{V} \leq V \leq 21\text{V}$, $1\text{mA} \leq I_L \leq 40\text{mA}$	5.27	5.6	5.93	V
		$V_i=11\text{V}$, $1\text{mA} \leq I_L \leq 70\text{mA}$	5.27	5.6	5.93	
I_B	Bias current	$I_L=0$		4.8	6.7	mA
ΔI_B	Bias current differential	$9\text{V} \leq V_i \leq 21\text{V}$, $I_L=40\text{mA}$		0.1	1.5	mA
		$V_i=11\text{V}$, $1\text{mA} \leq I_L \leq 40\text{mA}$			0.2	
V_{NO}	Output noise voltage	BW: 10Hz~100kHz		55		μV_{rms}
RR	Ripple rejection ratio	$f=120\text{Hz}$, $V_{in}=0\text{dBm}$	63	73		dB
V_i-V_O	Minimum input-output voltage difference			2.0		V
I_{LP}	Peak load current			150		mA
I_{OS}	Output short circuit sustain current			16.5		mA
TC_{VO}	Temperature coefficient of output voltage	$I_L=5\text{mA}$		-0.65		mV/°C

M5278L08 ($V_i=14\text{V}$, $I_L=40\text{mA}$, $T_a=25^\circ\text{C}$, $C_i=0.33\mu\text{F}$, $C_O=0.1\mu\text{F}$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V_O	Output voltage		7.6	8.0	8.4	V
Reg-in	Input regulation	$10.5\text{V} \leq V_i \leq 23\text{V}$		60	200	mV
		$11\text{V} \leq V_i \leq 23\text{V}$		40	150	
Reg-L	Load regulation	$1\text{mA} \leq I_L \leq 100\text{mA}$		10	30	mV
		$1\text{mA} \leq I_L \leq 40\text{mA}$		5	40	
V_O	Output voltage	$10.5\text{V} \leq V_i \leq 23\text{V}$, $1\text{mA} \leq I_L \leq 40\text{mA}$	7.52	8.0	8.48	V
		$V_i=14\text{V}$, $1\text{mA} \leq I_L \leq 70\text{mA}$	7.52	8.0	8.48	
I_B	Bias current	$I_L=0$		4.8	6.7	mA
ΔI_B	Bias current differential	$10.5\text{V} \leq V_i \leq 23\text{V}$, $I_L=40\text{mA}$		0.1	1.5	mA
		$V_i=14\text{V}$, $1\text{mA} \leq I_L \leq 40\text{mA}$			0.2	
V_{NO}	Output noise voltage	BW: 10Hz~100kHz		80		μV_{rms}
RR	Ripple rejection ratio	$f=120\text{Hz}$, $V_{in}=0\text{dBm}$		56		dB
V_i-V_O	Minimum input-output voltage difference			2.0		V
I_{LP}	Peak load current			150		mA
I_{OS}	Output short circuit sustain current			12.5		mA
TC_{VO}	Temperature coefficient of output voltage	$I_L=5\text{mA}$		-0.9		mV/°C

M5278LXX, M5278LXXM

(5V, 5.6V, 8V, 9V, 10V, 12V, 15V) 3-TERMINAL FIXED POSITIVE OUTPUT VOLTAGE REGULATOR (WITH FOLD-BACK PROTECTION CIRCUIT)

M5278L09 ($V_i=16V$, $I_L=40mA$, $T_a=25^\circ C$, $C_i=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V_O	Output voltage		8.55	9.0	9.45	V
Reg_{in}	Input regulation	$12V \leq V_i \leq 24V$		60	225	mV
		$13V \leq V_i \leq 24V$		40	170	
Reg_L	Load regulation	$1mA \leq I_L \leq 100mA$		10	90	mV
		$1mA \leq I_L \leq 40mA$		5	40	
V_O	Output voltage	$12V \leq V_i \leq 24V$, $1mA \leq I_L \leq 40mA$	8.46	9.0	9.54	V
		$V_i=16V$, $1mA \leq I_L \leq 70mA$	8.46	9.0	9.54	
I_B	Bias current	$I_L=0$		4.8	6.7	mA
ΔI_B	Bias current differential	$13V \leq V_i \leq 24V$, $I_L=40mA$		0.1	1.5	mA
		$V_i=16V$, $1mA \leq I_L \leq 40mA$			0.2	
V_{NO}	Output noise voltage	BW: 10Hz~100kHz		90		μV_{rms}
RR	Ripple rejection ratio	$f=120Hz$, $V_{in}=0dBm$		60		dB
V_i-V_O	Minimum input-output voltage difference			2.0		V
I_{LP}	Peak load current			150		mA
I_{OS}	Output short circuit sustain current			12.5		mA
TC_{VO}	Temperature coefficient of output voltage	$I_L=5mA$		-0.65		mV/°C

M5278L10 ($V_i=17V$, $I_L=40mA$, $T_a=25^\circ C$, $C_i=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V_O	Output voltage		9.5	10.0	10.5	V
Reg_{in}	Input regulation	$12.5V \leq V_i \leq 25V$		70	230	mV
		$13V \leq V_i \leq 25V$		50	170	
Reg_L	Load regulation	$1mA \leq I_L \leq 100mA$		10	90	mV
		$1mA \leq I_L \leq 40mA$		5	45	
V_O	Output voltage	$12.5V \leq V_i \leq 25V$, $1mA \leq I_L \leq 40mA$	9.4	10.0	10.6	V
		$V_i=17V$, $1mA \leq I_L \leq 70mA$	9.4	10.0	10.6	
I_B	Bias current	$I_L=0$		4.8	6.7	mA
ΔI_B	Bias current differential	$13V \leq V_i \leq 25V$, $I_L=40mA$		0.1	1.5	mA
		$V_i=17V$, $1mA \leq I_L \leq 40mA$			0.2	
V_{NO}	Output noise voltage	BW: 10Hz~100kHz		100		μV_{rms}
RR	Ripple rejection ratio	$f=120Hz$, $V_{in}=0dBm$	52	59		dB
V_i-V_O	Minimum input-output voltage difference			2.0		V
I_{LP}	Peak load current			130		mA
I_{OS}	Output short circuit sustain current			12.5		mA
TC_{VO}	Temperature coefficient of output voltage	$I_L=5mA$		-0.9		mV/°C

MITSUBISHI <LINEAR ICs>
M5278LXX, M5278LXXM

**(5V, 5.6V, 8V, 9V, 10V, 12V, 15V) 3-TERMINAL FIXED POSITIVE
OUTPUT VOLTAGE REGULATOR (WITH FOLD-BACK PROTECTION CIRCUIT)**

M5278L12 ($V_I=19V$, $I_L=40mA$, $T_a=25^\circ C$, $C_I=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V_O	Output voltage		11.4	12.0	12.6	V
$R_{reg.in}$	Input regulation	$14.5V \leq V_I \leq 27V$		70	250	mV
		$16V \leq V \leq 27V$		50	200	
$R_{reg.L}$	Load regulation	$1mA \leq I_L \leq 100mA$		10	100	mV
		$1mA \leq I_L \leq 40mA$		5	50	
V_O	Output voltage	$14.5V \leq V_I \leq 27V$, $1mA \leq I_L \leq 40mA$	11.3	12.0	12.7	V
		$V_I=19V$, $1mA \leq I_L \leq 70mA$	11.3	12.0	12.7	
I_B	Bias current	$I_L=0$		4.8	6.7	mA
ΔI_B	Bias current differential	$16V \leq V_I \leq 27V$, $I_L=40mA$		0.1	1.5	mA
		$V_I=19V$, $1mA \leq I_L \leq 40mA$			0.2	
V_{NO}	Output noise voltage	BW: 10Hz~100kHz		110		μV_{rms}
RR	Ripple rejection ratio	$f=120Hz$, $V_{in}=0dBm$	50	56		dB
V_I-V_O	Minimum input-output voltage difference			2.0		V
I_{LP}	Peak load current			150		mA
I_{OS}	Output short circuit sustain current			12.5		mA
TC_{VO}	Temperature coefficient of output voltage	$I_L=5mA$		-1.0		mV/°C


M5278L15 ($V_I=23V$, $I_L=40mA$, $T_a=25^\circ C$, $C_I=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V_O	Output voltage		14.25	15.0	15.75	V
$R_{reg.in}$	Input regulation	$17.5V \leq V_I \leq 30V$		80	300	mV
		$20V \leq V_I \leq 30V$		60	250	
$R_{reg.L}$	Load regulation	$1mA \leq I_L \leq 100mA$		10	150	mV
		$1mA \leq I_L \leq 40mA$		5	75	
V_O	Output voltage	$17.5V \leq V_I \leq 30V$, $1mA \leq I_L \leq 40mA$	14.1	15.0	15.9	V
		$V_I=23V$, $1mA \leq I_L \leq 70mA$	14.1	15.0	15.9	
I_B	Bias current	$I_L=0$		4.8	6.7	mA
ΔI_B	Bias current differential	$23V \leq V_I \leq 30V$, $I_L=40mA$		0.1	1.5	mA
		$V_I=23V$, $1mA \leq I_L \leq 40mA$			0.2	
V_{NO}	Output noise voltage	BW: 10Hz~100kHz		140		μV_{rms}
RR	Ripple rejection ratio	$f=120Hz$, $V_{in}=0dBm$	40	45		dB
V_I-V_O	Minimum input-output voltage difference			2.0		V
I_{LP}	Peak load current			150		mA
I_{OS}	Output short circuit sustain current			12.5		mA
TC_{VO}	Temperature coefficient of output voltage	$I_L=5mA$		-0.9		mV/°C


**(5V, 5.6V, 8V, 9V, 10V, 12V, 15V) 3-TERMINAL FIXED POSITIVE
 OUTPUT VOLTAGE REGULATOR (WITH FOLD-BACK PROTECTION CIRCUIT)**

TYPICAL CHARACTERISTICS


THERMAL DERATING (MAXIMUM RATING)




BIAS CURRENT VS. INPUT VOLTAGE




BIAS CURRENT VS. INPUT VOLTAGE




OUTPUT VOLTAGE VS. INPUT VOLTAGE



OUTPUT VOLTAGE VS. INPUT VOLTAGE




OUTPUT VOLTAGE VS. INPUT VOLTAGE




M5278LXX, M5278LXXM

(5V, 5.6V, 8V, 9V, 10V, 12V, 15V) 3-TERMINAL FIXED POSITIVE
OUTPUT VOLTAGE REGULATOR (WITH FOLD-BACK PROTECTION CIRCUIT)


OUTPUT VOLTAGE VS. INPUT VOLTAGE




OUTPUT VOLTAGE VS. LOAD CURRENT




BIAS CURRENT VS.
AMBIENT TEMPERATURE



OUTPUT VOLTAGE VS.
AMBIENT TEMPERATURE




RIPPLE REJECTION VS. FREQUENCY



M5278LXX, M5278LXXM

(5V, 5.6V, 8V, 9V, 10V, 12V, 15V) 3-TERMINAL FIXED POSITIVE
OUTPUT VOLTAGE REGULATOR (WITH FOLD-BACK PROTECTION CIRCUIT)



FOLD-BACK PROTECTION CIRCUIT

The M5278L series has been designed to be complete with three-pin, 78L type regulators manufactured by other companies for applications with loading currents in the 100mA class. They additionally have an internalized fold-back protection circuit for protection against shorted loads.

Other 78L units do have an internalized protection circuit known as a drooping type circuit that are rather simple, merely limiting maximum loading current. When large current begins to flow in these units due to a short circuit, abnormal temperatures are generated leading to breakdown and effective setting reliability.

As shown in the diagram, the fold-back protection circuit employed in the M5278L decreases immediately excessive current caused by a short in the load. This not only improves set reliability but permits the elimination of such protection circuits as fuses in the protection circuit.

PRECAUTIONS FOR USE

The current-control circuit requires that, as an IC power supply, this device be operated within the fold-back operating range shown in the accompanying chart.

OUTPUT VOLTAGE VS. LOAD CURRENT

