


PHYSICAL DIMENSIONS:

A	6.99 [.275]	± 0.10 [.004]
B	5.72 [.225]	± 0.10 [.004]
B ₁	6.73 [.265]	MAX
C	9.53 [.375]	± 0.15 [.006]
C ₁	10.31 [.406]	MAX.
D	2.41 [.095]	± 0.08 [.003]
E	0.89 [.035]	± 0.13 [.005]
E ₁	1.91 [.075]	± 0.13 [.005]
WIRE:		
T ₁	1.91 [.075]	± 0.25 [.010]
T ₂	0.38 [.015]	TYP.
T ₃	0.38 [.015]	TYP.

CM2722R201R-10

**UNCONTROLLED
DOCUMENT**



RoHS



ELECTRICAL CHARACTERISTICS:

Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	200	
Minimum	160	
Maximum	—	0.02 5,000 mA


NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS, 13" REELS 500 PCS per REEL.
2. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
3. REF. CARRIER TAPE SPECIFICATION# CART2722-2P.
4. TERMINATION FINISH IS 100% TIN.
5. THIS PART HAS NO PIN POLARITY.
6. OPERATION TEMPERATURE (INCLUDING SELF-HEATING): -40 ~ +125°C.


Z vs. FREQUENCY (C,O,N)




LAND PATTERNS FOR REFLOW SOLDERING



EQUIVALENT CIRCUIT
NO POLARITY



RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm (INCHES).

This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			Laird		
D	ADD NOTE 6	08/30/12	QIU	PROJECT/PART NUMBER:	CM2722R201R-10
C	UPDATE COMPANY LOGO ADD EQUIVALENT CIRCUIT	01/30/09	JRK	REV D	PART TYPE: ASSEMBLY
B	UPDATE COMPANY LOGO & ROHS SYMB.	11/14/07	JRK	DATE: 06/01/04	SCALE: NTS
A	ORIGINAL DRAFT	6/01/04	JRK	CAD #	SHEET: 1 of 2
REV	DESCRIPTION	DATE	INT	CM2722R201R-10-D-1	H0275-2