

V4L

- Characteristics
- long overtravel of 2.2 mm minimum
 - sealed to (IP6K7) option
 - pre-wired option
 - solder terminals

Rating 250 VAC, 5 A

Dimensions (mm) 20 × 11 × 6.4

- Actuator
- plunger
 - plain lever
 - ice break lever

Approvals ENEC, UL, CSA




Preferred Range

Ordering Reference	Actuating Force (N) (ozf)		Sealing	Operating pos. (mm)	Terminal	Circuit	Actuator	Contacts	Electrical rating
V4LS	2,5	9,0	IP6K7	11,7 ± 0,4	Cable 500 mm	C0	Plunger	Ag	250 VAC, 5 A
V4LSA1	2,5	9,0	IP6K7	14,5 ± 0,8	Cable 500 mm	C0	Plain lever	Ag	250 VAC, 5 A
V4LSA2	2,0		IP6K7	16,5 ± 1,0	Cable 500 mm	C0	Plain lever	Ag	250 VAC, 5 A
V4LST7	2,5	9,0	IP6K7	11,7 ± 0,4	Solder	C0	Plunger	Ag	250 VAC, 5 A
V4LST7A1	2,5		IP6K7	14,5 ± 0,8	Solder	C0	Plain lever	Ag	250 VAC, 5 A
V4LST7A2	2,0		IP6K7	14,6 ± 1,0	Solder	C0	Plain lever	Ag	250 VAC, 5 A
V4LT7	2,4	8,6	no symbol	11,7 ± 0,4	Solder	C0	Plunger	Ag	250 VAC, 5 A


Specifications

Housing	Glass fibre reinforced polyamide (PA 6.6)
Plunger	Polyacetal (POM)
Mechanism	Snap-action coil spring mechanism with stainless steel spring. Change-over, normally closed or normally open
Contact carrier	Brass. Moving contact beryllium-copper
Contacts	Fine silver or gold crosspoint
Terminals	V4L – solder tags V4LS – PVC covered leads 0.5 m long
Temperature range °C	–40°C to +85°C
Mechanical life	V4L 2×10^6 cycles/min., V4LS 2×10^5 cycles/min. (impact free actuation)
Protection	V4L series IP40, V4LS series IP6K7, with encapsulated terminals
Mounting	Side mounting to a flat surface
Actuators	Plain lever. Ice break lever
Cowl	Silicon elastomer

Circuit diagram







Dimensions



Recommended maximum electrical ratings

Voltage (VAC)	Resistive load (A) (Ag Contact)	Incandescent lamp load (A) (Ni1 Contact)	Inductive load (A) (Ag Contact)	Voltage (VDC) up to	Resistive load (A) (Ag Contact)	Incandescent lamp load (A) (Ni1 Contact)	Inductive load (A) (Ag Contact)
125	5	2	2	30	5	2	3
250	5	2	2	50	1	0.4	1
				75	0.75	0.3	0.75
				125	0.5	0.2	0.03
				250	0.25	0.1	0.03

Ordering Reference

Actuator	Reference	Actuating Force		Release Force		Free Position		Operating Position		Movement Differential		Total overtravel		Overtravel	
		Maximum (N)	(ozf)	Minimum (N)	(ozf)	Maximum (mm)	(in)	(mm)	(in)	Maximum (mm)	(in)	Minimum (mm)	(in)	Minimum (mm)	(in)
 Plunger	V4LT7	2.4	8,60	0.4	1.44	12.9	0.507	11.7 ± 0.4	0.46 ± 0.012	0.9	0.023	9.2	0.36	2.2	0.09
	V4LST7	2.5	9.00	0.5	1.78	12.9	0.507	11.7 ± 0.4	0.46 ± 0.012	0.9	0.023	9.2	0.36	2.2	0.09
 A1 Lever	V4L...	2.4	8,60	0.4	1.44	14.5	0.57	12.6 ± 0.8	0.59 ± 0.03	1.0	0.04	9.6	0.38	2.2	0.09
	V4LS...	2.5	9.00	0.5	1.78	14.5	0.57	12.6 ± 0.8	0.59 ± 0.03	1.0	0.04	9.6	0.38	2.2	0.09
Width of lever 4.0 mm/0.16 in															
 A2 Lever	V4L...	1.5	5.70	0.3	1.08	16.5	0.65	13.5 ± 1.0	0.53 ± 0.04	1.3	0.05	9.6	0.38	2.9	1.1
	V4LS...	2	7.20	0.3	1.08	16.5	0.65	13.5 ± 1.0	0.53 ± 0.04	1.3	0.05	9.6	0.38	2.9	1.1
Width of lever 4.0 mm/0.16 in															
 F Lever	V4L...	For positions and forces of this actuator please contact Burgess													
	V4LS...														
Width of lever 4.0 mm/0.16 in															

Ordering Reference

Basic type	V4L						Example: V4L						S	T7	C2	A1	G	UL
Type of sealing	S						No symbol, unsealed Sealed IP6K7											
Terminals	T7						No symbol, pre-wired 500 mm with cable FLRY 0.5 mm ² and cable box (V4LS only)											
	T8						Solder 2.95 × 0.5 × 3.55 long PCB 0.8 × 0.5 × 4.0 long											
Circuit	C2						No symbol, change over											
	C4						Normally closed Normally open											
Actuators	A1						No symbol, without lever											
	A2						Plain lever 20.0 mm, fitted at the end opposite to plunger											
	A2						Plain lever 30.0 mm, fitted at the end opposite to plunger											
	F						Special lever F type 20.0 mm, fitted at the end opposite to plunger											
Contact Material	G						No symbol, Ag											
	G						Gold plate on silver (GP)											
	X						Gold alloy on silver palladium crosspoint (AUX)											
Other contact materials on special request																		
Approvals	UL						No symbol, without approval											
	EN						UL and CSA approval											
	EN						ENEC approval only											
	UN						UL, CSA and ENEC approval											
Special Features	/ ☐ ☐ ☐ ☐						Burgess specialise in customer specific solutions. Additional product variants are available or can be provided. If your requirements cannot be satisfied from the options listed, please contact www.saia-burgess.com or your local SB outlet.											