



Ref: PWB LAYOUT



SPECIFICATIONS:

1. INDUCTANCE: @ 10 kHz, 0.1 Vrms,
1 - 4 = 225 uHy MIN
2. DCR: mOHMS
1 - 4 = 0.1 Nom
5 - 8 = 0.1 Nom
3. LEAKAGE INDUCTANCE: 1 - 4, 0.1V @ 100kHz
SHORT 5 - 8 < 0.4 uHy
4. INTERWINDING CAPACITANCE:
1 - 4 to 5 - 8 @ 100 KHz, 1.0V < 15 pf
5. TURNS AND PHASE:
1 - 4 : 5 - 8 = 1 : 1 +/- 2%
- 6 DIELECTRIC STRENGTH:
1500 VAC 1 sec

A						
REV.	DATE	ECN	BY	DESCRIPTION		
TOLERANCES ON			Newava Tech. Watertown, SD 57201 605-886-0264		Transformer, SMD Digital Audio, 1:1	
.XXX + -		.XX + -				
			DATE			
DRAWN:			SCALE		MODEL	
CHECKED: -			-		DRAWING NO.	
APPROVED: -			-		S37211	
			NEXT ASSY:		A	
THIS PRINT MUST NOT BE COPIED IN WHOLE OR IN PART				OR USED DETRIMENTALLY TO OUR INTEREST		
				SHEET 1 OF 1		