



EPOXY COATED, NON-INDUCTIVE, METALLIZED FILM CAPACITORS, RADIAL LEAD

FEATURES

- ☐ VERY SMALL SIZE, HIGHLY RELIABLE BECAUSE OF ITS SELF-HEALING PERFORMANCE
- ☐ COATED WITH EPOXY RESIN FOR SUPERIOR HEAT RESISTANCE, HUMIDITY RESISTANCE AND SOLVENT RESISTANCE
- ☐ RECOMMENDED FOR USE WITH FILTERING, DC BLOCKING, AND COUPLING COMMUNICATIONS EQUIPMENT.

SPECIFICATIONS

OPERATING TEMPERATURE RANGE	-55°C to +125°C with voltage derating of 1.25% per degree C
RATED VOLTAGE (DC)	250V, 400V, 630V
CAPACITANCE RANGE	0.01 to 4.7 MFD
CAPACITANCE TOLERANCE	±10% (K), ±5% (J)
INSULATION RESISTANCE	C < 0.33 MFD. R ≥ 15,000 MEGOHM
	C ≥ 0.33 MFD. RC ≥ 5,000 MEGOHM X MFD
DISSIPATION FACTOR	≤ 0.007 (at 1 KHz, 25°C)
DIELECTRIC STRENGTH	150% of rated voltage for 5 seconds



STANDARD PRODUCTS AND CASE SIZE TABLE (UNIT: mm)

[illegible]

Special sizes & capacitance values are available upon request.