



- ?

[Circuit Board Indicators](#)

?

[Panel Mount Indicators](#)

?

[Solid State Lighting](#)

?

[Traffic Signals](#)

?

[Vehicle Lighting](#)

?

[Rail](#)

?

[Obstruction Lighting](#)

?

[Hazardous Area Lighting](#)

?

[Heliport Lighting](#)

Region:

Product Line:

Circuit Board Indicators

Check stock with our distributors now.

5973323307F

Please note that the stock check**is only applicable** to products *within* **Circuit Board Indicators** and **Panel Mount Indicators**.

Please select a Product Line to search.

Circuit Board Indicators

Part No.:

Text Search:

[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp.
[View PDF File](#)

[Application Notes](#)
[FAQs](#)

[Dialight Ltd \(UK\)](#)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)

menu rendered

Circuit Board Indicators - Surface Mount Indicators	
P/N# 5973323307F	PLCC-2 Single Color
Description	

Forward Current Continuous	30 mA
Forward Current Pulse	100 mA
Derating	from 40° @ .42mA/°C
Solder Temp	240° for 20 sec
Operating Temp	-55~+100° C
Storage Temp	-55~+100° C
Peak Wave Length	523



Operating Characteristics	
LED Position	
Color	Green
Lamp Type	Single Color
LED Type	InGaN
Intensity Min (mcd)	180
Intensity Typ (mcd)	224.0
Intensity Max (mcd)	
Fwd Voltage Min	3.7
Fwd Voltage Typ	4.3
Fwd Voltage Max	525
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	114
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

