




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing per Tucsonix standard test plans and Mil-Std-202 Test Methods.



SILVER PLATED COPPER
 $.050 \pm .010$ [1.27±.25]
(2) PLCS., TINNED.

SILVER PLATED BRASS
5/16" -32 UNEF-2A
THREAD SERIES

.562
[14.28]

.250 ±.010
[6.35 ±.25]

.437 ±.010
[11.09 ±.25]

.060 [1.52]
TYPICAL

.750
[19.05]

NOTES:

1. TUSONIX STANDARD PART NUMBER: 4206-006.
TUSONIX RoHS COMPLIANT PART NUMBER: 4206-006 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: STANDARD PART #: SILVER PLATED WITH 60/40 SOLDER DIP. RoHS PART #: SILVER PLATED WITH 95.5 Sn/3.8 Ag/0.7 Cu SOLDER DIP.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. SUPPLIED WITH SILVER PLATED HEX NUT
AND INTERNAL TOOTH LOCK WASHER.

CAP. (pF)	WORKING VOLTAGE DC (V)	CURRENT dc (A)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
			10 MHz	100 MHz	1 GHz	10 GHz
3000 MIN.	85 °C	125 °C	25 A	10	55	70
	1000	500		70		

REVISION RECORD					
Original Release C.O.	0				
DIM. 562 WAS .567. SM. 12-5-97					
19971203-5-01	6				
NOTE REVISED & DELETED VAR. S.M. 06-08-99					
19990607-3-03	7				
ADDED NOTES 1-3 & CIRCUIT. S.M. 07-29-05					
20050727-3-02	8				
				TOLERANCES unless otherwise specified 2 PLC. DECIMAL \pm  3 PLC. DECIMAL \pm .031 [0.79]	
				ANGLES \pm 	
				Drawn	E.C. 06-07-96
				Approved	B.Mc. 06-07-96
				A	4206-006

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4206-006LF](#)