




- RoHS COMPATIBLE, NOTE 6.
- TOTAL NB OF POSITIONS 04 TO 50
- PACKAGING OPTIONS, NOTE 3.
- PIN STYLE SEE SHEET 2
- PLATING SEE SHEET 2

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE
THERMOPLASTIC. UL94V-0 COLOR: BLACK
2. PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PACKAGING OPTIONS:
 - = POLY BAGS
 - B = TUBE + CAP
 - A = TAPE & REEL WITH CAP, SEE TA840
FOR PRODUCT AVAILABILITY.
 - TR = CUSTOM TAPE & REEL WITH CAP, SEE TA840
ONLY FOR P/N 95278-102TR04LF
AND P/N 95278-101TR10LF

4. 9N MIN RETENTION IN EITHER DIRECTION
5. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$
6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- a – PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL UNDERPLATE.
- b – MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDES IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- c – LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d – LEGAL STATEMENT: SEE GS-47-0004



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK			
ltr ecn no dr date				tolerances unless otherwise specified				 mm 		title			
N F08-0148 RTR 08.03.31				angles linear		X.X ±0.3				UNSHR.HEADER DR SMT			
P F08-0253 LMU 08.12.10						X.XX ±0.13							
R F10-0008 LMU 10.03.09						X.XXX ±0.05							
S B-18789 LMU 14.09.11				dr		D.LE 01.01.24							dwg no
T B-18983 LMU 14.10.03				enrg		JM.C 01.01.24				95278		A.	
U B-20276 LMU 15.02.16				chr		JM.C 01.01.24				type CUSTOMER Drawing			
V B-20561 AMA 15.03.26				appd		JF.N 01.01.24							
sheet index		revision sheet		V	T								
		1 2											

PIN	STYLE	MATING
01		5.9
02		8
03		9.9
04		11.4
05		9.2
06		10.4
07		5.3
09		17.00
10		8.10
11		8.50
12		3.05
13		14.35
14		4.00

PLATING


1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

4 = 2µm TIN MIN FULL PLATED

5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

– 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS



mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
N	F08-0253	LMU	08.12.10	angles	linear	mm	UNSHR.HEADER
P	B-18789	LMU	14.09.11				DR SMT
R	B-18983	LMU	14.10.03			scale N/A	
S	B-20276	LMU	15.02.16	dr	D.LE	01.01.24	dwg no
T	B-20561	AMA	15.03.26	enr	JM.C	01.01.24	sheet 2 of -
				chr	JM.C	01.01.24	size
				appd	JF.N	01.01.24	A3
sheet index		revision sheet					type CUSTOMER Drawing