




FAGOR ELECTRONICS

2 Amp. Silicon Rectifier Diodes

Tol-15

Dimensions in mm.

DO-15
(Plastic)

Mounting instructions

1. Min. distance from body to soldering point, 4 mm.
2. Max. solder temperature, 350°C.
3. Max. soldering time, 3,5 sec.
4. Do not bend lead at a point closer than 2 mm. to the body.

Voltage
50 to 1.000 V.Current
2.0 A. at 55°C.

- Low cost
- Diffused junction
- High current capability
- The plastic material carries U/L recognition 94 V-0
- Terminals: Axial Leads
- Polarity: Color band denotes cathode

Maximum Ratings, according to IEC publication No. 134





		RF 2001	RF 2002	RF 2003	RF 2004	RF 2005	RF 2006	RF 2007
V_{RRM}	Peak recurrent and non recurrent reverse voltage (V)	50	100	200	400	600	800	1000
$I_{F(AV)}$	Forward current at $T_{amb} = 55^\circ\text{C}$	2 A						
I_{FRM}	Recurrent peak forward current	20 A						
I_{FSM}	8,3 ms. peak forward surge current	70 A						
T_j	Max. operating temperature	175°C						
T_{stg}	Storage temperature range	- 65 to + 175 °C						

Electrical Characteristics at $T_{amb} = 25^\circ\text{C}$

V_F	Max. forward drop at $I_F = 2\text{ A}$	1.1V
I_R	Reverse current at V_{RRM} at 25°C	5 μA
R_{thja}	Max. thermal resistance ($I = 10\text{ mm.}$)	45° C/W

FAGOR ELECTRONICS


Characteristic Curves




Package Outlines

Dimensions in mm.


1 DO-41
(Plastic)




2 DO-15
F-126
58 A 2
(Plastic)




3 DO-27 A
DO-201 AD
(Plastic)





4 DO-201 AE
(Plastic)






5 P-6
(Plastic)



7




6




Package Outlines

Dimensions in mm


8




9



10




11




Package Outlines

Dimensions in mm.


12



13




14



15

DF - M






	mm	Pulgadas
A	6.2 - 6.5	0.245" - 0.255"
B	7.4 - 7.9	0.285" - 0.315"
C	7.6 - 8.9	0.300" - 0.350"
D	6.6 - 8.9	0.260" - 0.270"
D ₁	6 - 6.2	0.235" - 0.245"
E	3.8 - 4.6	0.150" - 0.180"
F	5 - 5.2	0.195" - 0.205"
G	2.5 - 2.6	0.100" - 0.102"
H	1.27 - 2.03	0.045" - 0.080"
I	0.46 - 0.56	0.018" - 0.022"

Dimensions in mm

REEL PACKAGING (Under IEC-CEI 286-1 and RS-296 D)


CASE TYPE (OUTLINE)	REEL DIMENSIONS					UNITS PER REEL	APROX GROSS WEIGHT PER REEL PACKED
	K	b	S	m	a		
(1) DO41 (Plastic)	6 4	53 ±2	5 ±0.5	1 2	6 ±1	6000	2.5 kg (5.52 Lbs)
(2) DO15 (Plastic)	7 85	53 ±2	5 ±0.5	1 2	6 ±1	5000	2.3 kg (5.07 Lbs)
(3) DO201AD (Plastic) (4) DO201AE (Plastic)	11	53 ±2	10 ±0.5	1.2	6 ±1	1500	2 kg (4.41 Lbs)
(5) P-6 (Plastic)	11 27	53 ±2	10 ±0.5	1.2	6 ±1	1000	3 kg (6.61 Lbs)

REEL PACKAGING



AMMO BOX PACKAGING (SUFFIX "AMP")

OUTLINES	BOX SIZE	UNITS PER BOX	APROX GROSS WEIGHT PER REEL PACKED
D0-41 (Plastic)	330 x 75 x 145	6000	2 20 kg (4 85 Lbs)
D0-15 (Plastic)	330 x 75 x 145	5000	2 20 kg (4 85 Lbs)
D0-201AD (Plastic)	330 x 75 x 145	1500	1 85 kg (4 08 Lbs)
D0-201ED (Plastic)	330 x 75 x 145	1500	1 85 kg (4 08 Lbs)
P-600	330 x 75 x 145	500	1 2 kg (2 65 Lbs)

DIL PACKAGING
ANTISTATIC PLASTIC TUBE


BOX PACKAGING


DEVICE TYPE (OUTLINE)	BOX SIZE	UNITS PER BOX	APROX GROSS WEIGHT
(6) (7) HVR3. HVR4 HVR082 (7) = Suffix E1	70 x 105 x 205	(6) 250 (7) 200	0 710 kg (1 560 Lbs)
(8) B C800, C1000, C1500 R, WL F, WF / (*A*)	70 x 105 x 205	500 / (1.500)	0 650 kg (1 430 Lbs)
(9) B C1500/1000, C2000/1500	70 x 105 x 205	500	1 100 kg (2 425 Lbs)
(10) B . C3700/2200	70 x 105 x 205	100	1 100 kg (2 425 Lbs)
(10) B . C500/3300, C5000/3300-400	70 x 105 x 205	100	1 100 kg (2 425 Lbs)
(11) FBP, 2FBP	215 x 85 x 335	500	2 10 kg (4.62 Lbs)
(12) FBU 4 - 6 - 8	270 x 90 x 400	500	4 20 kg (9 23 Lbs)
(13) FB 10 - 15 - 25 - 35 - 50 B 10 - 15 - 25 - 35 - 50	70 x 105 x 205	50	0 850 kg (1.872 Lbs)
(14) FB 10L - 15L - 25L B 10L - 15L - 25L	35 x 135 x 205	20	0.350 kg (0.770 Lbs)
DF - M	540 x 145 x 110	5 600	4 0 kg (8 82 Lbs.)


Standard lead forming specifications


Dimensions in mm.


Plastic Cases


DO-41		Type	Dimensions		
			a	b	RM
		C2-3	3 ± 0.5	43 ± 0.5	10 ± 0.5
		C2-5	10 ± 0.5	113 ± 0.5	10 ± 0.5
		C2-8	4 ± 0.5	53 ± 0.5	10 ± 0.5

DO-15		Type	Dimensions		
			a	b	RM
		C2-3	3 ± 0.5	45 ± 0.5	10 ± 0.5
		C2-5	10 ± 0.5	115 ± 0.5	10 ± 0.5
		C2-8	4 ± 0.5	55 ± 0.5	10 ± 0.5

DO-201AD DO-27A (d = 1.27)		Type	Dimensions		
			a	b	RM
		C2-1	35 ± 0.5	6 ± 0.5	15 ± 0.5
		C2-2	4 ± 0.5	65 ± 0.5	15 ± 0.5
		C2-4	75 ± 0.3	10 ± 0.3	178 ± 0.15
		C2-6	35 ± 0.5	6 ± 0.5	175 ± 0.5
		C2-7	45 ± 0.5	7 ± 0.5	21 ± 0.5
		C2-11	45 ± 0.5	7 ± 0.5	175 ± 0.5
		C2-12	125 ± 0.5	15 ± 0.5	175 ± 0.5
		C2-13	16 ± 0.5	185 ± 0.5	152 ± 0.5
		C2-14	75 ± 0.5	10 ± 0.5	15 ± 0.5
		C2-17	4 ± 0.5	85 ± 0.5	20 ± 0.5

DO-201AD DO-27A (d = 1.27)		Type	Dimensions		
			a	b	RM
		C6-1	10 ± 0.5	5 ± 0.5	152 ± 0.5
		C6-2	10 ± 0.5	5 ± 0.5	175 ± 0.5
		C6-3	7 ± 0.5	5 ± 0.5	21 ± 0.5
		C6-4	135 ± 0.5	5 ± 0.5	152 ± 0.5
		C6-5	10 ± 0.5	5 ± 0.5	20 ± 0.5

DO-201AD DO-27A (d = 1.27)		Type	Dimensions		
			a	b	RM
		C4-2	45 ± 0.3	10.5 ± 0.3	75 ± 0.5

P-6		Type	Dimensions		
			a	b	RM
		C6-1	10 ± 0.5	5 ± 0.5	152 ± 0.5
		C6-2	10 ± 0.5	5 ± 0.5	175 ± 0.5
		C6-3	7 ± 0.5	5 ± 0.5	21 ± 0.5
		C6-4	135 ± 0.5	5 ± 0.5	152 ± 0.5