

NPCAP™-PXK Series

- Super low ESR, impedance and high heat resistance have been obtained by using conductive polymer as electrolyte.
- Rated voltage range : 2.5 to 16V_{dc}, Capacitance range : 100 to 560μF
- Suitable for DC-DC converters, voltage regulators and decoupling applications used to computer motherboards etc.
- RoHS Compliant
- Halogen Free

PXK
↓
Downsized
PXE P36




◆SPECIFICATIONS

Items	Characteristics	
Category		
Temperature Range	-55 to +105°C	
Rated Voltage Range	2.5 to 16V _{dc}	
Capacitance Tolerance	±20% (M)	
Surge Voltage	Rated voltage × 1.15V	
Leakage Current	Shall not exceed values shown in STANDARD RATINGS.	
Dissipation Factor (tan δ)	0.12 max.	
Low Temperature Characteristics (Max. Impedance Ratio)	Z(-25°C)/Z(+20°C) ≤ 1.15 Z(-55°C)/Z(+20°C) ≤ 1.25	
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage is applied for 2,000 hours (F46 : 1,000 hours) at 105°C. Appearance No significant damage Capacitance change ≤ ±20% of the initial value DF (tan δ) ≤ 150% of the initial specified value ESR ≤ 150% of the initial specified value Leakage current ≤ The initial specified value	
Bias Humidity	The following specifications shall be satisfied when the capacitors are restored to 20°C after subjecting them to the DC rated voltage at 60°C, 90 to 95% RH for 1,000 hours (F46 : 500 hours). Appearance No significant damage Capacitance change ≤ ±20% of the initial value DF (tan δ) ≤ 150% of the initial specified value ESR ≤ 150% of the initial specified value Leakage current ≤ The initial specified value	
Surge Voltage	The capacitors shall be subjected to 1,000 cycles each consisting of charge with the surge voltage specified at 105°C for 30 seconds through a protective resistor (R=1kΩ) and discharge for 5 minutes 30 seconds. Appearance No significant damage Capacitance change ≤ ±20% of the initial value DF (tan δ) ≤ 150% of the initial specified value ESR ≤ 150% of the initial specified value Leakage current ≤ The initial specified value	
Failure Rate	0.5% per 1,000 hours maximum (Confidence level 60% at 105°C)	

*Note : If any doubt arises, measure the leakage current after following voltage treatment.
Voltage treatment : DC rated voltage are applied to the capacitors for 120 minutes at 105°C.

◆DIMENSIONS [mm]

●Terminal Code : A




Note : L+0.1/-0.2 for F46


Size Code	φD	L	A	B	C	W	P
E61	5	5.8	5.3	5.3	5.9	0.5 to 0.8	1.4
F46	6.3	4.5	6.6	6.6	7.2	0.5 to 0.8	1.9
F61	6.3	5.8	6.6	6.6	7.2	0.5 to 0.8	1.9

◆MARKING

EX) 2.5V330μF



◆PART NUMBERING SYSTEM



Supplement code
Size code

Capacitance tolerance code

Capacitance code (ex. 330μF:331, 560μF:561)

Taping code

Terminal code

Voltage code (ex. 2.5V:2R5, 6.3V:6R3)

Series code

Category

Please refer to "Product code guide (conductive polymer type)"

NPCAP™-PXK Series

◆STANDARD RATINGS

WV (V _{dc})	Cap (μ F)	Size code	Leakage current (μ A max./after 2min.)	ESR (m Ω max./20°C, 100k to 300kHz)	Rated ripple current (mArms/105°C, 100kHz)	Part No.
2.5	220	F46	300	19	2,780	APXK2R5ARA221MF46G
	330	E61	412	16	3,500	APXK2R5ARA331ME61G
	330	F46	700	16	3,500	APXK2R5ARA331MF46G
	560	F61	700	16	3,500	APXK2R5ARA561MF61G
4	180	F46	360	19	2,780	APXK4R0ARA181MF46G
	220	E61	440	17	3,390	APXK4R0ARA221ME61G
	390	F61	780	17	3,390	APXK4R0ARA391MF61G
6.3	150	F46	472	19	2,780	APXK6R3ARA151MF46G
	180	E61	567	17	3,390	APXK6R3ARA181ME61G
	220	F46	700	18	3,200	APXK6R3ARA221MF46G
	330	F61	1,040	17	3,390	APXK6R3ARA331MF61G
16	100	F61	320	24	2,490	APXK160ARA101MF61G