



Strap on a Reel T&B Catalog Number:

TYD-50R
78621071340
Active

UPC Number:
Status:
Description:

Cable Tie Deltec 1/2 in. x 50 ft. Reel of Strap
Features

Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.

Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.

Locking device is marine-grade corrosion-resistant copper alloy.

Application

Ideal solution for bundling in harsh outdoor environments.

General

Material	Weather-Resistant Acetal
Color	Black

Dimension Information

Length (feet)	50
Width (inches)	.500

Specifications

Temperature Rating	-30°F to 150°F
--------------------	----------------

Tooling

Application Tools	WT3D
-------------------	------

Packaging

T&B Order Multiple	5
T&B Inner Pack	1
Package in Units	5
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	97 lbs. per 100

Application Support

Overview	Available on Website
Material Selection Guide	Available on Website

Notes

The recommended maximum continuous static loading for the Deltec® straps is 20 lbs. Per strap. For best results suggested spacing is 15 inches. It is the responsibility of the user to determine whether or not their application meets our recommendation.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com