

E-Z Hook, A Div. of Tektest, Inc.
P.O. Box 660729,
Arcadia, CA 91066-0729
Phone: 626.446.6175
Fax: 626.446.0972
E-mail: info@e-z-hook.com
Website: www.e-z-hook.com

[All Categories](#) > [Test Leads](#) > [Alligator Clip Test Leads](#) > [Item # 684](#)

Item # 684, Alligator Jumper



[larger image](#)

Alligator Jumper

Standard alligator clip to standard alligator clip test lead jumper with heavier gauge wire.

Standard alligator test lead is offered in 18 AWG PVC wire. Additional lead lengths, wire types, and custom leads available upon request.

Available in 10 standard colors.

[Specifications](#) · [Lead Length and Cable Length Information](#) · [How to Order Test Leads & Cable Assemblies](#) · [Field Servicing Information](#)

Specifications

Gator Model	Standard
Wire Gauge	18 AWG
Wire	PVC
Connector #1	9274, standard alligator clip
Connector #2	9274, standard alligator clip
Standard Lengths	3 in (8 cm) 6 in (15 cm) 12 in (30 cm) 18 in (45 cm) 24 in (60 cm) 36 in (90 cm) 48 in (120 cm) 60 in (150 cm)
Colors	 Black (0) larger image  Brown (1) larger image  Red (2) larger image  Orange (3) larger image  Yellow (4) larger image  Green (5) larger image  Blue (6)

	larger image  Violet (7) larger image  Gray (8) larger image  White (9) larger image
Unit	each


Lead Length and Cable Length Information

E-Z-Hook offers a selection of standard length test leads, patch cords, and cable assemblies. We also offer custom lengths to fit special requirements.

All length measurements are made in inches, see diagrams below for measuring examples:



Standard lengths in inches for test lead and patch cord assemblies:	
3" (8 cm) lead wire	18" (45 cm)
4" (10 cm) lead wire	24" (60 cm)
6" (15 cm)	36" (90 cm)
8" (20 cm)	48" (120 cm)
12" (30 cm)	60" (150 cm)



Standard lengths in inches for cable assemblies:	
6" (15 cm)	30" (75 cm)
12" (30 cm)	36" (90 cm)
18" (45 cm)	48" (120 cm)
24" (60 cm)	60" (150 cm)
*Longer lengths available	

How to Order Test Leads & Cable Assemblies

Ordering E-Z-Hook test leads and cable assemblies is E-Z. Select the part number supplied in the product section, then select your lead or cable length and color. Example: 704XR-18-RED (Part No.-Length-Color). Variations of each hook may be ordered in place of the standard hook. Ordering information is provided at the beginning of each section.

Field Servicing Information

Most hooks are designed to be field serviceable. To replace a lead wire, pull on the plunger until it slips free of the body. Strip lead wire 3/4" (19 mm), feed wire through plunger and wrap around terminal as shown. Solder and cut off excess wire at solder point. Reassemble part, making sure the terminal and nylon fins enter their respective grooves. Keep slack in lead wire pulled out while assembling to prevent binding.

NOTE: To disassemble XM Micro-Hook connectors or leads, actuate plunger to expose hook and grasp behind hook with long nose pliers before pulling plunger off. Failure to do so will result in damage to part.

