




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		H	REVISED PER ECR-12-013459	27NOV2012	KH	PD



- 1
- CONTINUOUS STRIP ON REELS
- 2
- MATING TAB THK TO BE 0.81±0.025 [.032±.001]
- 3
- WIRE SIZE IS #14-#10 AWG.
- 4
- INSULATION RANGE IS 3.81-5.08 [.150-.200] DIA.




VIEW A-A
SCALE 8:1



SECTION B-B
SCALE 8:1




SECTION C-C
SCALE 8:1



SECTION D-D
SCALE 8:1

TIN	BRASS	62253-2
-	BRASS	62253-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 7/12/89		 TE Connectivity			
		CHK MS FEHER 7/12/89					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C MEYERS 7/12/89		NAME	
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE, FASTON TM PIGGYBACK, 6.35 [.250] SERIES	
		1 PLC ± -		—			
		2 PLC ± -		APPLICATION SPEC			
		3 PLC ± 0.38 [.015]		114-2082		SIZE	
		4 PLC ± -		WEIGHT		CAGE CODE	
MATERIAL		FINISH		—		DRAWING NO	
SEE TABLE		SEE TABLE		A2		00779	
				CUSTOMER DRAWING		C-62253	
						RESTRICTED TO	
						—	
						SCALE	
						4:1	
						SHEET	
						1 of 1	
						REV	
						H	