

C0603C0G1E4R7C030BA (TDK item description : C0603C0G1E4R7CT****)

Applications



Commercial Grade



Please refer to Part No. CGA1A2C0G1E4R7C030BA for automotive use.


Feature



General (Up to 50V)

Series

C0603 [EIA CC0201]



Size

Length(L)	0.60mm +/-0.03mm
Width(W)	0.30mm +/-0.03mm
Thickness(T)	0.30mm +/-0.03mm
Terminal Width(B)	0.10mm Min.
Terminal Spacing(G)	0.20mm Min.
Recommended Land Pattern(PA)	0.25 to 0.35mm
Recommended Land Pattern(PB)	0.20 to 0.30mm
Recommended Land Pattern(PC)	0.25 to 0.35mm
Recommended Slit Pattern(SD)	

Electrical Characteristics

Capacitance	4.7pF +/-0.25pF
Rated Voltage	25Vdc
Temperature Characteristic	C0G(0+/-30ppm/degC)
Q	494 Min.
Insulation Resistance	10000MΩ Min.

Other

Soldering Method	Reflow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	15000Pcs Min.

C0603C0G1E4R7C030BA

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)

