



CREATES COMPRESSION OF INTERFACE MATERIAL

Tputty™ 502 is the best material for applications where large tolerance differences create the need for compression of the interface material beyond 50% of its original thickness.

Tputty™ 502 will flow and ensure low pressures on the components being cooled. In conjunction with outstanding compression characteristics, Tputty™ 502 has a high thermal conductivity, resulting in very low thermal resistance.

Tputty™ 502 is naturally tacky and requires no additional adhesive coating that can inhibit thermal performance.

FEATURES AND BENEFITS

- Soft and ultra high compressibility for low stress applications
- 3 W/mK thermal conductivity
- Available in sheets 0.020" - 0.200" (0.5mm - (5.0mm) thick and in bulk
- Naturally tacky needing no further adhesive coating

APPLICATIONS

- Cooling components to the chassis or frame
- Entire large panel PCB cooling
- Semiconductor automated test equipment (ATE)
- Any high compression low stress application

global solutions: local support™

Americas: +1.800.843.4556

Europe: +49.8031.2460.0

Asia: +86.755.2714.1166

CLV-customerservice@lairdtech.com

www.lairdtech.com/thermal

	Tputty™ 0.020	Tputty™ 0.040	Tputty™ 0.060	Tputty™ 0.080	Tputty™ 0.100	TEST METHOD
Construction & Composition	Reinforced boron nitride filled silicone elastomer	Reinforced boron nitride filled silicone elastomer	Reinforced boron nitride filled silicone elastomer	Reinforced boron nitride filled silicone elastomer	Reinforced boron nitride filled silicone elastomer	
Color	White	White	White	White	White	Visual
Thickness	0.020" (0.51mm)	0.040" (1.02mm)	0.060" (1.52mm)	0.080" (2.03mm)	0.100" (2.54mm)	
Thickness Tolerance	± 0.002" (± 0.05mm)	± 0.003" (± 0.08mm)	± 0.004" (± 0.10mm)	± 0.004" (± 0.10mm)	± 0.005" (± 0.13mm)	
Specific Gravity	1.39 g/cc	1.38 g/cc	1.37 g/cc	1.37 g/cc	1.36 g/cc	Helium Pycnometer
Hardness *without fiberglass	05 Shore OO	05 Shore OO	05 Shore OO	05 Shore OO	05 Shore OO	ASTM D2240
Outgassing TML (Post Cured)	0.11%	0.11%	0.11%	0.11%	0.11%	ASTM E595
Outgassing CVCN (Post Cured)	0.06%	0.06%	0.06%	0.06%	0.06%	ASTM E595
Temperature Range	-45°C to 200°C	-45°C to 200°C	-45°C to 200°C	-45°C to 200°C	-45°C to 200°C	
Thermal Conductivity	3 W/mK	3 W/mK	3 W/mK	3 W/mK	3 W/mK	ASTM D5470 (modified)
Thermal Impedance @ 10 psi @ 69KPa	0.44 °C-in ² /W 2.84 °C-cm ² /W	0.49 °C-in ² /W 3.16 °C-cm ² /W	0.53 °C-in ² /W 3.42 °C-cm ² /W	0.58 °C-in ² /W 3.74 °C-cm ² /W	0.62 °C-in ² /W 4.00 °C-cm ² /W	ASTM D5470 (modified)
Thermal Expansion	92 ppm/C	92 ppm/C	92 ppm/C	92 ppm/C	92 ppm/C	IPC-TM-650 2.4.24
Breakdown Voltage	2000 Volts AC	4000 Volts AC	>5000 Volts AC	>5000 Volts AC	>5000 Volts AC	ASTM D149
Volume Resistivity	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	ASTM D257
Dielectric Constant @ 1MHz	3.20	3.20	3.20	3.20	3.20	ASTM D150

STANDARD THICKNESSES

0.020" (0.51mm)	0.030" (0.76mm)	0.040" (1.02mm)	0.050" (1.27mm)
0.060" (1.52mm)	0.070" (1.78mm)	0.080" (2.03mm)	0.090" (2.29mm)
0.100" (2.54mm)	0.110" (2.79mm)	0.120" (3.05mm)	0.130" (3.30mm)
0.140" (3.56mm)	0.150" (3.81mm)	0.160" (4.06mm)	0.170" (4.32mm)
0.180" (4.57mm)	0.190" (4.83mm)	0.200" (5.08mm)	

Consult the factory for alternate thicknesses.

BULK

Tputty™ 502 is available in bulk form in the following sizes:
100 cc Jar 500 cc Jar 1000 cc Jar

Consult the factory for alternate bulk sizes.

STANDARD SHEET SIZES

9" x 9" (229mm x 229mm) and 18" x 18" (457mm x 457mm).
9" x 9" only over 0.100" thickness

Tputty™ 502 is available in individual die cut shapes. Pressure sensitive adhesive is not applicable for Tputty™ products.

REINFORCEMENT

Tputty™ 502 sheets are reinforced on both sides with fiberglass.

Data for design engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

THR-SPEC-Tputty-502 0710

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2010 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.

A13502-00 Rev G, 2/05/07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Technologies:

[A10242-04](#) [A10243-04](#) [A10244-06](#) [A10245-06](#) [A10246-04](#) [A10247-05](#) [A10247-04](#) [A10248-04](#) [A10538-18](#)
[A10249-14](#) [A10874-12](#) [A10874-01](#) [A10233-31](#) [A10233-30](#) [A10234-38](#) [A10234-31](#) [A10235-36](#) [A14938-00](#) [A14938-](#)
[00-W5](#) [A10235-31](#) [A10236-05](#) [A10236-04](#) [A10237-22](#) [A10237-21](#) [A10238-08](#) [A10238-09](#) [A10241-09](#) [A10548-08](#)
[A10538-17](#) [A10548-5](#) [A10239-09](#) [A10548-7](#) [A10240-05](#) [A10548-6](#) [A10548-8](#)