

LTC 0455 Series

Color Cameras



Security Systems



- 1/3-inch Format CCD Imager
- High Sensitivity
- Advanced Digital Signal Processing
- High Resolution with Outstanding Picture Quality
- Extended Sensitivity with NightSense™
- Auto Detection of Lens Type with Lens Wizard
- Easy to Install
- Accepts AC or DC Voltages

The LTC 0455 series are compact rugged, 1/3-inch image format digital color CCD cameras. Their superior sensitivity, resolution and picture quality provide optimal performance in virtually all situations.

This fully automatic camera is ready to work for you, and is easy to install in even the most demanding applications. On-screen Displays (OSD) provide quick and easy access to all camera features.

The LTC 0455 cameras also comes with a lens wizard that automatically detects the type of lens installed and provides an OSD guide that allows the installer to easily adjust the lens level and focus without special tools or filters.

The automatic black level feature, now introduced in color cameras, enhances contrast by removing veiling glare from the picture. NightSense™ is used to further extend the excellent sensitivity by a factor 3 in monochrome operation. This mode can be automatically activated under low light situations.

Automatic sensing for tracking white balance, provides true to life color images in indoor and outdoor applications.

The ability to operate on AC or DC provides added flexibility to system designs and reduces the amount of training and support items to keep on-hand.

Easy Installation, digital signal processing, on screen displays, superior picture quality and reliability brings the video performance of high resolution color cameras to a level never reached before and makes the LTC 0455 series the best choice for first time and professional users.

Bilinx Technology

The LTC0455 series cameras incorporate Bilinx. Bilinx is a bi-directional communication capability embedded in the video signal of all Bosch Dinion cameras. With Bilinx technicians can check status, change camera settings and even update firmware from virtually anywhere along the video cable. Bilinx reduces service and installation time, provides for more accurate set-up and adjustment, and improves overall performance. In addition, Bilinx uses the standard video cable to transmit alarm and status messages, providing superior performance without additional installation steps.

Security you can rely on

BOSCH

SPECIFICATIONS

Electrical

Model No.	Rated Voltage	Voltage Range	System
LTC 0455/10	12 VDC	10.8-39 VDC	PAL
	24 VAC, 50 Hz	12-28 VAC, 45-65 Hz	
LTC 0455/20	12 VDC	10.8-39 VDC	NTSC
	24 VAC, 60 Hz	12-28 VAC, 45-65 Hz	
LTC 0455/50	230 VAC, 50 Hz	85-265 VAC, 45-65 Hz	PAL
LTC 0455/60	120 VAC, 60 Hz	85-265 VAC, 45-65 Hz	NTSC

Power Consumption: 4 W, excluding lens.

Imager: Interline transfer CCD, 1/3-inch image format.

Active Picture Elements:

PAL Models: 752 H x 582 V.

NTSC Models: 768 H x 494 V.

Sensitivity (3200 k):

	Usable Picture (30 IRE)	Usable Picture (50 IRE)	Full Video
Scene illumination ¹⁾ (color mode) fc	0.03	0.07	0.26
lx	0.30	0.65	2.6
Imager illumination (color mode) fc	0.005	0.010	0.040
lx	0.045	0.10	0.40
Scene illumination ¹⁾ (night mode) fc	0.012	0.026	0.104
lx	0.12	0.26	1.04
Imager illumination (night mode) fc	0.002	0.004	0.016
lx	0.018	0.040	0.16

¹⁾ for f/1.2 lens, 89% scene reflectance.

Horizontal Resolution: 480 TVL.

Signal-to-noise Ratio: 50 dB.

AGC: 21 dB, (max).

Electronic Shutter:

Automatic, 1/50 to 1/125000 sec. (CCIR),

1/60 to 1/150000 sec. (EIA)

Aperture Correction: Horizontal and vertical, symmetrical.

Backlight Compensation: Center window weighting.

White Balance: Automatic sensing (2500 - 9000 K).

Video Output: Composite video 1.0 Vpp, 75 ohms.

Synchronization:

Line-Lock :	(When powered by AC only) Synchronizes the camera to the power line zero crossing for roll-free vertical interval switching. Vertical phase delay can be adjusted (0 - 358 degrees) to allow vertical synchronization in multi-phase power installations.
	Free Running (When DC-supply or L/L off): Internal crystal reference is standard on all models.

Controls

Video level.

Shutter: AES/Off/Flickerless

AGC: On/Off

BLC: On/Off

Auto Black: On/Off

NightSense™: On/Auto/Forced

ATW: On/Hold

R-offset, B-offset

Vphase Adjustment: 0 - 358 degrees

MECHANICAL

Connectors:

- Video Output: BNC.

- Video/DC-Iris connector: 4-pin EIA-J.

Power:

LTC 0455/10 and LTC 0455/20:

push type connectors, polarity independent,

isolated from video output terminals

LTC 0455/50: 2-wire power cord with Euro plug

LTC 0455/60: 2-wire power cord with polarized plug

Camera mounting: Top and Bottom, 1/4-inch 20 UNC.

Lens mounting: C and CS.

Dimensions: (HxWxD*) 58 x 66 x 122 mm
(2.28 x 2.6 x 4.8 inch). *including connectors.

Weight: 0.45 kg (0.99 lb).

ENVIRONMENTAL

Temperature range:

Operating: -20 to 50°C (-4 to 122 °F).

Storage: -25 to 70°C (-13 to 158 °F).

Operating Humidity: 5% to 93% non-condensing.

Electromagnetic compatibility:

EMC immunity: According EN50130-4

EMC emission: According EN505022 class B,

According FCC, class B part 15

Safety:

LTC 0455/10 and LTC 0455/50: EN60065

LTC 0455/20 and LTC 0455/60: UL6500

Accessories

Lenses DC iris:

LTC 3364/40: 2,8 - 12 mm, F1,4 - F360.

LTC 3374/20: 5 - 50 mm, F1,4 - F185.

Power Transformers and Power Supplies:

Model No.	Rated Input	Rated Output
TC1334	120 VAC, 60 Hz	24 VAC, 30 VA
TC120PS	120 VAC, 60 Hz	15 VDC, 9 VA
TC220PSX-24	220 - 240 VAC, 50/60 Hz	24 VAC, 20 VA
TC220PS	220 - 240 VAC, 50/60 Hz	15 VDC, 9 VA

Bosch Security Systems.
5600 JB Eindhoven
The Netherlands
Tel: +31 (40) 27 80000
Fax: +31 (40) 27 80001
www.boschsecuritysystems.com

BOSCH