






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
AF	50				A	REV AF-5787, RELEASE PER FASR	12/7/88

1 CONTINUOUS STRIP ON REELS



SECTION A-A
SCALE 8:1

SECTION B-B
SCALE 10:1

F	.100	.260	F	.055	.041	22	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± - MATERIAL #4 HARD BRASS FINISH TIN PL .000080 MIN	.040-.060	29-22	63506-1
					.038	24		INSULATION RANGE	MAGNET WIRE RANGE	PART NO
					.037	26		OR P. FORTNEY 7/6/88	AMP INCORPORATED Harrisburg, Pa. 17105	
					.035	28		OR MS FEHER 7/8/88		
					.035	29		APPD 7/8/88		
		APPD 7/8/88								
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	HEIGHT ±.002	WIRE	PRODUCT SPEC	RECEPTACLE, PIN, .062 DIA		
INSUL BARREL CRIMP			WIRE BARREL CRIMP				APPLICATION SPEC	SIZE B	PSCH NO 00779	DRAWING NO 63506
							WEIGHT	SCALE 5:1	SHEET 1 OF 1	